


MALE PCB PINS

PRINTED CIRCUIT PINS

3117

3117-X-00-XX-00-00-08-0

Swage mount in .035 hole




Basic Part Number	Board Thickness	Length V
3117-1	.031	.047
3117-2	.062	.078
3117-3	.094	.110
3117-4	.125	.141

3114/3115

311X-X-00-XX-00-00-08-0

Swage mount in .035 mounting hole




Basic Part Number	Board Thickness	Length A	Length V
3114-1	.031	.150	.051
3114-2	.062	.150	.082
3115-1	.031	.300	.051
3115-2	.062	.300	.082

3112

3112-X-00-XX-00-00-08-0

Swage mount in .043 hole




Basic Part Number	Board Thickness	Length V
3112-1	.031	.051
3112-2	.062	.082
3112-3	.094	.113

3118/3119

311X-X-00-XX-00-00-08-0

Swage mount in .035 hole




Basic Part Number	Board Thickness	Length S	Length V
3118-1	.031	.170	.051
3118-2	.062	.170	.082
3119-1	.031	.420	.051
3119-2	.062	.420	.082

3139

3139-0-00-XX-00-00-08-0


Wire crimp termination. Accepts wire sizes 24 AWG Max. / 28 AWG Min.



3602

3602-0-07-XX-00-00-08-0


Annealed
Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



3131

3131-1-00-XX-00-00-08-0


Swage mount in .043 hole



0912

0912-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except swage pins which are annealed)

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
Diameters: $\pm .002$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)
- ◆ 21 20 μ " GOLD OVER NICKEL (RoHS)
- ◆ 34 50 μ " GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3602-0-07-21-00-00-08-0](#) [3131-1-00-01-00-00-08-0](#) [3119-2-00-01-00-00-08-0](#) [3119-1-00-01-00-00-08-0](#) [3118-2-00-01-00-00-08-0](#) [3118-1-00-01-00-00-08-0](#) [3117-4-00-01-00-00-08-0](#) [3117-3-00-01-00-00-08-0](#) [3117-2-00-01-00-00-08-0](#) [3117-1-00-01-00-00-08-0](#) [3114-2-00-01-00-00-08-0](#) [3114-1-00-01-00-00-08-0](#) [3112-3-00-01-00-00-08-0](#) [3112-2-00-01-00-00-08-0](#) [3112-1-00-01-00-00-08-0](#) [0912-0-00-80-00-00-03-0](#) [0912-0-00-01-00-00-03-0](#) [3131-1-00-80-00-00-08-0](#) [3119-2-00-80-00-00-08-0](#) [3119-1-00-80-00-00-08-0](#) [3118-2-00-80-00-00-08-0](#) [3118-1-00-80-00-00-08-0](#) [3117-4-00-80-00-00-08-0](#) [3117-3-00-80-00-00-08-0](#) [3117-2-00-80-00-00-08-0](#) [3117-1-00-80-00-00-08-0](#) [3114-2-00-80-00-00-08-0](#) [3114-1-00-80-00-00-08-0](#) [3112-3-00-80-00-00-08-0](#) [3112-2-00-80-00-00-08-0](#) [3112-1-00-80-00-00-08-0](#) [0912-0-00-15-00-00-03-0](#) [0912-0-00-21-00-00-03-0](#) [0912-0-00-34-00-00-03-0](#) [3112-1-00-15-00-00-08-0](#) [3112-1-00-34-00-00-08-0](#) [3112-2-00-15-00-00-08-0](#) [3112-2-00-34-00-00-08-0](#) [3112-3-00-21-00-00-08-0](#) [3112-3-00-34-00-00-08-0](#) [3114-1-00-15-00-00-08-0](#) [3114-1-00-21-00-00-08-0](#) [3114-1-00-34-00-00-08-0](#) [3114-2-00-15-00-00-08-0](#) [3114-2-00-21-00-00-08-0](#) [3114-2-00-34-00-00-08-0](#) [3117-1-00-15-00-00-08-0](#) [3117-1-00-34-00-00-08-0](#) [3117-2-00-15-00-00-08-0](#) [3117-2-00-34-00-00-08-0](#) [3117-3-00-15-00-00-08-0](#) [3117-3-00-21-00-00-08-0](#) [3117-3-00-34-00-00-08-0](#) [3117-4-00-15-00-00-08-0](#) [3117-4-00-21-00-00-08-0](#) [3117-4-00-34-00-00-08-0](#) [3118-1-00-15-00-00-08-0](#) [3118-1-00-21-00-00-08-0](#) [3118-1-00-34-00-00-08-0](#) [3118-2-00-15-00-00-08-0](#) [3118-2-00-21-00-00-08-0](#) [3118-2-00-34-00-00-08-0](#) [3119-1-00-15-00-00-08-0](#) [3119-1-00-21-00-00-08-0](#) [3119-1-00-34-00-00-08-0](#) [3119-2-00-15-00-00-08-0](#) [3119-2-00-21-00-00-08-0](#) [3119-2-00-34-00-00-08-0](#) [3131-1-00-15-00-00-08-0](#) [3131-1-00-21-00-00-08-0](#) [3131-1-00-34-00-00-08-0](#) [3139-0-00-21-00-00-08-0](#) [3139-0-00-34-00-00-08-0](#) [3602-0-07-15-00-00-08-0](#) [3115-2-00-00-00-00-08-0](#) [3131-1-00-00-00-00-08-0](#) [0912-0-00-00-00-00-03-0](#) [3117-2-00-00-00-00-08-0](#) [3117-1-00-00-00-00-08-0](#) [3117-3-00-00-00-00-08-0](#) [3114-1-00-00-00-00-08-0](#) [3112-3-00-00-00-00-08-0](#) [3115-1-00-00-00-00-08-0](#) [3117-4-00-00-00-00-08-0](#) [3118-1-00-00-00-00-08-0](#) [3112-2-00-00-00-00-08-0](#) [3114-2-00-00-00-00-08-0](#) [3112-1-00-00-00-00-08-0](#)