



N Connectors, 50 Ohm (Continued)

Panel Jacks, Crimp




Recommended
Panel Cutout

Connector Cable Range Selection Code [†]	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	Integral Die Hand Tool [‡]
D	58, 58A, 58B, 58C	Dual Crimp	Gold	Silver	TEFLON	Mil Type	Weatherproof	225606-4*	1.937 49.2	220045-2
M	8, 8A, 213	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	Weatherproof	225666-2	1.937 49.2	220015-1
		Dual Crimp	Gold	Silver	TEFLON	Mil Type	02B0016 Weatherproof	225089-2	1.937 49.2	220015-1
V	9, 9A, 9E, 214	Dual Crimp	Gold	Silver	TEFLON	Mil Type	02B0C17 Weatherproof	225089-1	1.937 49.2	220015-1


[†]Refer to pages 14 and 15 for code specifications.

[‡]Hand Tool 69710-1, Pneumatic Tools 69365 and 69365-3, with Die Insert 220062-1, are available to terminate these connectors.


Panel Jacks, Solder



Part No. 134866-1




Part No. 135014-1




Recommended
Panel Cutout

Panel Plug, Solder



Part No. 135012-1



Recommended
Panel Cutout