

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0539490878

Status:

Active

Overview:

SlimStack™ 0.50mm Pitch Board-to-Board Connectors

Description:

0.50mm Pitch SlimStack™ Plug, Surface Mount, Dual Row, Vertical, 2.50mm Stack Height, with Solder Tab, 80 Circuits

Documents:

- 3D Model

Product Specification PS-54150-002 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	PCB Headers
Series	53949
Application	Board-to-Board, Signal
Overview	SlimStack™ 0.50mm Pitch Board-to-Board Connectors
Product Name	SlimStack™
UPC	822348287604

Physical

Breakaway	No
Circuits (Loaded)	80
Circuits (maximum)	80
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	2.50mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	135.700/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.254µm
Plating min - Termination	0.102µm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

Product Specification	PS-54150-002
Sales Drawing	SD-53949-006, SD-53949-007



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

53949 Series

Mates With

54150 SlimStack™ Receptacle

This document was generated on 08/14/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION