








LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
AD	00	0		RELEASED PER EC 0512-0235-04	04OCT04	BM



$\phi 0.725 \pm 0.075$
 $\phi 0.15 \pm 0.015$
PLATED THROUGH HOLE

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCP000 G30A 32250.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS ALLOY NO. C51100, TEMPER: H04.
- 3 CONTACT FINISH:(D)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
FLASH GOLD PER ASTM B 488, OVER
0.00076 MIN PALLADIUM-NICKEL OVER UNDERPLATE, OR
0.00076 MIN GOLD PER ASTM B 488 OVER UNDERPLATE.
ON LEADS:
0.00127 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING, LOCATED APPROXIMATELY AS SHOWN.



6	1	10	5	11.88	3	8	5536620-1
E	D	C	B	A	FINISH	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				DIN D.R.BENDER 02/15/94	Tyco Electronics Corporation		
DIMENSIONS: mm				CHK D.R.BAECHTLE 05/19/94	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD	PRODUCT SPEC		
0 PLC ± -					APPLICATION SPEC		
1 PLC ± -					SIZE		
2 PLC ± 0.13					CAGE CODE		
3 PLC ± -					DRAWING NO		
4 PLC ± -					RESTRICTED TO		
ANGLES ± -					A1 00779C=5536620		
FINISH					CUSTOMER DRAWING		
1					SCALE 4:1		
2					SHEET 1 OF 1		
3					REV Q		