

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

OCT ,2001.



© COPYRIGHT 2001 By --

ALL RIGHTS RESERVED.

LOC
ESDIST
/

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	M2	REVISED PER ECO-11-005033	25MAR11	RK	HMR



DETAIL L (SCALE 5:1)

HOW TO MATE AND UNMATE

MATE: ① → ④
UNMATE: ⑤ → ⑦



(APPLIED TO SHEET 1-2)

1. MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC UL94V-0
CONTACT: COPPER ARROY
LOCK LEVER: STAINLESS STEEL
SOLDER PEG: COPPER ARROY
- △ FINISH ; CONTACT AREA: GOLD FLASH ON 0.0013MIN ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLT.
SOLDER PEG: TIN PLATING.

△ MECHANICAL KEY POSITION OF CONNECTOR SEE TABLE.




△ TOLERANCES NON-CUMULATIVE.

△ NOT TO SCALE.

△ [] INSIDE MUST BE RESIST COAT EXCEPT SOLDER PATTERN.

7. IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.

△ FINISH ; CONTACT AREA: 0.00076 GOLD ON 0.0013MIN ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLT.
SOLDER PEG: TIN PLATING.



GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ > 10 : ±0.25
100 ≥ > 30 : ±0.3
ANGLES : ±3°

△	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1473150-6
△	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1-1473150-4
△	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1473150-4
△	AVAILABLE	2.5V (DDR1)	18.45	1.5	1.8	200	1473150-1
FINISH	TOOLING STATUS	POWER SUPPLY	D5	D4	D3	POS	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B.WONG	20JUL10	 TE Connectivity		
			CHK C.WANG	20JUL10			
			APVD S.YAO	20JUL10			
			PRODUCT SPEC 108-5701				
DIMENSIONS: MM			APPLICATION SPEC		DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS STANDARD PROFILE REVERSE TYPE (NEW LATCH TYPE)		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			WEIGHT 4.7g		SIZE A3	CAGE CODE 00779	DRAWING NO C-1473150
MATERIAL			CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 4	REV M2

