




D



C





B



A

- 2 PHOSPHOR BRONZE
- 3 LCP, UL94V-0
- 4 FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE; APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- 10 HOLE DIAMETER SHOULD BE 3.10 WHEN USING FEED THROUGH GUIDE PIN P/N 120759
CLEARANCE FOR M3x0.5 THREAD





D

C

B

A

5.50	9.7	5120661-2
5.50	8.2	5120661-1
N	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. CARBO	06DEC04	 TE Connectivity		
DIMENSIONS: mm			CHK R. PATTERSON	06DEC04			
			APVD R. PATTERSON	06DEC04	NAME HEADER ASSEMBLY, 50 POSITION, RIGHT HAND, 10 ROW, Z PACK HS3		
			PRODUCT SPEC				
			APPLICATION SPEC		SIZE A1		
			WEIGHT -				
MATERIAL HOUSING: 3			CUSTOMER DRAWING		CAGE CODE 00779		
CONTACTS: 2			SIGNAL CONTACT: 4		DRAWING NO 5120661		
					RESTRICTED TO -		
					SCALE 5:1		
					SHEET 1		
					OF 1		
					REV B2		