

1825271-1 Product Details

Share

Print

Email

1825271-1

TE Internal Number: 1825271-1

Active

View 3D PDF

Slide Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 3 Positions
- Six Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Top
- Actuator Color = Black
- MSS Series

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: - SLIDE SWITCH, MSS 6200 SERIES, 6P-DT (PDF, English) Catalog Pages/Data Sheets: - SWITCHES_CORE_PROGRAM_CATALOG (PDF, English) Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version A) 3D Model (IGES, Version A) 3D Model (STEP, Version A) List all Documents	Additional Information: - Product Line Information Related Products: - Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Actuator Style = Extended, Top - Series = MSS - Mount Angle = Vertical - Terminal Configuration = Standard - Grade = Instrumentation - Termination Type = PC - PCB Mount Retention = With - PCB Mount Retention Type = Guide Posts Electrical Characteristics: - Contact Rating = 300mA @ 125 VAC Dimensions: - PCB Tail Length (mm [in]) = 3.00 [0.118] - Actuator Length (mm [in]) = 5.99 [0.236] Body Features: - Actuator Color = Black - Mount Style = Through-Hole - Actuator Material = Polyester	Contact Features: - Contact Plating = Silver Housing Features: - UL Flammability Rating = UL 94V-0 Configuration Features: - Number of Positions = 3 - Configuration (Pole-Throw) = Six Pole - Double Throw - Threaded Case = With - Number of Actuators = Single Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant Identification Marking: - Stamped Marking = With Other: - Brand = Alcoswitch