






4#40 Thread



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PBT
 FLAMABILITY RATING: UL94-V0
 COLOR: BLUE
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: STEEL TIN PLATED
 QUALITY CLASS: 3 AS PER CECC 75 301-802

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 85°C
 COMPLIANCE: LEAD FREE AND ROHS


ELECTRICAL
 CURRENT RATING: 3A
 WORKING VOLTAGE: 250V AC
 INSULATOR RESISTANCE: >3000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC/MN
 CONTACT RESISTANCE: 30 mOHM MAX

PACKAGING
 TRAY + BAG*
 *Strain relief is always delivered in a separate bag for optional use

DIMENSION

PINS	A	B	C	D
9	16.92	25.00	30.80	22.40
15	25.25	33.30	39.20	30.80
25	38.96	47.10	53.10	44.50
37	55.42	63.50	69.40	61.40

NOTE
 Pre-crim position (can slightly vary because of not totally fixed part)
 After crimp position (can slightly vary depends on the tooling used)

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK		
J	22-AUG-12	UL	GG	APPROVAL: RJ	UNIT: MM	DESCRIPTION: MALE IDC WITH UNC 4-40 NUT D-SUB		SIZE A4
I	14-NOV-11	TOTAL HEIGHT	GG		SCALE:			
H	31-AUG-11	DIM A	GG		SHEET: 1/1	WERI PART NO: 618 0xx 226 221		
REV	DATE	FILE	BY		DRAW: JOE			