

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-017969	14DEC05	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

THIS ITEM MUST BE WHITE
- 5

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 4 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:CENTRE CONTACT:1.50 mOhm Max

OUTER CONTACT:0.20 mOhm Max

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 6

MECHANICAL CHARATERISTICS


COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A

DURABILITY:500 Cycles Min
- 7


ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		2	2	PTFE	INSULATION	12
		1	1	BRASS	SLEEVE	11
		1	1	BRASS	CONTACT II	10
		1	1	BRASS	WASHER	9
		1	1	SPRING STEEL	SPRING	8
		1	1	BRASS	RETAINING RING	7
		1	1	SILICON RUBBER	GASKET	6
		1	1	PTFE	INSULATION	5
		1	1	BRASS	BODY 2	4
		1	1	BRASS	SHELL	3
		1	1	BRASS	CONTACT I	2
		1	1	BRASS	BODY 1	1
		6--0	1--0	MATERIAL	DESCRIPTION	ITEM

QUANTITY PER ASSY			PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	14DEC05	tyco Electronics		Tyco Electronics Corporation	
		CHK S.PARLOW	14DEC05			Bideford EX39 4HE	
DIMENSIONS: mm		APVD F.WHEELER-KING	14DEC05	NAME BNC TEE ADAPTOR J-P-J 50 OHM			
		PRODUCT SPEC —	— —				
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL SEE TABLE	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-1337459	RESTRICTED TO —
				SCALE NTS	SHEET 1	OF 1	REV C