



CONTENTS


	Page
APPLICATION DETAILS	5
DIODES — SCHOTTKY	3
— STANDARD RECOVERY	4
— ULTRA FAST RECOVERY	4
ENCAPSULATED BRIDGES	4
FOOTPRINT AND PAD DIMENSIONS	8
HEXFETs	3
MILITARY CAPABILITY	9
OUTLINES	6
TAPE REEL INFORMATION	7 & 8

HEXFETs

N-CHANNEL

Types	V _{DS} V	R _{DS(ON)} (max) Ω	I _D cont T _C = 25°C A	I _{DM} pulsed A	P _D max W	Bulletin	Case Style
IRFS1Z3†	60	3.20	0.75	2.5	3.5	PD-9.438	TO-243AA (SOT-89) Outline 1 
IRFS1Z0†	100	2.40	0.90	3.5	3.5	PD-9.438	
IRFR024 IRFR014	60	0.10 0.20	15.0 8.2	60.0 33.0	42 25	— —	TO-252AA (D-pak) Outline 2 
IRFR121 IRFR111	80	0.27 0.54	8.4 4.7	34.0 17.0	50 30	PD-9.523 PD-9.524	
IRFR120 IRFR110	100	0.27 0.54	8.4 4.7	34.0 17.0	50 30	PD-9.523 PD-9.524	
IRFR220 IRFR222 IRFR210 IRFR212	200	0.80 1.20 1.50 2.40	4.6 3.8 2.7 2.1	18.0 15.0 11.0 8.4	42 42 25 25	PD-9.525 PD-9.525 PD-9.526 PD-9.526	
IRFR224 IRFR214	250	1.10 2.00	3.8 2.0	15.0 8.0	42 25	PD-9.600 PD-9.601	
IRFR320 IRFR310	400	1.80 3.60	3.1 1.7	12.0 4.3	42 25	PD-9.598 PD-9.597	
IRFR420	500	3.00	2.4	9.6	42	PD-9.599	

P-CHANNEL

IRFR9024 IRFR9025 IRFR9014 IRFR9015	-60	0.28 0.30 0.50 0.70	-9.9 -9.0 -5.3 -4.5	-40.0 -36.0 -21.0 -18.0	42 42 25 25	PD-9.517 PD-9.517 PD-9.516 PD-9.516	TO-252AA (D-pak) Outline 2 
IRFR9121 IRFR9111	-80	0.60 1.20	-5.9 -3.2	-24.0 -13.0	42 25	PD-9.520 PD-9.519	
IRFR9120 IRFR9110	-100	0.60 1.20	-5.9 -3.2	-24.0 -13.0	42 25	PD-9.520 PD-9.519	
IRFR9220 IRFR9222 IRFR9210 IRFR9212	-200	1.50 2.40 3.00 4.50	-3.6 -2.8 -2.0 -1.6	-14.0 -11.0 -8.0 -6.4	42 42 25 25	PD-9.522 PD-9.522 PD-9.521 PD-9.521	