

MATERIALS AND FINISHES

BODY ZINC ALLOY
PLATED NICKEL
NOTE: ISOLATED FROM PANEL

HOUSING PLOYESTER BUTYLENE TEREPHTALATE
COLOR: BLACK

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

INSULATOR POLYPROPYLENE (94-V2)

MOUNTING POST BRASS
PLATED TIN

SOLDER TAIL BRASS WIRE
PLATED TIN

LOCKWASHER PHOSPHOR BRONZE
PLATED NICKEL

JAM NUT BRASS
PLATED NICKEL

METAL
ISOLATED FROM
PANEL




BNC JACK
INTERFACE
75 OHM

PLASTIC

1/2-28 UNEF-2A

JAM NUT

LOCKWASHER



RECOMMENDED MOUNTING HOLE
PANEL THICKNESS: 5.50(.217) MAX
RECOMMENDED MOUNTING TORQUE:
0.56 N(5 INCH-LBS) MAX

RECOMMENDED PCB
CONFIGURATION

73171-6090	73100-0067 W/O NUT AND WASHER, TRAY PACK
73171-2980	73100-0067, ONE PER BAG
73100-0067	TRAY
PART NO.	PACKAGING

PS-89675-1030	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

CHG: ADD
ISOLATION NOTE
PS WAS
73598-0051

EC NO: URF2014-0213
2013/10/07
DRWN: WIENER
2013/10/07
CHKD: SSS
2013/10/09
APPR: WIENER

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0004
3 PLACES	± .004	± .0003
2 PLACES	± .003	± .0002
1 PLACE	± .002	± .0001

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
C.M. HUNG

DATE
1993/02/01

CHECKED BY
C.M. HUNG

DATE
1993/02/01

APPROVED BY
KWH

DATE
1993/04/01

MATERIAL NO.
SEE TABLE

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

BNC JACK, R/A, PCB
RECEPTACLE, 75 OHMS
BNC-J/RA/PCB

MOLEX INCORPORATED

DOCUMENT NO.
SD-73100-0067

SHEET NO.
1 OF 1