

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0757576361](#)

Status: **Active**

Overview: [MX150™ Unshrouded Header](#)

Description: MX150 Dual Row Header, Vertical, 12 Circuits, 1.25µm Nickel (Ni) Overall, 2.50µm Minimum Select Matte Tin (Sn) Plating on Tail, 0.75µm Select Gold (Au) Contact Area, 27.77mm Mating Pin Length, 3.05mm

Documents:

[3D Model](#)


[Drawing \(PDF\)](#)

[Product Specification PS-75757-000 \(PDF\)](#)

[Product Specification PS-75757-000-001 \(PDF\)](#)

[Packaging Specification PK-36518-340 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

General

Product Family	PCB Headers
Series	75757
3D Viewer	Yes
Application	Power, Wire-to-Board
CURRENT-MAX-NUMERIC	17.0
Overview	MX150™ Unshrouded Header
PITCH-MATING-NUMERIC	3.50
Product Name	MX150
UPC	883906570712

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.493/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[75757](#) Series

Mates With

[33472](#) Dual Row MX150 Receptacles

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-36518-340
Product Specification	PS-75757-000, PS-75757-000-001
Sales Drawing	SD-75757-003-001

This document was generated on 09/06/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION