

FAIRCHILD TRANSISTORS

POWER

POWER TRANSISTORS (BY I_{Cmax} , POLARITY AND ASCENDING V_{CE0}) (Cont'd)

Item	DEVICE NO. Polarity		VCE0 V Max	hFE Min/Max	@ IC A	VCE(sat) V Max	@ IC A	fT MHz Min(Typ)	PD(Max) W TC=25°C	Package No.
	NPN	PNP								
IC = 15.0 A Max Continuous (Cont'd)										
1	2N6488	2N6491	80	20/150	5.0	1.3	5.0	5.0	75	TO-220
2	2N6577*		90	2K/20K	4.0	4.0	15	10	120	TO-3
IC = 16.0 A Max Continuous										
3	2N5629		100	25/100	8.0	1.0	10	0.5	200	TO-3
4		2N6029	100	25/100	8.0	2.0	16	1.0	200	TO-3
5	2N5630		120	20/80	8.0	1.0	10	0.5	200	TO-3
6		2N6030	120	20/80	8.0	2.0	16	1.0	200	TO-3
7	2N5631		140	15/60	8.0	1.0	10	0.5	200	TO-3
8		2N6031	140	15/60	8.0	2.0	16	1.0	200	TO-3
IC = 20.0 A Max Continuous										
9	2N3772		60	15/60	10	1.4	10	0.2	150	TO-3
10	2N5885	2N5883	60	20/100	10	1.0	15	4.0	200	TO-3
11	2N6282*	2N6285*	60	750/18K	10	2.0	10	4.0	160	TO-3
12	2N5039		75	20/100	10	1.0	10	60	140	TO-3
13	2N6283*	2N6286*	80	750/18K	10	2.0	10	4.0	160	TO-3
14	2N5886	2N5884	80	20/100	10	1.0	15	4.0	200	TO-3
15	2N5303		80	15/60	10	2.0	20	2.0	200	TO-3
16	2N5038		90	20/100	12	1.0	12	60	140	TO-3
17	2N6284*	2N6287*	100	750/18K	10	2.0	10	4.0	160	TO-3
IC = 30.0 A Max Continuous										
18	2N3771		40	15/60	15	2.0	15	0.2	150	TO-3
19		2N4398	40	15/60	15	1.0	15	4.0	200	TO-3
20	2N5301		40	15/60	15	2.0	20	2.0	200	TO-3
21		2N4399	60	15/60	15	1.0	15	4.0	200	TO-3
22	2N5302		60	15/60	15	2.0	20	2.0	200	TO-3
23	SE9306	SE9406	60	1000/-	10	2.0	10	4.0	160	TO-3
24	SE9307	SE9407	80	1000/-	10	2.0	10	4.0	160	TO-3
25	MJ802	MJ4502	90	25/100	7.5	0.8	7.5	2.0	200	TO-3
26	SE9308	SE9408	100	1000/-	10	2.0	10	4.0	160	TO-3

*Darlington