

2 W DC-DC CONVERTER

Type	V _{in}	V _{out}	I _{out}
GS2T5-12	5 V	12 V	200 mA

DESCRIPTION

The GS2T5-12 is a 2.4W DC-DC converter designed to provide an isolated 12V/200mA power source.

The module operates from a 5V input source and features continuous short-circuit protection.


An input filter minimizes the reflected input current.



ELECTRICAL CHARACTERISTICS (T_{amb.} = 25° C unless otherwise specified)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V _i	Input Voltage	V _o = 12V I _o = 0 to 200mA	4.5	5	5.5	V
I _{ir}	Input Reflected Current	V _i = 5V V _o = 12V I _o = 200mA		20	30	mApp
V _o	Output Voltage	V _i = 4.5 to 5.5V I _o = 0 to 200mA	11.4	12.0	12.6	V
V _{or}	Output Ripple Voltage	V _i = 5V I _o = 200mA		5	10	mVrms
δV _o	Line Regulation	V _i = 4.5 to 5.5 I _o = 200mA			10	mV
δV _o	Load Regulation	V _i = 5V I _o = 50 to 200mA			10	mV
I _o	Output Current	V _i = 4.5 to 5.5V V _o = 12V	50		200	mA
V _{is}	Isolation Voltage		2500			Vdc
η	Efficiency	V _i = 5V I _o = 200mA	65	70		%
T _{op}	Operating Ambient Temperature Range		0		+60	°C
T _{stg}	Storage Temperature Range		-40		+85	°C

CONNECTION DIAGRAM AND MECHANICAL DATA



Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

© 1994 SGS-THOMSON Microelectronics – All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A.