

Sounders PATROL series 110 / 120 dB(A) PA 10 / PA 20



PATROL - the new generation of sounders.

Three dimensional innovation;

- safe; an incorrect installation is virtually impossible
- easy; significantly shorter assembly and installation times
- economical; extremely high efficiency and good penetration of acoustical obstacles significantly reduce the required number of sounders

PA 10



max. signal
reception range

PA 20



max. signal
reception range



Protection
system



Operating
temperature



Acoustic
penetration



EN
54-3



VdS




UL

Electrical data	PA 10		
Rated voltage	95 – 265 V AC	24 V AC	10 – 60 V DC
Rated frequency	50 / 60 Hz	50 / 60 Hz	
Operating range	95 – 265 V	20 – 30 V	10 – 60 V
Nominal current consumption	20 – 115 mA	250 – 900 mA	60 – 485 mA
Electrical data	PA 20		
Rated voltage	95 – 265 V AC	24 V AC	10 – 60 V DC
Rated frequency	50 / 60 Hz	50 / 60 Hz	
Operating range	95 – 265 V	20 – 30 V	10 – 60 V
Nominal current consumption ¹	75 – 330 mA	500 – 1 800 mA	120 – 880 mA

¹ power consumption dependent on operating voltage

Mechanical data	PA 10	PA 20
Sound pressure level	110 dB (A)	120 dB (A)
Sound level reduction	max. - 12 dB via potentiometer	
Alarm tones	80 (see tone table page 140/141)	
Duty cycle	100%	
Operating temperature	- 40 °C ... + 55 °C	
Storage temperature	- 40 °C ... + 70 °C	
Relative humidity	90%	
Protection system according to EN 60529	IP 66	
Protection class	II	
Material	PC / ABS blend	
Colour	similar to RAL 3000 (flame red) / RAL 7035 (light grey) / RAL 9003 (signal white)	
Cable entry	5 x M20 knock-outs on side, 1 knock-out on back	
Integrated seal with cable entry	6 – 13 mm (feed-through grommet)	
Connecting terminals	2.5 mm² fine wire with cable end sleeve, AWG 16	
Weight	AC	1 060 g
	DC	1 050 g

Dimensions



Ordering details

Article numbers		PA 10			PA 20		
Version	Rated voltage	95-265 V AC	24 V AC	10-60 V DC	95-265 V AC	24 V AC	10-60 V DC
Standard	housing red	233 60 64 0 000	233 60 30 0 000	233 60 63 0 000	233 70 64 0 000	233 70 30 0 000	233 70 63 0 000
GL	housing red	233 60 64 0 001	233 60 30 0 001	233 60 63 0 001	233 70 64 0 001	233 70 30 0 001	233 70 63 0 001
Standard	housing grey	233 60 64 0 055	233 60 30 0 055	233 60 63 0 055	233 70 64 0 055	233 70 30 0 055	233 70 63 0 055
GL	housing grey	233 60 64 0 056	233 60 30 0 056	233 60 63 0 056	233 70 64 0 056	233 70 30 0 056	233 70 63 0 056

Article numbers for other voltages and versions on request

Options / Accessories



Enclo-
sure
fitting



Surface
gasket



Tamper-
proof
sealing



Panel
mount-
ing kit



SSM
(only for 24 V DC)





















See page 141 for further information





















Conformity to standards

The acoustic parameters conform to the European standard DIN EN ISO 7731;
“Ergonomic – alarm signals for public areas and workplaces – acoustic alarm signals”.


The requirement for an acoustic alarm signal can be found in the harmonised standards:
EN 60204-1 Electrical equipment of machines
EN 60825-1 Radiation safety of laser devices, identical to IEC 825 and DIN-VDE 0837




Tone table PA 1 / PA 5 / PA 10 / PA 20

Basic tone no.	Description	
1	no tone	
2	Sawtooth, DIN tone 33404-3 Germany (emergency signal), PFEER PTAP	1200 Hz 1 s  [EN54-3]
9	Slow whoop, fire alarm, UK BS5839-1	970 Hz 1 s 
11	Interrupted tone (fast)	970 Hz 20 ms 
13	Interrupted tone	800 Hz 
15	Slow whoop, evacuation alarm Netherlands NEN 2575	900 Hz 0,3 s 
16	Slow whoop, Australian evacuation alarm AS2220	1200 Hz 3,75 s  [EN54-3]
18	Slow whoop, NFPA	700 Hz 0,6 s 
22	Pulsating tone, Australien alert AS1670, ISO8201	1200 Hz 0,5 s 
23	Siren	2400 Hz 3 s 
24	Siren	500 Hz 3 s 
25	Siren	300 Hz 3 s 
26	Pulsating tone, industrial alarm Germany	1000 Hz 10 s 
27	Sweeping	2900 Hz 0,5 s 
29	Sweeping (fast)	2400 Hz 10 ms 
30	Sweeping	2900 Hz 70 ms 
31	Sweeping, France NFC48-265	1600 Hz 1 s 
33	Sweeping (medium), UK BS5839-1	1400 Hz 0,5 s 
34	Sweeping (fast)	1000 Hz 0,5 s 
35	Sweeping (fast), UK BS5839-1	800 Hz 10 ms 
36	Sweeping	800 Hz 70 ms 
43	Sweeping	1500 Hz 1,5 s 
44	Sweeping, IMO 3d, Germany KTA3901 evacuation alarm	1200 Hz 1 s 
45	Sweeping	500 Hz 3 s 
46	Sweeping, general alarm Finland	1500 Hz 7 s 
52	Continuous tone	2400 Hz 
53	Continuous tone	2000 Hz 
54	Continuous tone, Finland (all-clear signal)	1500 Hz 
55	Continuous tone, PFEER gasalarm	1200 Hz 
56	Continuous tone	1000 Hz 
57	Continuous tone, UK BS5839-1	950 Hz 
59	Continuous tone	880 Hz
60	Continuous tone	825 Hz [EN54-3]
61	Continuous tone	800 Hz
63	Continuous tone	725 Hz
65	Continuous tone, Sweden SS031711 (all-clear signal)	660 Hz
66	Continuous tone	554 Hz
67	Continuous tone, Germany KTA3901 (all-clear signal)	500 Hz
68	Continuous tone	470 Hz

Basic tone no.	Description	
69	Continuous tone	440 Hz 
71	Continuous tone	340 Hz 
77	Interrupted tone	2400 Hz 
82	Interrupted tone, PFEER (general alarm), UK BS5839-1 (back-up alarm)	1000 Hz 
83	Interrupted tone, PFEER (general alarm)	1000 Hz 
88	Interrupted tone	950 Hz 
90	Interrupted tone	825 Hz 
91	Interrupted tone	800 Hz 
92	Interrupted tone	800 Hz 
93	Interrupted tone (fast), electromechanical horn	800 Hz 
97	Interrupted tone	725 Hz 
98	Interrupted tone, Sweden SS031711 (emergency signal)	700 Hz 
100	Interrupted tone, industrial alarm (Germany)	680 Hz 
101	Interrupted tone, Sweden SS031711 (important message (pres-mess))	660 Hz 
102	Interrupted tone, Sweden SS031711 (local warning)	660 Hz 
103	Interrupted tone, Sweden SS031711 (air raid warning)	660 Hz 
104	Interrupted tone, Sweden SS031711 (emergency signal)	660 Hz  [EN54-3]
107	Interrupted tone, Germany KTA3901 (evacuation alarm)	500 Hz 
109	Interrupted tone, Australia AS2220, AS1610, AS1670	420 Hz 
110	Interrupted tone, (fast variable), bell	1450 Hz 
111	Interrupted tone, ISO8201 (emergency evacuation signal), USA (evacuation alarm)	470 Hz 
112	Interrupted tone, ISO8201 (emergency evacuation signal)	950 Hz 
113	Interrupted tone, ISO8201 (emergency evacuation signal), sweeping	2850 Hz 
115	Interrupted tone, IMO (telephone call)	950 Hz 
116	Interrupted tone, IMO (leave ship)	950 Hz 
117	Interrupted tone, IMO SOLAS III/50 + SOLAS III/6.4 (general alarm)	825 Hz 
122	Alternating tone	2900 Hz 
123	Alternating tone	2900 Hz 
124	Alternating tone, Singapore	2000 Hz 
125	Alternating tone	1400 Hz 
128	Alternating tone	1025 Hz 
130	Alternating tone, UK BS5839-1 (fire alarm)	1000 Hz 
131	Alternating tone, UK BS5839-1 (fire alarm, railway crossing)	1000 Hz  [EN54-3]
135	Alternating tone, UK BS5839-1 (fire alarm, increased urgency - railway crossing)	1000 Hz 
142	Alternating tone	900 Hz 

Tone table PA 1 / PA 5 / PA 10 / PA 20

Basic tone no.	Description	
143	Alternating tone, industrial alarm (Germany)	660 Hz 
144	Alternating tone	650 Hz 
146	Alternating tone, France NFS 32-001 (fire alarm)	554 Hz  [EN54-3]

Basic tone no.	Description	
147	Alternating tone, Sweden SS031711	554 Hz 
148	Alternating tone, Sweden SS031711	554 Hz 
152	Alternating tone (two tone chime)	800 Hz 

Control of the tones

Tone selection switch/DIP-Switch (setting of basic tone)							External tone selection			Tone selection switch/DIP-Switch (setting of basic tone)							External tone selection		
1	2	3	4	5	6	Basic tone no.	C1	C2	C1+C2	1	2	3	4	5	6	Basic tone no.	C1	C2	C1+C2
							Tone no.										Tone no.		
						1	2	88	57						ON	71	131	52	93
						2 *	128	112	57	ON					ON	77	61	52	122
	ON					2	26	100	93		ON				ON	82	131	52	83
ON	ON					2	61	131	112	ON	ON				ON	83	56	2	82
		ON				9	57	11	82			ON			ON	88	2	57	128
ON		ON				15	131	52	112	ON		ON			ON	90	131	52	125
	ON	ON				16	109	52	56		ON	ON			ON	91	30	52	110
ON	ON	ON				18	111	57	68	ON	ON	ON			ON	92	33	52	57
			ON			22	16	109	68				ON		ON	93	2	128	57
ON			ON			23	131	52	112	ON			ON		ON	97	2	63	93
	ON		ON			24	131	52	131		ON		ON		ON	100	131	52	125
ON	ON		ON			25	131	52	92	ON	ON		ON		ON	101	98	102	65
		ON	ON			26	2	100	93			ON	ON		ON	103	131	65	147
ON		ON	ON			27	123	52	92	ON		ON	ON		ON	104	103	65	101
	ON	ON				29	35	52	61		ON	ON	ON		ON	109	16	52	22
ON	ON	ON				30	27	52	77	ON	ON	ON	ON		ON	110	131	61	91
				ON		31	131	52	57					ON	ON	112	2	57	128
ON				ON		33	30	52	35	ON				ON	ON	113	52	123	104
	ON			ON		34	35	52	93		ON			ON	ON	115	117	116	44
ON	ON			ON		35	27	52	110	ON	ON			ON	ON	116	117	93	125
		ON		ON		36	146	67	57			ON			ON	117	93	116	125
ON		ON		ON		43	131	52	91	ON		ON			ON	123	27	52	77
	ON	ON		ON		45	2	57	93		ON	ON			ON	124	53	83	2
ON	ON	ON		ON		52	15	65	82	ON	ON	ON			ON	130	2	107	67
			ON	ON		54	46	54	131				ON	ON	ON	131	2	112	57
ON			ON	ON		55	131	52	128	ON			ON	ON	ON	135	16	56	109
	ON		ON	ON		56	82	35	33		ON			ON	ON	142	2	54	88
ON	ON		ON	ON		59	143	59	101	ON	ON			ON	ON	143	59	93	33
			ON	ON		60	131	52	125			ON	ON		ON	144	110	61	2
ON		ON	ON	ON		65	131	52	93	ON	ON		ON	ON	ON	146	31	67	57
	ON	ON	ON	ON		66	110	52	107			ON	ON	ON	ON	148	131	52	92
ON	ON	ON	ON	ON		69	131	52	110	ON	ON	ON	ON	ON	ON	152	110	61	13

* factory setting

Accessories

Ordering details

Article numbers		PA 1	PA 5	PA 10 / PA 20
Enclosure fitting	For connection (daisy-chaining) of several sounders of the PATROL series	283 00 00 0 003		
Surface gasket	Sealing of the sounder installation surface when, e.g. cable entry is executed from the back.	283 00 00 0 004	283 00 00 0 005	283 00 00 0 006
Tamper-proof sealing (pack of 4)	Anti-tamper sealing for fasteners of the PATROL devices after installation in order to prevent manipulation of the devices.	283 00 00 0 002		
Panel mount installation kit PATROL	The PATROL devices are also suitable for panel mounting. This kit consists of a plug connector for the electrical contact, as well as all installation materials.	283 00 00 0 007	283 00 00 0 008	283 00 00 0 009