


Field effect rectifier

Datasheet - production data



Description

This single rectifier is based on a proprietary technology, enabling to achieve the best in class V_F/I_R trade-off for a given silicon surface.

Packaged in PowerFLAT™ 5x6, this device is intended to be used in rectification and freewheeling operations in switch-mode power supplies.

Table 1: Device summary

Symbol	Value
$I_{F(AV)}$	20 A
V_{RRM}	60 V
T_J (max.)	+150 °C
V_F (typ.)	350 mV

Features

- ST proprietary process
- Stable leakage current over reverse voltage
- Low forward voltage drop
- High frequency operation



TM: PowerFLAT is a trademark of STMicroelectronics

1 Characteristics

Table 2: Absolute ratings (limiting values at 25 °C, unless otherwise specified, anode terminals short circuited)

Symbol	Parameter		Value	Unit
V_{RRM}	Repetitive peak reverse voltage		60	V
$I_{F(RMS)}$	Forward rms current		45	A
$I_{F(AV)}$	Average forward current $\delta = 0.5$, square wave	$T_C = 115\text{ °C}$	20	A
I_{FSM}	Surge non repetitive forward current	$t_p = 10\text{ ms}$ sinusoidal	180	A
T_{stg}	Storage temperature range		-65 to +175	°C
T_j	Maximum operating junction temperature ⁽¹⁾		+150	°C

Notes:

⁽¹⁾ $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 3: Thermal resistance parameters

Symbol	Parameter	Value	Unit
$R_{th(j-c)}$	Junction to case	2.6	°C/W

Table 4: Static electrical characteristics, anode terminals short circuited

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25\text{ °C}$	$V_R = V_{RRM}$	-		800	μA
		$T_j = 125\text{ °C}$		-	30	70	mA
$V_F^{(2)}$	Forward voltage drop	$T_j = 25\text{ °C}$	$I_F = 10\text{ A}$	-	0.380	0.425	V
		$T_j = 125\text{ °C}$		-	0.350	0.400	
		$T_j = 25\text{ °C}$	$I_F = 20\text{ A}$	-	0.465	0.510	
		$T_j = 125\text{ °C}$		-	0.465	0.505	

Notes:

⁽¹⁾Pulse test: $t_p = 5\text{ ms}$, $\delta < 2\%$

⁽²⁾Pulse test: $t_p = 380\text{ μs}$, $\delta < 2\%$

To evaluate the conduction losses use the following equation:

$$P = 0.295 \times I_{F(AV)} + 0.0105 I_{F(RMS)}^2$$

1.1 Characteristics (curves)




Figure 2: Average forward current versus ambient temperature ($\delta = 0.5$)




Figure 3: Relative variation of thermal impedance junction to case versus pulse duration




Figure 4: Reverse leakage current versus reverse voltage applied (typical values)




Figure 5: Junction capacitance versus reverse voltage applied (typical values)






Figure 6: Forward voltage drop versus forward current (typical values)





2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

- Epoxy meets UL 94,V0
- Cooling method: by conduction (C)

2.1 PowerFLAT™ 5x6 8L package information

Figure 8: PowerFLAT™ 5x6 8L package outline





Table 5: PowerFLAT™ 5x6 8L mechanical data

Ref	Dim.					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.80		1.00	0.031		0.039
b	0.30		0.50	0.011		0.019
c		0.25			0.10	
D			5.10			0.201
D2	3.91		4.11	0.153		0.162
e		1.27			0.05	
E	5.90		6.10	0.232		0.240
E2	3.34		3.54	0.131		0.139
K	1.10		1.575	0.043		0.062
L	0.50		0.80	0.019		0.031
L1	0.06		0.20	0.002		0.008
L2			0.10			0.004

Figure 9: PowerFLAT™ 5x6 8L recommended footprint (dimensions are in mm)



3 Ordering information

Table 6: Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
FERD20U60DJFD-TR	FD20U60	PowerFLAT 5x6	0.9 g	3000	Tape and reel

4 Revision history

Table 7: Document revision history

Date	Revision	Changes
11-Feb-2015	1	Initial release.
27-Sep-2017	2	Updated description in cover page. Minor text changes.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics – All rights reserved