


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn99.25%, Cu0.7%, Ni0.05%	Yes	Yes

more than you expect

Midcom





LOT CODE & DATE CODE

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	2.733 ohms max.
D.C. RESISTANCE	5-4 @20°C	1.145 ohms max.
D.C. RESISTANCE	S-F @20°C	0.095 ohms max.
INDUCTANCE	3-1 10kHz, 1.0VAC, Ls	0.72mH ±10%
DIELECTRIC	1-S tie(3+4), 3000VAC, 1 second	-
TURNS RATIO	(3-1):(5-4)	2.8:1, ±2%
TURNS RATIO	(3-1):(S-F)	13.0:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
02	12/12	Method: Tray		Angles: ±1°	TRANSFORMER	750341657
01	11/12	PKG-0027		Decimals: ±.005 [.13]		
00	10/12	www.we-online.com/midcom		Fractions: ±1/64		
		SEE REVISION SHEET FOR REVISION LEVEL		Footprint: ±.001 [.03]		
				This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341657	SPECIFICATION SHEET 1 OF 1

