




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
CM	52		F	REV & REDWN PER EC 0L30-0146-97	5-19-97	TB




1. WIRE RANGE: 0.2 - 0.6 MM² (24 - 20 AWG)
2. INSULATION RANGE: 1.52 - 2.29
3. 0.00203 MIN MATTE TIN PLATING OVER ALL.




FITS 1.47 DIAMETER PIN

SECTION A-A



SECTION B-B



SECTION C-C

1.359	.0535	2.16	.085	3.94	.155	-	-
1.14	.045	1.96	.077	3.18	.125	-	-
0.51	.020	1.91	.075	2.82	.111	-	-
0.25	.010	1.52	.060	2.79	.110	10.03	.395
0.13	.005	1.486	.0585	2.41	.095	6.55	.258
0.00203	.000080	1.47	.058	2.29	.090	6.40	.252
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

	0.25 BE CU	60940-2
PRE-TIN	0.25 PH BRZ	60940-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 5-19-97	AMP Incorporated Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK R. SWING 5-19-97				
		APVD A. BEDDICK 8-08-97	NAME RECEPTACLE, .058 DIAMETER, 24-20 AWG, .060-.090 INSULATION, P.C. CONTACT			
		PRODUCT SPEC 108-1025	SIZE A2			
MATERIAL SEE TABLE		FINISH SEE TABLE	APPLICATION SPEC 114-1008		CAGE CODE 00779	
			WEIGHT -		DRAWING NO 60940	
			CUSTOMER DRAWING		RESTRICTED TO -	
			SCALE 10:1		SHEET 1 OF 1	
					REV F	