











Package	Part No.	Chip		Lens Appearance	Absolute Maximum Ratings			Electro-optical Data(At 2mA)			Viewing Angle 2 θ 1/2 (deg)	Drawing No.	
		Material/ Emitted Color	Peak Wave Length λ p (nm)		Δ λ (nm)	Pd (mw)	If (mA)	Vf (V)		Iv (mcd)			
								Typ	Max				Typ.
T-1 Standard 1.0" Lead 3 ϕ	BL-B5131-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	1.0	40	L-144	
	BL-B4531-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	6.0			
	BL-B2131-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	6.0			
	BL-BX1131-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.8	2.2	8.0			
	BL-B3131-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	4.0			
	BL-B4131-L	GaAsP/GaP/ Orange	635	Orange Diffused	45	10	5	1.8	2.2	6.0			
	BL-B4331-L	GaAsP/GaP/ Orange	635	Water Clear	45	10	5	1.8	2.2	12.0	30		
T-1 Standard 1.0" Lead 3 ϕ	BL-B5141-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	1.0	40	L-145	
	BL-B4541-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	6.0			
	BL-B2141-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	6.0			
	BL-BX1141-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.8	2.2	8.0			
	BL-B3141-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	4.0			
	BL-B4141-L	GaAsP/GaP/ Orange	635	Orange Diffused	45	10	5	1.8	2.2	6.0			
	BL-B4341-L	GaAsP/GaP/ Orange	635	Water Clear	45	10	5	1.8	2.2	12.0	30		
T-1 Low Profile 1.0"Lead 5 ϕ	BL-B4531E-L	GaAsP/GaP/ Hi-Eff Red	635	Red Diffused	45	10	5	1.8	2.2	30.0	45	L-146	
	BL-B2131E-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	30.0			
	BL-B3131E-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	20.0			
	BL-B2431E-L	GaP/GaP/ Green	568	Green Trans	30	10	5	1.9	2.2	65.0	40		
	BL-B3431E-L	GaAsP/GaP/ Yellow	585	Yellow Trans	35	10	5	1.9	2.2	55.0			
	BL-B2331E-L	GaP/GaP/ Green	568	Water Clear	30	10	5	1.9	2.2	65.0			
	BL-B3331E-L	GaAsP/GaP/ Yellow	585		35	10	5	1.9	2.2	55.0			
T-1 Low Profile 1.0"Lead 5 ϕ	BL-B4531K-L	GaAsP/GaP/ Hi-Eff Red	635	Red Diffused	45	10	5	1.8	2.2	30.0	45	L-147	
	BL-B2131K-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	30.0			
	BL-B3131K-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	20.0			
	BL-B2431K-L	GaP/GaP/ Green	568	Green Trans	30	10	5	1.9	2.2	65.0	40		
	BL-B3431K-L	GaAsP/GaP/ Yellow	585	Yellow Trans	35	10	5	1.9	2.2	55.0			
	BL-B2331K-L	GaP/GaP/ Green	568	Water Clear	30	10	5	1.9	2.2	65.0			
	BL-B3331K-L	GaAsP/GaP/ Yellow	585		35	10	5	1.9	2.2	55.0			
T-13/4 Standard 1.0" Lead 5 ϕ	BL-B5134-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	3.5	35	L-148	
	BL-B4534-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	4.5			
	BL-B2134-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	4.5			
	BL-BX1134-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.8	2.2	5.0			
	BL-B3134-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	4.0			
	BL-B4134-L	GaAsP/GaP/ Orange	635	Orange Diffused	45	10	5	1.8	2.2	5.0			
	BL-B4334-L	GaAsP/GaP/ Orange	635	Water Clear	45	10	5	1.8	2.2	12.0	12		
T-13/4 Standard 1.0" Lead 5 ϕ	BL-B5134-1-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	2.5	40	L-149	
	BL-B4534-1-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	3.5			
	BL-B2134-1-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	3.5			
	BL-BX1134-1-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.9	2.2	4.0			
	BL-B3134-1-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	3.0			
	BL-B4134-1-L	GaAsP/GaP/Orange	635	Orange Diffused	45	10	5	1.8	2.2	3.5			
	BL-B4334-1-L	GaAsP/GaP/ Orange	635	Water Clear	45	10	5	1.8	2.2	10.0	20		
T-13/4 Standard 1.0" Lead 5 ϕ	BL-B5134G-1-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	2.0	45	L-150	
	BL-B4534G-1-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	3.0			
	BL-B2134G-1-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	3.0			
	BL-BX1134G-1-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.9	2.2	4.0			
	BL-B3134G-1-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	2.0			
	BL-B4334G-1-L	GaAsP/GaP/ Orange	635	Water Clear	45	10	5	1.8	2.2	8.0	25		
T-13/4 Flangeless 1.0" Lead 5 ϕ	BL-B5134N-1-L	GaP/GaP/ Bright Red	700	Red Diffused	90	10	5	1.9	2.2	2.0	45	L-151	
	BL-B4534N-1-L	GaAsP/GaP/ Hi-Eff Red	635		45	10	5	1.8	2.2	3.0			
	BL-B2134N-1-L	GaP/GaP/ Green	568	Green Diffused	30	10	5	1.9	2.2	3.0			
	BL-BX1134N-1-L	GaP/GaP/ Hi-Eff Green	568		30	10	5	1.8	2.2	3.5			
	BL-B3134N-1-L	GaAsP/GaP/ Yellow	585	Yellow Diffused	35	10	5	1.9	2.2	3.0			

Remark : 1.Hi-Eff Red / High-Efficiency Red.

2.Trans / Transparent.

3.2 θ 1/2 The off-axis angle at which the luminous intensity is half the axial luminous intensity.



L-144 BL-Bxx31-L Series 	L-145 BL-Bxx41-L Series 
L-146 BL-Bxx31E-L Series 	L-147 BL-Bxx31K-L Series 
L-148 BL-Bxx34-L Series 	L-149 BL-Bxx34-1-L Series 
L-150 BL-Bxx34G-1-L Series 	L-151 BL-Bxx34N-1-L Series 

Notes : 1.All Dimensions are in millimeters (inches).
2.Tolerance is $\pm 0.25\text{mm}$ (.010").