


SPECIFICATIONS

FUNCTION:
1P2T ON-ON

RATINGS:
0.5A 50VDC



CONTACT RESISTANCE:
Initial: 30mΩ Max.

INSULATION RESISTANCE:
500MΩ Min. at 500VDC

DIELECTRIC STRENGTH:
500VAC For 1 Minute

ELECTRICAL LIFE:
10,000 Cycles

APPROVALS:
ROHS LEAD FREE
COMPLIANT PROCESS COMPATIBLE



MATERIALS

UPPER BODY:
Nickel Plated Cold Rolled Steel (SPCC-SD)

LOWER BODY:
Penolite Board (SD-102C), UL94 HB

ACTUATOR:
Polyoxymethylene (POM)
(TYSTRON POM7520), UL94 HB

SPRING:
Steel

CONTACT:
Silver Plated Brass (C2680R)

TERMINALS:
Silver Plated Brass (C2680R)

OTHER:
Red Terminal Solder (AKS881R)

COLORS

BODY:
Metallic

ACTUATOR:
Black

