



LOC	DIST	REVISIONS				
CM	0	P	LTR	DESCRIPTION	DATE	APVD
		M1		REVISED PER ECR-16-010553	07AUG2017	SG



- 1
- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 2
- 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.
- 3
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 4
- 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 5
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57 THICK BOARD
TOLERANCES NON-ACCUMULATIVE

BRASS, TIN	4	NYLON, UL94V-0	BLACK	5-770170-0
BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770170-1
BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770170-0
BRASS, GOLD	3	NYLON, UL94V-0	WHITE	770170-2
BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770170-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER	08JUN05	 TE Connectivity	
		CHK R JONES	28JUL2003		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSEMBLY, 3 CKT, MINI UNIVERSAL MATE-N-LOK —	
		APVD R JONES	28JUL2003		
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		SIZE A2		CAGE CODE 00779	DRAWING NO C=770170
MATERIAL —		FINISH —		WEIGHT —	
CUSTOMER DRAWING		SCALE 1:1		SHEET 1 of 1	
				REV M1	