

# MB1505W THRU MB1510W

## Features

- Mounting Hole For #8 Screw
- High Conductivity Metal Case
- Any Mounting Position
- Case to Terminal Isolation Voltage 2500V
- Halogen free available upon request by adding suffix "-HF"
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/Rohs Compliant (Note1) ("P" Suffix designates Compliant. See ordering information)

## Maximum Ratings

- Mounting Torque: 20 in-lbs Maximum
- Operating Temperature: -55°C to +125°C
- Storage Temperature: -55°C to +150°C
- UL Recognized File # E165989

| MCC Catalog Number | Device Marking | Maximum Recurrent Peak Reverse Voltage | Maximum RMS Voltage | Maximum DC Blocking Voltage |
|--------------------|----------------|----------------------------------------|---------------------|-----------------------------|
| MB1505W            | MB1505W        | 50V                                    | 35V                 | 50V                         |
| MB151W             | MB151W         | 100V                                   | 70V                 | 100V                        |
| MB152W             | MB152W         | 200V                                   | 140V                | 200V                        |
| MB154W             | MB154W         | 400V                                   | 280V                | 400V                        |
| MB156W             | MB156W         | 600V                                   | 420V                | 600V                        |
| MB158W             | MB158W         | 800V                                   | 560V                | 800V                        |
| MB1510W            | MB1510W        | 1000V                                  | 700V                | 1000V                       |


## Electrical Characteristics @ 25°C Unless Otherwise Specified

|                                                         |             |              |                                                                 |
|---------------------------------------------------------|-------------|--------------|-----------------------------------------------------------------|
| Average Forward Current                                 | $I_{F(AV)}$ | 15.0A        | $T_C = 55^\circ\text{C}$                                        |
| Peak Forward Surge Current                              | $I_{FSM}$   | 300A         | 8.3ms, half sine                                                |
| Maximum Forward Voltage Drop Per Element                | $V_F$       | 1.2V         | $I_{FM} = 7.5\text{A}$ per element;<br>$T_J = 25^\circ\text{C}$ |
| Maximum DC Reverse Current At Rated DC Blocking Voltage | $I_R$       | 10μA<br>1 mA | $T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$           |

Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7

## 15 Amp Single Phase Bridge Rectifier 50 to 1000 Volts


### MB-35W



| DIM | INCHES |       | MM    |       | NOTE    |
|-----|--------|-------|-------|-------|---------|
|     | MIN    | MAX   | MIN   | MAX   |         |
| A   | 1.115  | 1.135 | 28.33 | 28.83 |         |
| B   | .427   | .447  | 10.85 | 11.35 |         |
| C   | .774   | ----- | 19.65 | ----- |         |
| D   | .673   | .752  | 17.10 | 19.10 |         |
| E   | .038   | .042  | 0.96  | 1.07  | 4PL/TYP |
| G   | .193   | ---   | 4.90  | ---   | Ø       |
| H   | .429   | .469  | 10.90 | 11.90 |         |


## MB1505W thru MB1510W

Figure 1  
Typical Forward Characteristics




Instantaneous Forward Current - Amperes versus  
Instantaneous Forward Voltage - Volts

Figure 3  
Forward Derating Curve




Average Forward Rectified Current - Amperes versus  
Case Temperature -  $^\circ\text{C}$

Figure 2  
Typical Reverse Characteristics



Instantaneous Reverse Leakage Current - MicroAmperes versus  
Percent Of Rated Peak Reverse Voltage - Volts

Figure 4  
Peak Forward Surge Current



Peak Forward Surge Current - Amperes versus  
Number Of Cycles At 60Hz - Cycles



TM

Micro Commercial Components

Ordering Information

|                  |                 |
|------------------|-----------------|
| Device           | Packing         |
| (Part Number)-BP | Bulk;400Pcs/Ctn |

Note : Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

\*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

\*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

\*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.