





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		G	REVISED PER ECR-13-008204	10DEC2013	KH	TM



- 1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2 WIRE RANGE: 0.2-1mm² [24-18 AWG].
INSULATION RANGE: 1.02-2.54 [.040-.100] DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 SUPERSEDED BY 1-770252-0



5	GOLD 4	0.30 [.012]	BRASS	1-770252-0
	GOLD 1	0.30 [.012]	BRASS	-770252-2-
	PRE-TIN	0.30 [.012]	BRASS	770252-1
	FINISH	MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 30SEP04	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C.JONES 30SEP04				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.JONES 30SEP04	NAME			
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 0°30'		PRODUCT SPEC	PIN, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II			
MATERIAL		APPLICATION SPEC	-			
FINISH		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=770252	RESTRICTED TO -
-		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1	REV G	