

### Description

The 9FGV0241 is a 2-output very low power frequency generator for PCIe Gen 1, 2, 3 and 4 applications with integrated output terminations providing  $Z_o = 100\Omega$ . The device has 2 output enables for clock management and supports 2 different spread spectrum levels in addition to spread off.

### Recommended Application

PCIe Gen1-4 clock generation for Riser Cards, Storage, Networking, JBOD, Communications, Access Points

### Output Features

- 2 – 0.7V low-power HCSL-compatible (LP-HCSL) DIF pairs with  $Z_o = 100\Omega$
- 1 – 1.8V LVCMOS REF output w/Wake-On-LAN (WOL) support


### Key Specifications

- DIF cycle-to-cycle jitter <50ps
- DIF output-to-output skew <50ps
- DIF phase jitter is PCIe Gen1-2-3-4 compliant
- REF phase jitter is < 1.5ps RMS


### Features/Benefits

- Integrated terminations provide  $100\Omega$  differential  $Z_o$ ; reduced component count and board space
- 1.8V operation; reduced power consumption
- OE# pins; support DIF power management
- LP-HCSL differential clock outputs; reduced power and board space
- Programmable Slew rate for each output; allows tuning for various line lengths
- Programmable output amplitude; allows tuning for various application environments
- DIF outputs blocked until PLL is locked; clean system start-up
- Selectable 0%, -0.25% or -0.5% spread on DIF outputs; reduces EMI
- External 25MHz crystal; supports tight ppm with 0 ppm synthesis error
- Configuration can be accomplished with strapping pins; SMBus interface not required for device control
- 3.3V tolerant SMBus interface works with legacy controllers
- Space saving 4 x 4 mm 24-VFQFPN; minimal board space

### Block Diagram



## Pin Configuration



### 24-pin VFQFPN, 4x4 mm, 0.5mm pitch

^ prefix indicates internal 120KOhm pull up resistor  
v prefix indicates internal 120KOhm pull down resistor

## SMBus Address Selection Table

|                                                   | SADR | Address | + Read/Write Bit |
|---------------------------------------------------|------|---------|------------------|
| State of SADR on first application of CKPWRGD_PD# | 0    | 1101000 | x                |
|                                                   | 1    | 1101010 | x                |

## Power Management Table

| CKPWRGD_PD# | SMBus OE bit | DIFx     |           | REF               |
|-------------|--------------|----------|-----------|-------------------|
|             |              | True O/P | Comp. O/P |                   |
| 0           | X            | Low      | Low       | Hi-Z <sup>1</sup> |
| 1           | 1            | Running  | Running   | Running           |
| 1           | 0            | Low      | Low       | Low               |

1. REF is Hi-Z until the 1st assertion of CKPWRGD\_PD# high. After this, when CKPWRGD\_PD# is low, REF is Low.

## Power Connections


| Pin Number |       | Description   |
|------------|-------|---------------|
| VDD        | GND   |               |
| 3          | 5,24  | XTAL, REF     |
| 7          | 6     | Digital Power |
| 11,20      | 10,21 | DIF outputs   |
| 16         | 15    | PLL Analog    |

## Pin Descriptions


| Pin# | Pin Name     | Type        | Pin Description                                                                                                                                                                                           |
|------|--------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1    | X1_25        | IN          | Crystal input, Nominally 25.00MHz.                                                                                                                                                                        |
| 2    | X2           | OUT         | Crystal output.                                                                                                                                                                                           |
| 3    | VDDXTAL1.8   | PWR         | Power supply for XTAL, nominal 1.8V                                                                                                                                                                       |
| 4    | vSADR/REF1.8 | LATCHED I/O | Latch to select SMBus Address/1.8V LVCMOS copy of X1 pin.                                                                                                                                                 |
| 5    | GNDREF       | GND         | Ground pin for the REF outputs.                                                                                                                                                                           |
| 6    | GNDDIG       | GND         | Ground pin for digital circuitry                                                                                                                                                                          |
| 7    | VDDDIG1.8    | PWR         | 1.8V digital power (dirty power)                                                                                                                                                                          |
| 8    | SCLK_3.3     | IN          | Clock pin of SMBus circuitry, 3.3V tolerant.                                                                                                                                                              |
| 9    | SDATA_3.3    | I/O         | Data pin for SMBus circuitry, 3.3V tolerant.                                                                                                                                                              |
| 10   | GND          | GND         | Ground pin.                                                                                                                                                                                               |
| 11   | VDD1.8       | PWR         | Power supply, nominal 1.8V                                                                                                                                                                                |
| 12   | vOE0#        | IN          | Active low input for enabling DIF pair 0. This pin has an internal pull-down.<br>1 =disable outputs, 0 = enable outputs                                                                                   |
| 13   | DIF0         | OUT         | Differential true clock output                                                                                                                                                                            |
| 14   | DIF0#        | OUT         | Differential Complementary clock output                                                                                                                                                                   |
| 15   | GND          | GND         | Ground pin for the PLL core.                                                                                                                                                                              |
| 16   | VDDA1.8      | PWR         | 1.8V power for the PLL core.                                                                                                                                                                              |
| 17   | DIF1         | OUT         | Differential true clock output                                                                                                                                                                            |
| 18   | DIF1#        | OUT         | Differential Complementary clock output                                                                                                                                                                   |
| 19   | vOE1#        | IN          | Active low input for enabling DIF pair 1. This pin has an internal pull-down.<br>1 =disable outputs, 0 = enable outputs                                                                                   |
| 20   | VDD1.8       | PWR         | Power supply, nominal 1.8V                                                                                                                                                                                |
| 21   | GND          | GND         | Ground pin.                                                                                                                                                                                               |
| 22   | ^CKPWRGD_PD# | IN          | Input notifies device to sample latched inputs and start up on first high assertion. Low enters Power Down Mode, subsequent high assertions exit Power Down Mode. This pin has internal pull-up resistor. |
| 23   | vSS_EN_tri   | LATCHED IN  | Latched select input to select spread spectrum amount at initial power up :<br>1 = -0.5% spread, M = -0.25%, 0 = Spread Off                                                                               |
| 24   | GNDXTAL      | GND         | GND for XTAL                                                                                                                                                                                              |

## Test Loads


Low-Power HCSL Differential Output Test Load



REF Output Test Load



## Alternate Terminations



Driving LVDS inputs with the 9FGV0241

| Component | Value                    |                                    | Note |
|-----------|--------------------------|------------------------------------|------|
|           | Receiver has termination | Receiver does not have termination |      |
| R7a, R7b  | 10K ohm                  | 140 ohm                            |      |
| R8a, R8b  | 5.6K ohm                 | 75 ohm                             |      |
| $C_c$     | 0.1 uF                   | 0.1 uF                             |      |
| Vcm       | 1.2 volts                | 1.2 volts                          |      |

## Absolute Maximum Ratings

Stresses above the ratings listed below can cause permanent damage to the 9FGV0241. These ratings, which are standard values for IDT commercially rated parts, are stress ratings only. Functional operation of the device at these or any other conditions above those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods can affect product reliability. Electrical parameters are guaranteed only over the recommended operating temperature range.

| PARAMETER                 | SYMBOL             | CONDITIONS                | MIN  | TYP | MAX                   | UNITS | NOTES |
|---------------------------|--------------------|---------------------------|------|-----|-----------------------|-------|-------|
| 1.8V Supply Voltage       | VDDxx              | Applies to All VDD pins   | -0.5 |     | 2.5                   | V     | 1,2   |
| Input Voltage             | V <sub>IN</sub>    |                           | -0.5 |     | V <sub>DD</sub> +0.3V | V     | 1, 3  |
| Input High Voltage, SMBus | V <sub>IHSMB</sub> | SMBus clock and data pins |      |     | 3.6V                  | V     | 1     |
| Storage Temperature       | T <sub>s</sub>     |                           | -65  |     | 150                   | °C    | 1     |
| Junction Temperature      | T <sub>j</sub>     |                           |      |     | 125                   | °C    | 1     |
| Input ESD protection      | ESD prot           | Human Body Model          | 2000 |     |                       | V     | 1     |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup>Operation under these conditions is neither implied nor guaranteed.

<sup>3</sup>Not to exceed 2.5V.

## Electrical Characteristics–Current Consumption

TA = T<sub>COM</sub> or T<sub>IND</sub>; Supply Voltage per VDD of normal operation conditions, See Test Loads for Loading Conditions

| PARAMETER                | SYMBOL              | CONDITIONS                                 | MIN | TYP | MAX | UNITS | NOTES |
|--------------------------|---------------------|--------------------------------------------|-----|-----|-----|-------|-------|
| Operating Supply Current | I <sub>DDAOP</sub>  | VDDA, PLL Mode, All outputs active @100MHz |     | 7   | 8   | mA    | 1     |
|                          | I <sub>DDOP</sub>   | VDD, All outputs active @100MHz            |     | 15  | 18  | mA    | 1     |
| Suspend Supply Current   | I <sub>DDSUSP</sub> | VDDxxx, PD# = 0, Wake-On-LAN enabled       |     | 6   | 8   | mA    | 1     |
| Powerdown Current        | I <sub>DDPD</sub>   | PD#=0                                      |     | 0.6 | 1   | mA    | 1, 2  |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup>Assuming REF is not running in power down state

## Electrical Characteristics–Output Duty Cycle, Jitter, and Skew Characteristics

TA = T<sub>COM</sub> or T<sub>IND</sub>; Supply Voltage per VDD of normal operation conditions, See Test Loads for Loading Conditions

| PARAMETER              | SYMBOL               | CONDITIONS                        | MIN | TYP | MAX | UNITS | NOTES |
|------------------------|----------------------|-----------------------------------|-----|-----|-----|-------|-------|
| Duty Cycle             | t <sub>DC</sub>      | Measured differentially, PLL Mode | 45  | 50  | 55  | %     | 1     |
| Skew, Output to Output | t <sub>sk3</sub>     | V <sub>T</sub> = 50%              |     | 34  | 50  | ps    | 1     |
| Jitter, Cycle to cycle | t <sub>jcy-cyc</sub> | PLL mode                          |     | 14  | 50  | ps    | 1,2   |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup>Measured from differential waveform

## Electrical Characteristics–Input/Supply/Common Parameters–Normal Operating Conditions

TA = T<sub>COM</sub> or T<sub>IND</sub>; Supply Voltage per VDD of normal operation conditions, See Test Loads for Loading Conditions

| PARAMETER                                        | SYMBOL              | CONDITIONS                                                                                                                                              | MIN                   | TYP  | MAX                   | UNITS  | NOTES |
|--------------------------------------------------|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|-----------------------|--------|-------|
| 1.8V Supply Voltage                              | VDD                 | Supply voltage for core, analog and single-ended LVCMOS outputs                                                                                         | 1.7                   | 1.8  | 1.9                   | V      | 1     |
| Ambient Operating Temperature                    | T <sub>COM</sub>    | Commercial range                                                                                                                                        | 0                     | 25   | 70                    | °C     | 1     |
|                                                  | T <sub>IND</sub>    | Industrial range                                                                                                                                        | -40                   | 25   | 85                    | °C     | 1     |
| Input High Voltage                               | V <sub>IH</sub>     | Single-ended inputs, except SMBus                                                                                                                       | 0.75 V <sub>DD</sub>  |      | V <sub>DD</sub> + 0.3 | V      | 1     |
| Input Mid Voltage                                | V <sub>IM</sub>     | Single-ended tri-level inputs ('_tri' suffix, if present)                                                                                               | 0.4 V <sub>DD</sub>   |      | 0.6 V <sub>DD</sub>   | V      | 1     |
| Input Low Voltage                                | V <sub>IL</sub>     | Single-ended inputs, except SMBus                                                                                                                       | -0.3                  |      | 0.25 V <sub>DD</sub>  | V      | 1     |
| Schmitt Trigger Positive Going Threshold Voltage | V <sub>T+</sub>     | Single-ended inputs, where indicated                                                                                                                    | 0.4 V <sub>DD</sub>   |      | 0.7 V <sub>DD</sub>   | V      | 1     |
| Schmitt Trigger Negative Going Threshold Voltage | V <sub>T-</sub>     | Single-ended inputs, where indicated                                                                                                                    | 0.1 V <sub>DD</sub>   |      | 0.4 V <sub>DD</sub>   | V      | 1     |
| Hysteresis Voltage                               | V <sub>H</sub>      | V <sub>T+</sub> - V <sub>T-</sub>                                                                                                                       | 0.1 V <sub>DD</sub>   |      | 0.4 V <sub>DD</sub>   | V      | 1     |
| Output High Voltage                              | V <sub>IH</sub>     | Single-ended outputs, except SMBus. I <sub>OH</sub> = -2mA                                                                                              | V <sub>DD</sub> -0.45 |      |                       | V      | 1     |
| Output Low Voltage                               | V <sub>IL</sub>     | Single-ended outputs, except SMBus. I <sub>OL</sub> = -2mA                                                                                              |                       |      | 0.45                  | V      | 1     |
| Input Current                                    | I <sub>IN</sub>     | Single-ended inputs, V <sub>IN</sub> = GND, V <sub>IN</sub> = VDD                                                                                       | -5                    |      | 5                     | uA     | 1     |
|                                                  | I <sub>INP</sub>    | Single-ended inputs<br>V <sub>IN</sub> = 0 V; Inputs with internal pull-up resistors<br>V <sub>IN</sub> = VDD; Inputs with internal pull-down resistors | -20                   |      | 20                    | uA     | 1     |
| Input Frequency                                  | F <sub>in</sub>     | XTAL, or X1 input                                                                                                                                       | 23                    | 25   | 27                    | MHz    | 1     |
| Pin Inductance                                   | L <sub>pin</sub>    |                                                                                                                                                         |                       |      | 7                     | nH     | 1     |
| Capacitance                                      | C <sub>IN</sub>     | Logic Inputs, except DIF_IN                                                                                                                             | 1.5                   |      | 5                     | pF     | 1     |
|                                                  | C <sub>OUT</sub>    | Output pin capacitance                                                                                                                                  |                       |      | 6                     | pF     | 1     |
| Clk Stabilization                                | T <sub>STAB</sub>   | From V <sub>DD</sub> Power-Up and after input clock stabilization or de-assertion of PD# to 1st clock                                                   |                       | 0.4  | 1.8                   | ms     | 1,2   |
| SS Modulation Frequency                          | f <sub>MOD</sub>    | Allowable Frequency (Triangular Modulation)                                                                                                             | 31                    | 31.6 | 32                    | kHz    | 1     |
| OE# Latency                                      | t <sub>LATOE#</sub> | DIF start after OE# assertion<br>DIF stop after OE# deassertion                                                                                         | 2                     | 3    | 4                     | clocks | 1,3   |
| Tdrive_PD#                                       | t <sub>DRVPD</sub>  | DIF output enable after PD# de-assertion                                                                                                                |                       | 4    | 300                   | us     | 1,3   |
| Tfall                                            | t <sub>F</sub>      | Fall time of single-ended control inputs                                                                                                                |                       |      | 5                     | ns     | 1,2   |
| Trise                                            | t <sub>R</sub>      | Rise time of single-ended control inputs                                                                                                                |                       |      | 5                     | ns     | 1,2   |
| SMBus Input Low Voltage                          | V <sub>ILSMB</sub>  | V <sub>DDSMB</sub> = 3.3V, see note 4 for V <sub>DDSMB</sub> < 3.3V                                                                                     |                       |      | 0.8                   | V      | 1,4   |
| SMBus Input High Voltage                         | V <sub>IHSMB</sub>  | V <sub>DDSMB</sub> = 3.3V, see note 5 for V <sub>DDSMB</sub> < 3.3V                                                                                     | 2.1                   |      | 3.6                   | V      | 1,5   |
| SMBus Output Low Voltage                         | V <sub>OLSMB</sub>  | @ I <sub>PULLUP</sub>                                                                                                                                   |                       |      | 0.4                   | V      | 1     |
| SMBus Sink Current                               | I <sub>PULLUP</sub> | @ V <sub>OL</sub>                                                                                                                                       | 4                     |      |                       | mA     | 1     |
| Nominal Bus Voltage                              | V <sub>DDSMB</sub>  |                                                                                                                                                         | 1.7                   |      | 3.6                   | V      | 1     |
| SCLK/SDATA Rise Time                             | t <sub>RSMB</sub>   | (Max V <sub>IL</sub> - 0.15) to (Min V <sub>IH</sub> + 0.15)                                                                                            |                       |      | 1000                  | ns     | 1     |
| SCLK/SDATA Fall Time                             | t <sub>FSMB</sub>   | (Min V <sub>IH</sub> + 0.15) to (Max V <sub>IL</sub> - 0.15)                                                                                            |                       |      | 300                   | ns     | 1     |
| SMBus Operating Frequency                        | f <sub>MAXSMB</sub> | Maximum SMBus operating frequency                                                                                                                       |                       |      | 400                   | kHz    | 1     |

<sup>1</sup> Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup> Control input must be monotonic from 20% to 80% of input swing.

<sup>3</sup> Time from deassertion until outputs are > 200mV.

<sup>4</sup> For V<sub>DDSMB</sub> < 3.3V, V<sub>ILSMB</sub> < = 0.35V<sub>DDSMB</sub>.

<sup>5</sup> For V<sub>DDSMB</sub> < 3.3V, V<sub>IHSMB</sub> > = 0.65V<sub>DDSMB</sub>.

## Electrical Characteristics–DIF 0.7V Low Power HCSL Outputs

TA = T<sub>COM</sub> or T<sub>IND</sub>; Supply Voltage per VDD of normal operation conditions, See Test Loads for Loading Conditions

| PARAMETER              | SYMBOL                 | CONDITIONS                                                                                            | MIN  | TYP  | MAX  | UNITS | NOTES   |
|------------------------|------------------------|-------------------------------------------------------------------------------------------------------|------|------|------|-------|---------|
| Slew rate              | Trf                    | Scope averaging on 3.0V/ns setting                                                                    | 2    | 3.1  | 4.3  | V/ns  | 1, 2, 3 |
|                        |                        | Scope averaging on 2.0V/ns setting                                                                    | 1.5  | 2.3  | 3.5  | V/ns  | 1, 2, 3 |
| Slew rate matching     | ΔTrf                   | Slew rate matching, Scope averaging on                                                                |      | 3    | 20   | %     | 1,2,4   |
| Voltage High           | V <sub>HIGH</sub>      | Statistical measurement on single-ended signal using oscilloscope math function. (Scope averaging on) | 660  | 794  | 850  | mV    | 1,7     |
| Voltage Low            | V <sub>LOW</sub>       |                                                                                                       | -150 | 21   | 150  |       | 1       |
| Max Voltage            | V <sub>max</sub>       | Measurement on single ended signal using absolute value. (Scope averaging off)                        |      | 816  | 1150 | mV    | 1       |
| Min Voltage            | V <sub>min</sub>       |                                                                                                       | -300 | -15  |      |       | 1       |
| Vswing                 | V <sub>swing</sub>     | Scope averaging off                                                                                   | 300  | 1551 |      | mV    | 1,2     |
| Crossing Voltage (abs) | V <sub>cross_abs</sub> | Scope averaging off                                                                                   | 300  | 397  | 550  | mV    | 1,5     |
| Crossing Voltage (var) | Δ-V <sub>cross</sub>   | Scope averaging off                                                                                   |      | 15   | 140  | mV    | 1,6     |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup> Measured from differential waveform

<sup>3</sup> Slew rate is measured through the V<sub>swing</sub> voltage range centered around differential 0V. This results in a +/-150mV window around differential 0V.

<sup>4</sup> Matching applies to rising edge rate for Clock and falling edge rate for Clock#. It is measured using a +/-75mV window centered on the average cross point where Clock rising meets Clock# falling. The median cross point is used to calculate the voltage thresholds the oscilloscope is to use for the edge rate calculations.

<sup>5</sup> V<sub>cross</sub> is defined as voltage where Clock = Clock# measured on a component test board and only applies to the differential rising edge (i.e. Clock rising and Clock# falling).

<sup>6</sup> The total variation of all V<sub>cross</sub> measurements in any particular system. Note that this is a subset of V<sub>cross\_min/max</sub> (V<sub>cross</sub> absolute) allowed. The intent is to limit V<sub>cross</sub> induced modulation by setting Δ-V<sub>cross</sub> to be smaller than V<sub>cross</sub> absolute.

<sup>7</sup> At default SMBus settings.

## Electrical Characteristics–Filtered Phase Jitter Parameters - PCIe Common Clocked (CC) Architectures

T<sub>AMB</sub> = over the specified operating range. Supply Voltages per normal operation conditions, See Test Loads for Loading Conditions

| SYMBOL                    | PARAMETER              | CONDITIONS                                                                                       | MIN | TYP  | MAX  | Specification Limit | UNITS    | NOTES   |
|---------------------------|------------------------|--------------------------------------------------------------------------------------------------|-----|------|------|---------------------|----------|---------|
| t <sub>jphPCIeG1-CC</sub> | Phase Jitter, PLL Mode | PCIe Gen 1                                                                                       | 21  | 25   | 35   | 86                  | ps (p-p) | 1, 2, 3 |
| t <sub>jphPCIeG2-CC</sub> |                        | PCIe Gen 2 Low Band<br>10kHz < f < 1.5MHz<br>(PLL BW of 5-16MHz, 8-16MHz, CDR = 5MHz)            | 0.9 | 0.9  | 1.1  | 3                   | ps (rms) | 1, 2    |
|                           |                        | PCIe Gen 2 High Band<br>1.5MHz < f < Nyquist (50MHz)<br>(PLL BW of 5-16MHz, 8-16MHz, CDR = 5MHz) | 1.5 | 1.6  | 1.9  | 3.1                 | ps (rms) | 1, 2    |
| t <sub>jphPCIeG3-CC</sub> |                        | PCIe Gen 3<br>(PLL BW of 2-4MHz, 2-5MHz, CDR = 10MHz)                                            | 0.3 | 0.37 | 0.44 | 1                   | ps (rms) | 1, 2    |
| t <sub>jphPCIeG4-CC</sub> |                        | PCIe Gen 4<br>(PLL BW of 2-4MHz, 2-5MHz, CDR = 10MHz)                                            | 0.3 | 0.37 | 0.44 | 0.5                 | ps (rms) | 1, 2    |

### Notes on PCIe Filtered Phase Jitter Tables

<sup>1</sup> Applies to all differential outputs, guaranteed by design and characterization.

<sup>2</sup> Calculated from Intel-supplied Clock Jitter Tool, with spread on and off.

<sup>3</sup> Sample size of at least 100K cycles. This figure extrapolates to 108ps pk-pk at 1M cycles for a BER of 1<sup>-12</sup>.

## Electrical Characteristics–REF

TA = T<sub>COM</sub> or T<sub>IND</sub>; Supply Voltage per VDD of normal operation conditions, See Test Loads for Loading Conditions

| PARAMETER              | SYMBOL               | CONDITIONS                                                        | MIN | TYP  | MAX  | UNITS    | Notes |
|------------------------|----------------------|-------------------------------------------------------------------|-----|------|------|----------|-------|
| Long Accuracy          | ppm                  | see T <sub>period</sub> min-max values                            |     | 0    |      | ppm      | 1,2   |
| Clock period           | T <sub>period</sub>  | 25 MHz output nominal                                             |     | 40   |      | ns       | 1,2   |
| Rise/Fall Slew Rate    | t <sub>rf1</sub>     | Byte 3 = 1F, V <sub>OH</sub> = VDD-0.45V, V <sub>OL</sub> = 0.45V | 0.5 | 1    | 2.5  | V/ns     | 1,3   |
| Rise/Fall Slew Rate    | t <sub>rf1</sub>     | Byte 3 = 5F, V <sub>OH</sub> = VDD-0.45V, V <sub>OL</sub> = 0.45V | 0.5 | 1.6  | 2.5  | V/ns     | 1,3   |
| Rise/Fall Slew Rate    | t <sub>rf1</sub>     | Byte 3 = 9F, V <sub>OH</sub> = VDD-0.45V, V <sub>OL</sub> = 0.45V | 0.5 | 2    | 2.5  | V/ns     | 1,3   |
| Rise/Fall Slew Rate    | t <sub>rf1</sub>     | Byte 3 = DF, V <sub>OH</sub> = VDD-0.45V, V <sub>OL</sub> = 0.45V | 0.5 | 2.1  | 2.5  | V/ns     | 1,3   |
| Duty Cycle             | d <sub>t1</sub>      | V <sub>T</sub> = VDD/2 V                                          | 45  | 53.1 | 55   | %        | 1,4   |
| Duty Cycle Distortion  | d <sub>tcd</sub>     | V <sub>T</sub> = VDD/2 V                                          | 0   | 2    | 4    | %        | 1,5   |
| Jitter, cycle to cycle | t <sub>jcc-cyc</sub> | V <sub>T</sub> = VDD/2 V                                          |     | 19   | 250  | ps       | 1,4   |
| Noise floor            | t <sub>dBc1k</sub>   | 1kHz offset                                                       |     | -130 | -105 | dBc      | 1,4   |
| Noise floor            | t <sub>dBc10k</sub>  | 10kHz offset to Nyquist                                           |     | -140 | -120 | dBc      | 1,4   |
| Jitter, phase          | t <sub>jphREF</sub>  | 12kHz to 5MHz                                                     |     | 0.63 | 1.5  | ps (rms) | 1,4   |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup>All Long Term Accuracy and Clock Period specifications are guaranteed assuming that REF is trimmed to 25.00 MHz

<sup>3</sup>Typical value occurs when REF slew rate is set to default value

<sup>4</sup>When driven by a crystal.

<sup>5</sup>When driven by an external oscillator via the X1 pin. X2 should be floating in this case.

## Clock Periods–Differential Outputs with Spread Spectrum Disabled

| SSC OFF | Center Freq. MHz | Measurement Window     |                             |                             |                      |                             |                             |                        | Units | Notes |
|---------|------------------|------------------------|-----------------------------|-----------------------------|----------------------|-----------------------------|-----------------------------|------------------------|-------|-------|
|         |                  | 1 Clock                | 1us                         | 0.1s                        | 0.1s                 | 0.1s                        | 1us                         | 1 Clock                |       |       |
|         |                  | -c2c jitter AbsPer Min | -SSC Short-Term Average Min | - ppm Long-Term Average Min | 0 ppm Period Nominal | + ppm Long-Term Average Max | +SSC Short-Term Average Max | +c2c jitter AbsPer Max |       |       |
| DIF     | 100.00           | 9.94900                |                             | 9.99900                     | 10.00000             | 10.00100                    |                             | 10.05100               | ns    | 1,2   |

## Clock Periods–Differential Outputs with -0.5% Spread Spectrum Enabled

| SSC ON | Center Freq. MHz | Measurement Window     |                             |                             |                      |                             |                             |                        | Units | Notes |
|--------|------------------|------------------------|-----------------------------|-----------------------------|----------------------|-----------------------------|-----------------------------|------------------------|-------|-------|
|        |                  | 1 Clock                | 1us                         | 0.1s                        | 0.1s                 | 0.1s                        | 1us                         | 1 Clock                |       |       |
|        |                  | -c2c jitter AbsPer Min | -SSC Short-Term Average Min | - ppm Long-Term Average Min | 0 ppm Period Nominal | + ppm Long-Term Average Max | +SSC Short-Term Average Max | +c2c jitter AbsPer Max |       |       |
| DIF    | 99.75            | 9.94906                | 9.99906                     | 10.02406                    | 10.02506             | 10.02607                    | 10.05107                    | 10.10107               | ns    | 1,2   |

<sup>1</sup>Guaranteed by design and characterization, not 100% tested in production.

<sup>2</sup>All Long Term Accuracy and Clock Period specifications are guaranteed assuming that REF is trimmed to 25.00 MHz

## General SMBus Serial Interface Information

### How to Write

- Controller (host) sends a start bit
- Controller (host) sends the write address
- IDT clock will **acknowledge**
- Controller (host) sends the beginning byte location = N
- IDT clock will **acknowledge**
- Controller (host) sends the byte count = X
- IDT clock will **acknowledge**
- Controller (host) starts sending Byte N through Byte N+X-1
- IDT clock will **acknowledge** each byte **one at a time**
- Controller (host) sends a Stop bit

| Index Block Write Operation |           |                      |     |
|-----------------------------|-----------|----------------------|-----|
| Controller (Host)           |           | IDT (Slave/Receiver) |     |
| T                           | starT bit |                      |     |
| Slave Address               |           |                      |     |
| WR                          | WRite     |                      |     |
|                             |           |                      | ACK |
| Beginning Byte = N          |           |                      |     |
|                             |           |                      | ACK |
| Data Byte Count = X         |           |                      |     |
|                             |           |                      | ACK |
| Beginning Byte N            |           |                      |     |
|                             |           |                      | ACK |
| O                           |           | X Byte               |     |
| O                           |           |                      | O   |
| O                           |           |                      | O   |
|                             |           |                      | O   |
| Byte N + X - 1              |           |                      |     |
|                             |           |                      | ACK |
| P                           | stoP bit  |                      |     |

**Note:** Read/Write address is determined by SADR latch.

### How to Read

- Controller (host) will send a start bit
- Controller (host) sends the write address
- IDT clock will **acknowledge**
- Controller (host) sends the beginning byte location = N
- IDT clock will **acknowledge**
- Controller (host) will send a separate start bit
- Controller (host) sends the read address
- IDT clock will **acknowledge**
- IDT clock will send the data byte count = X
- IDT clock sends Byte N+X-1
- IDT clock sends **Byte 0 through Byte X (if X<sub>(H)</sub> was written to Byte 8)**
- Controller (host) will need to acknowledge each byte
- Controller (host) will send a not acknowledge bit
- Controller (host) will send a stop bit

| Index Block Read Operation |                 |                      |                   |
|----------------------------|-----------------|----------------------|-------------------|
| Controller (Host)          |                 | IDT (Slave/Receiver) |                   |
| T                          | starT bit       |                      |                   |
| Slave Address              |                 |                      |                   |
| WR                         | WRite           |                      |                   |
|                            |                 |                      | ACK               |
| Beginning Byte = N         |                 |                      |                   |
|                            |                 |                      | ACK               |
| RT                         | Repeat starT    |                      |                   |
| Slave Address              |                 |                      |                   |
| RD                         | ReaD            |                      |                   |
|                            |                 |                      | ACK               |
| ACK                        |                 |                      | Data Byte Count=X |
| ACK                        |                 |                      | Beginning Byte N  |
|                            |                 | X Byte               |                   |
| O                          |                 |                      | O                 |
| O                          |                 |                      | O                 |
| O                          |                 |                      | O                 |
| ACK                        |                 |                      |                   |
| ACK                        |                 |                      | Byte N + X - 1    |
| N                          | Not acknowledge |                      |                   |
| P                          | stoP bit        |                      |                   |

**SMBus Table: Output Enable Register**

| Byte 0 | Name    | Control Function | Type | 0       | 1       | Default |
|--------|---------|------------------|------|---------|---------|---------|
| Bit 7  |         | Reserved         |      |         |         | 1       |
| Bit 6  |         | Reserved         |      |         |         | 1       |
| Bit 5  |         | Reserved         |      |         |         | 1       |
| Bit 4  |         | Reserved         |      |         |         | 1       |
| Bit 3  |         | Reserved         |      |         |         | 1       |
| Bit 2  | DIF OE1 | Output Enable    | RW   | Low/Low | Enabled | 1       |
| Bit 1  | DIF OE0 | Output Enable    | RW   | Low/Low | Enabled | 1       |
| Bit 0  |         | Reserved         |      |         |         | 1       |

**SMBus Table: SS Readback and Vhigh Control Register**

| Byte 1 | Name         | Control Function            | Type            | 0                                                                        | 1                                    | Default |
|--------|--------------|-----------------------------|-----------------|--------------------------------------------------------------------------|--------------------------------------|---------|
| Bit 7  | SSENRB1      | SS Enable Readback Bit1     | R               | 00' for SS_EN_tri = 0, '01' for SS_EN_tri = 'M', '11 for SS_EN_tri = '1' |                                      | Latch   |
| Bit 6  | SSENRB1      | SS Enable Readback Bit0     | R               |                                                                          |                                      | Latch   |
| Bit 5  | SSEN_SWCNTRL | Enable SW control of SS     | RW              | SS control locked                                                        | Values in B1[4:3] control SS amount. | 0       |
| Bit 4  | SSENSW1      | SS Enable Software Ctl Bit1 | RW <sup>1</sup> | 00' = SS Off, '01' = -0.25% SS, '10' = Reserved, '11' = -0.5% SS         |                                      | 0       |
| Bit 3  | SSENSW0      | SS Enable Software Ctl Bit0 | RW <sup>1</sup> |                                                                          |                                      | 0       |
| Bit 2  |              | Reserved                    |                 |                                                                          |                                      | 1       |
| Bit 1  | AMPLITUDE 1  | Controls Output Amplitude   | RW              | 00 = 0.6V                                                                | 01 = 0.7V                            | 1       |
| Bit 0  | AMPLITUDE 0  |                             | RW              | 10 = 0.8V                                                                | 11 = 0.9V                            | 0       |

1. B1[5] must be set to a 1 for these bits to have any effect on the part.

**SMBus Table: DIF Slew Rate Control Register**

| Byte 2 | Name             | Control Function         | Type | 0       | 1       | Default |
|--------|------------------|--------------------------|------|---------|---------|---------|
| Bit 7  |                  | Reserved                 |      |         |         | 1       |
| Bit 6  |                  | Reserved                 |      |         |         | 1       |
| Bit 5  |                  | Reserved                 |      |         |         | 1       |
| Bit 4  |                  | Reserved                 |      |         |         | 1       |
| Bit 3  |                  | Reserved                 |      |         |         | 1       |
| Bit 2  | SLEWRATESEL DIF1 | Adjust Slew Rate of DIF1 | RW   | 2.0V/ns | 3.0V/ns | 1       |
| Bit 1  | SLEWRATESEL DIF0 | Adjust Slew Rate of DIF0 | RW   | 2.0V/ns | 3.0V/ns | 1       |
| Bit 0  |                  | Reserved                 |      |         |         | 1       |

**SMBus Table: REF Control Register**

| Byte 3 | Name                    | Control Function           | Type | 0                              | 1                      | Default |
|--------|-------------------------|----------------------------|------|--------------------------------|------------------------|---------|
| Bit 7  | REF                     | Slew Rate Control          | RW   | 00 = Slowest                   | 01 = Slow              | 0       |
| Bit 6  |                         |                            | RW   | 10 = Fast                      | 11 = Faster            | 1       |
| Bit 5  | REF Power Down Function | Wake-on-Lan Enable for REF | RW   | REF does not run in Power Down | REF runs in Power Down | 0       |
| Bit 4  | REF OE                  | REF Output Enable          | RW   | Low                            | Enabled                | 1       |
| Bit 3  |                         | Reserved                   |      |                                |                        | 1       |
| Bit 2  |                         | Reserved                   |      |                                |                        | 1       |
| Bit 1  |                         | Reserved                   |      |                                |                        | 1       |
| Bit 0  |                         | Reserved                   |      |                                |                        | 1       |

Byte 4 is reserved and reads back 'hFF'.

**SMBus Table: Revision and Vendor ID Register**

| Byte 5 | Name | Control Function | Type | 0            | 1 | Default |
|--------|------|------------------|------|--------------|---|---------|
| Bit 7  | RID3 | Revision ID      | R    | A rev = 0000 |   | 0       |
| Bit 6  | RID2 |                  | R    |              |   | 0       |
| Bit 5  | RID1 |                  | R    |              |   | 0       |
| Bit 4  | RID0 |                  | R    |              |   | 0       |
| Bit 3  | VID3 | VENDOR ID        | R    | 0001 = IDT   |   | 0       |
| Bit 2  | VID2 |                  | R    |              |   | 0       |
| Bit 1  | VID1 |                  | R    |              |   | 0       |
| Bit 0  | VID0 |                  | R    |              |   | 1       |

**SMBus Table: Device Type/Device ID**

| Byte 6 | Name         | Control Function | Type | 0                                             | 1 | Default |
|--------|--------------|------------------|------|-----------------------------------------------|---|---------|
| Bit 7  | Device Type1 | Device Type      | R    | 00 = FGV, 01 = DBV,<br>10 = DMV, 11= Reserved |   | 0       |
| Bit 6  | Device Type0 |                  | R    |                                               |   | 0       |
| Bit 5  | Device ID5   | Device ID        | R    | 00010 binary or 02 hex                        |   | 0       |
| Bit 4  | Device ID4   |                  | R    |                                               |   | 0       |
| Bit 3  | Device ID3   |                  | R    |                                               |   | 0       |
| Bit 2  | Device ID2   |                  | R    |                                               |   | 0       |
| Bit 1  | Device ID1   |                  | R    |                                               |   | 1       |
| Bit 0  | Device ID0   |                  | R    |                                               |   | 0       |

**SMBus Table: Byte Count Register**

| Byte 7 | Name     | Control Function       | Type | 0                                                                                               | 1 | Default |
|--------|----------|------------------------|------|-------------------------------------------------------------------------------------------------|---|---------|
| Bit 7  | Reserved |                        |      |                                                                                                 |   | 0       |
| Bit 6  | Reserved |                        |      |                                                                                                 |   | 0       |
| Bit 5  | Reserved |                        |      |                                                                                                 |   | 0       |
| Bit 4  | BC4      | Byte Count Programming | RW   | Writing to this register will configure how many bytes will be read back, default is = 8 bytes. |   | 0       |
| Bit 3  | BC3      |                        | RW   |                                                                                                 |   | 1       |
| Bit 2  | BC2      |                        | RW   |                                                                                                 |   | 0       |
| Bit 1  | BC1      |                        | RW   |                                                                                                 |   | 0       |
| Bit 0  | BC0      |                        | RW   |                                                                                                 |   | 0       |

## Recommended Crystal Characteristics (3225 package)

| PARAMETER                                                        | VALUE       | UNITS   | NOTES |
|------------------------------------------------------------------|-------------|---------|-------|
| Frequency                                                        | 25          | MHz     | 1     |
| Resonance Mode                                                   | Fundamental | -       | 1     |
| Frequency Tolerance @ 25°C                                       | ±20         | PPM Max | 1     |
| Frequency Stability, ref @ 25°C Over Operating Temperature Range | ±20         | PPM Max | 1     |
| Temperature Range (commercial)                                   | 0~70        | °C      | 1     |
| Temperature Range (industrial)                                   | -40~85      | °C      | 2     |
| Equivalent Series Resistance (ESR)                               | 50          | Ω Max   | 1     |
| Shunt Capacitance (C <sub>O</sub> )                              | 7           | pF Max  | 1     |
| Load Capacitance (C <sub>L</sub> )                               | 8           | pF Max  | 1     |
| Drive Level                                                      | 0.3         | mW Max  | 1     |
| Aging per year                                                   | ±5          | PPM Max | 1     |

**Notes:**



- FOX 603-25-150.
- For I-temp, FOX 603-25-261.

## Thermal Characteristics

| PARAMETER          | SYMBOL         | CONDITIONS                      | PKG            | TYP<br>VALUE | UNITS | NOTES |
|--------------------|----------------|---------------------------------|----------------|--------------|-------|-------|
| Thermal Resistance | $\theta_{JC}$  | Junction to Case                | NLG20<br>NLG24 | 62           | °C/W  | 1     |
|                    | $\theta_{Jb}$  | Junction to Base                |                | 5.4          | °C/W  | 1     |
|                    | $\theta_{JA0}$ | Junction to Air, still air      |                | 50           | °C/W  | 1     |
|                    | $\theta_{JA1}$ | Junction to Air, 1 m/s air flow |                | 43           | °C/W  | 1     |
|                    | $\theta_{JA3}$ | Junction to Air, 3 m/s air flow |                | 39           | °C/W  | 1     |
|                    | $\theta_{JA5}$ | Junction to Air, 5 m/s air flow |                | 38           | °C/W  | 1     |

<sup>1</sup>ePad soldered to board


## Marking Diagrams




Notes:

1. 'LOT' is the lot number.
2. 'YYWW' is the last two digits of the year and week that the part was assembled.
3. 'L' denotes RoHS compliant package.
4. 'I' denotes industrial temperature grade.

# Package Outline and Dimensions (NLG24)



# **Package Outline and Dimensions (NLG24), cont.**



## Ordering Information

| Part / Order Number | Shipping Packaging | Package       | Temperature   |
|---------------------|--------------------|---------------|---------------|
| 9FGV0241AKLF        | Tubes              | 24-pin VFQFPN | 0 to +70° C   |
| 9FGV0241AKLFT       | Tape and Reel      | 24-pin VFQFPN | 0 to +70° C   |
| 9FGV0241AKILF       | Tubes              | 24-pin VFQFPN | -40 to +85° C |
| 9FGV0241AKILFT      | Tape and Reel      | 24-pin VFQFPN | -40 to +85° C |

“LF” suffix to the part number are the Pb-Free configuration and are RoHS compliant.

“A” is the device revision designator (will not correlate with the datasheet revision).

## Revision History

| Issue Date        | Description                                                                                                                                                                                            |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| February 3, 2015  | Updated IDDAOP and IDDOP typ and max specs per latest characterization review.                                                                                                                         |
| November 30, 2015 | Updated block diagram                                                                                                                                                                                  |
| January 4, 2016   | Corrected typo in ordering information; changed rev "B" to rev "A"                                                                                                                                     |
| October 18, 2016  | Removed IDT crystal part number                                                                                                                                                                        |
| June 19, 2017     | Updated front page Gendes to reflect the PCIe Gen4 updates.<br>Updated Electrical Characteristics - Filtered Phase Jitter Parameters - PCIe Common Clocked (CC) Architectures and added PCIe Gen4 Data |
| June 6, 2019      | Updated Input Current minimum and maximum values from -200/200 uA to -20/20 uA.                                                                                                                        |



## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.