











THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO 1583000	USED ON _____												
	TOOL NUMBER  -1  -3 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 				CONTACT DESCRIP.	APPLIC. SPECIF.
								LOOSE PIECE 		STRIP FORM 			
	91500-1 91500-3 91500-4 	0.5 - 0.9 [20-18] 1.2 - 2.1 [16-14]	1.52 - 3.30 [.060 - .130]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.27 ± 0.05 [.050 ± .002] 1.60 ± 0.05 [.063 ± .002]	350547-[] 350669-[] 770250-[] 770254-[]	350550-[] 350705-[] 770251-[] 770251-[]	350218-[] 350654-[] 770007-[] 770193-[]	350536-[] 350687-[] 770008-[] 770008-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91506-1 91506-3	1.21 - 2.1 [16-14]	3.3 - 5.1 [.130 - .200]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.60 ± 0.05 [.063 ± .002]	350551-[] 350707-[] 350918-[] 770248-[]	350552-[] 350919-[] 770249-[] 770255-[]	350537-[] 350700-[] 350873-[] 770005-[]	350538-[] 350874-[] 770006-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91508-1 91508-3	0.5 - 0.9 [20-18]	3.3 - 5.1 [.130 - .200]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.24 ± 0.05 [.049 ± .002]	350551-[] 350707-[] 350918-[] 770248-[]	350552-[] 350919-[] 770249-[] 770255-[]	350537-[] 350700-[] 350873-[] 770005-[]	350538-[] 350874-[] 770006-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91510-1 91510-3	0.2 - 0.38 [24-22] 0.5 - 0.9 [20-18]	1.02 - 2.54 [.040 - .100]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.02 ± 0.05 [.040 ± .002] 1.17 ± 0.05 [.046 ± .002]	350689-[] 350706-[] 770252-[]	350690-[] 640347-[] 770253-[]	350570-[] 350699-[] 770009-[]	350561-[] 350851-[] 770010-[]	Univ MATE-N-LOK Contacts Univ MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043
	91522-1 91522-3	0.32 - 0.6 [22-20]	1.50 - 2.2 [.059 - .087]	YES	NO	3.45 ± 0.25 [.136 ± .010]	0.79 ± 0.05 [.031 ± .002]	170364-[]	170366-[]	170360-[]	170362-[]	Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017 114-13089
		(1 wire) 0.8-0.9 [18] (2 wire) 0.31-0.38 [22]	(1 wire) 1.54-2.4 [.059-.095] (2 wire) 1.5-1.7 [.059-.067]			(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.7 ± 0.2 [.146 ± .008]	1.04 ± 0.05 [.041 ± .002]	794228-[]	794229-[]	794220-[]	794221-[]	Mini-Univ. MATE-N-LOK 2 Contacts	
								770987-[]	770988-[]	770903-[]	770904-[]		
	91529-1 91529-3	0.12 - 0.24 [26-24]	1.2 - 1.6 [.047 - .063]	YES	YES	3.45 ± 0.25 [.136 ± .010]	0.69 ± 0.05 [.027 ± .002]	170363-[]	170365-[]	170359-[] 794136-[]	170361-[]	Mini-Univ. MATE-N-LOK Contacts Mini-Univ. MATE-N-LOK 2 Contacts	114-5050 & 114-16017 114-1111 114-13089
		0.32 - 0.38 [22]	1.5-1.75 [.059 - .069]				0.79 ± 0.05 [.031 ± .002]	770985-[]		770901-[]			
	91536-1 91536-3	0.5 - 0.9 [20-18]	2.0 - 3.0 [.079 - .118]	YES	NO	3.45 ± 0.25 [.136 ± .010]	1.07 ± 0.05 [.042 ± .002]	171638-[] 171639-[]		171636-[] 171637-[]		Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017
		(1 wire) 1.2-1.4 [16] (2 wire) 0.5-0.6 [20]	(1 wire) 2.5-3.2 [.098-.126] (2 wire) 2.0-2.4 [.079-.094]			(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.27 ± 0.05 [.050 ± .002]						
91594-1 91594-3	0.50-0.89 [20-18]	2.00-3.20 [.079-.126]	YES	NO	(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002]	794230-[] 794231-[]		794222-[] 794223-[]		Mini-Univ. MATE-N-LOK 2 Contacts	114-1111	
	0.50-1.42x2 [16-20x2]	2.49-3.20 [.098-.126]				1.29 ± 0.05 [.051 ± .002]			794406-[] 794407-[]		Mini-Univ. MATE-N-LOK CONTACTS	114-16017	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS SUBSIDIARIES. IT IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY CORPORATION. ANY VIOLATION OF THIS NOTICE WILL BE PROSECUTED TO THE FULL EXTENT OF THE LAW.

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.

 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED


 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET










DWN: M.YOUNGER 21FEB2012		MATERIAL: -	HEAT TREAT: -	
CHK: B.A.WOLFE 22FEB2012		 TE Connectivity		
APVD: B.A. WOLFE 22FEB2012				
NAME: CERTI-CRIMP II TOOL DATA SHEET UNIVERSAL MATE-N-LOK CONTACT FAMILY				
SCALE: -	SIZE: A1	DRAWING NO: 1583000	SHEET: 1 of 2	
REV: D7				

P	LTR	REVISION RECORD	DATE	DWN	APVD	SURFACE TEXTURE	✓
D7	REVISED		23NOV2022	GK	AM		
D6	REVISED		10/2019	AW	SS		

DIMENSIONS: mm			TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0	PLC			
1	PLC			
2	PLC			
3	PLC			
4	PLC			
ANGLES: -				
SURFACE TEXTURE				

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THIS DOCUMENT AND NOT BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT AUTHORIZATION FROM TE CONNECTIVITY.

THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO. 1583000

TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPT.	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
 91574-1	0.20-0.56 [24-20]	1.52-2.54 [.060-.100]	YES	NO 	5.16 ± 0.38 [.203 ± .015]	1.05 ± 0.08 [.041 ± .003]	350689-[] 350690-[] 350706-[]	350570-[] 350561-[] 350699-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75-0.89 [18]					1.27 ± 0.08 [.050 ± .003]				
 91575-1 91575-3	0.50-0.89 [20-18]	2.54-3.31 [.100-.130]	YES	NO 	5.16 ± 0.38 [.203 ± .015]	1.29-1.45 [.051-.057]	350547-[] 350705-[] 350669-[] 350550-[]	350218-[] 350687-[] 350564-[] 350536-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75+0.75 OR 0.75+1.25 [18+18 OR 18+16]					1.60-1.75 [.063-.069]				
1976176-1 OBSOLETE	18 GA SOLID	1.02-2.54 [.040-.100]	YES	NO 	4.37-0.38 [.172-.015]	1.118 ± .025 [.044 ± .001]	350689-[] 350550-[] 350690-[] 350547-[]	350851-[] 350536-[] 350561-[] 350218-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
2280977-1	0.12-0.24 [26-24]	1.19-1.60 [.047-.063]	YES	NO 	3.45 ± 0.25 [.136 ± .010]	0.68 ± 0.05 [.027 ± .002]	794226-[] 794227-[]	794218-[] 794219-[]	MINI UNERVERSAL MATE-N-LOK2 Contacts	114-1111
	0.32-0.38 [22]	1.50-1.75 [.059-.069]				0.79 ± 0.05 [.031 ± .002]				
2217759-1	0.05-0.15 [30-26]	0.81-1.45 [.032-.057]	YES	NO 	3.68-4.32 [.145-.170]	0.71 ± 0.05 [.028 ± .002]	770416-[] 770512-[] 770672-[] 770673-[]	350924-[] 350925-[] 794042-[] 770011-[] 770012-[]	Universal MATE N LOCK Universal MATE N LOCK II	114-1010 & 114-1043
2326453-1	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO 	3.45±0.25 [.136±.001]	0.79 ± 0.05 [.031 ± .002]	-	2825156-1 2825157-1	Mini-Univ. MATE-N-LOK Contacts	114-16017
	0.81-0.96 [18]	2.01-2.18 [.079-.089]				1.04 ± 0.05 [.041 ± .002]				
2326016-1 SUPERSEDED BY 2326453-1	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO 	3.45 ± 0.25 [.136 ± .001]	0.79 ± 0.05 [.031 ± .002]	-	2825156-1 2825157-1	MINI UNERVERSAL MATE-N-LOK2 Contacts	114-16017
	0.81-0.96 [18]	2.11-2.39 [.083-.094]				1.04 ± 0.05 [.041 ± .002]				
2326016-2	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO 	3.45 ± 0.25 [.136 ± .001]	0.79 ± 0.05 [.031 ± .002]	770987-[] 770988-[]	770904-[] 770903-[]	Universal MATE N LOCK	114-16017
	0.60-0.96 [18]	2.11-2.39 [.083-.094]				1.04 ± 0.05 [.041 ± .002]				

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.


 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED

 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET									
DWN: M.YOUNGER		21FEB2012		MATERIAL: -		HEAT TREAT: -			
CHK: B.A.WOLFE		22FEB2012							
APVD: B.A. WOLFE		22FEB2012							
NAME: CERTI-CRIMP II TOOL DATA SHEET UNIVERSAL MATE-N-LOK CONTACT FAMILY									
SCALE: -		SIZE: A1		DRAWING NO: 1583000		SHEET: 2 of 2		REV: D7	

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± . 4 PLC ± .			
ANGLES: -		SURFACE TEXTURE: 			
P	LTR	REVISION RECORD	DATE	DWN	APVD
-	SEE SHEET 1	-	-	-	-