




The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.


PTM90 Series Panel Control w/Push-Push Switch

BOURNS®


Mounting Hole Detail



Locating Lug Detail



Hardware



How To Order


PTM90 2 - 0 25 S - 103 B2

Model Number
Designator
PTM90 = Panel Control
w/Push-Push Switch
Number of Sections
2 = Dual Gang
Center Detent
0 = No Detent
1 = Center Detent
Shaft Length (FMS)
20 = 20 mm (Knurled and Flatted
shaft)
25 = 25 mm (Slotted shaft only)
30 = 30 mm (Flatted shaft only)
Shaft Style
F = Flatted Metal
K = Knurled (18 tooth serrated)
S = Slotted Metal
Resistance Code
(See Standard Resistance Table)
Resistance Taper (See Taper Charts)
Taper Series followed by Curve Number

Standard Resistance Table


Resistance (Ohms)	Resistance Code
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104
200,000	204
500,000	504
1,000,000	105

Switch Circuit






Schematic

Dual Gang



Tapers



REV. 02/15

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.