


NOTES:

1. MAXIMUM MOUNTING TORQUE = 4 in.lbs.
2. HARDWARE IS INCLUDED.



LEAD FINISH:	SILVER
BUSHING FINISH:	SILVER
CAPACITANCE	22nF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 100 VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	

FREQ. MHz	I.L. (db)
1	7
10	27
100	43
1 GHz	60
10 GHz	60

SCHEMATIC



MARKING:


PART: S712003
BAG:
SCI 51-712-003
DATE CODE
LOT NO.
QTY/BAG (100 MAX.)

48

CN. 173266

REV. 1
CHANGE NOTICE NO.

TOLERANCES UNLESS OTHERWISE SPECIFIED
Fract. 1/64
Dec. .xx±
Dec. .xxx±0.10
Angles ±0° 30'
CODE IDENT. NO.
DLSP2



SPECTRUM CONTROL INC.
Dwn KAUFFMAN
Ckd. 4-26-96
Apvd.
Scale NONE

ERIE, FAIRVIEW
PENNSYLVANIA

Descript. FEED THRU
RESIN SEAL FILTER

51-712-003