

MICRO SWITCH
a Honeywell Division


FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

YA-2RQ1250-A2

ADG9219



2X 6-32 UNC X (.219) BINDING
HEAD COMBINATION TERMINAL
SCREW AND CUPWASHER


NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\phi .139$ MAX ON $1.000 \pm .002$ CENTERS
- 2 - HIGH TEMPERATURE PHENOLICS
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 14 - 22 OZ
RELEASE FORCE ----- 10 OZ MIN
DIFFERENTIAL TRAVEL ----- .002 - .0075
OVERTRAVEL ----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

L23 20A 125, 250 OR 480 VAC
10A 125 VAC "L"
1HP 125 VAC, 2HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

L288
L308
L315
L319



20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

CATALOG LISTING
YA-2RQ1250-A2
PAGE 1 OF 1

ISSUE
5

REVISIONS

A	207614	CSL	10 MAR 03	01 OCT 09
B	207734	CSL	24 MAR 03	CMH
C	0017742	TSG	09 JAN 06	CMH
D	0057238	SSK	01 OCT 09	CHECK

REPLACES X114681-YA

RELEASE NO. 207278

CHECK

27 JAN 03

SAV

CHECK

27 JAN 03

RASTER
DRAWN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[YA-2RQ1250-A2](#)