

**INSTA
CP SNT 25W 5V 5A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



One-phase switched-mode power unit in installation housing in performance classes 24 and 48 W. .
The INSTA power units can be universally deployed because of their wide input range from 85 V AC to 265 V AC.
They are available with output voltages from 5 V to 48 V.

General ordering data

Order No.	8754960000
Type	CP SNT 25W 5V 5A
Version	Power supply, switch-mode power supply unit
GTIN (EAN)	4032248426119
Qty.	1 pc(s).

INSTA
CP SNT 25W 5V 5A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data
Dimensions

Length	62.5 mm	Width	70 mm
Height	90.5 mm	Weight	0.2 kg
Net weight	352 g		

Temperatures

Operating temperature	-10 °C...+70 °C (Derating ab 55 °C)	Storage temperature	-20 °C...+85 °C
-----------------------	--	---------------------	-----------------

Input

Conductor connection system	Screw connection	Input current	500 mA at rated load @ 230 V AC
Input current at 115 Vac	500 mA	Input current at 230 Vac	500 mA
Input frequency	50/ 60 Hz	Input fuse	Fusible link 2.5 A (T) / 250 V
Input voltage (voltage mode input)	85...264 V AC / 110...370 V DC	Turn-on current limit	Yes

output

Conductor connection system	Screw connection	Control at 10...100% load	1 %
Mains failure bridge-over time	11 ms @ 115 V AC / 50 ms @ 230 V AC	Max. capacitance at output	10000 µF
Max. residual ripple	120 mV _{SS}	Output current	5 A
Output voltage	4...8 V DC (adjustable via potentiometer)	Output voltage type	DC
Output voltage, max.	8 V	Output voltage, min.	4 V
Output voltage, note	(adjustable via potentiometer)	Overload protection	105 %...150 % I _{const} of max. output load; automatic reset
Parallel connection option	Max. 3 devices (rated voltages are to be calibrated at ±20 mV)	Surge protection	Varistor
output power	25 W		

General data

Building Width	62.5 mm	Building height	90.5 mm
Degree of efficiency at max. load	70 %	EMC standards	EN 55011, EN 55022, EN 61000-3-2,-3, EN 61000-6-2,-3,-4
Installation advice	Can be mounted side-by- side, clearance: above/ below > 30 mm	MTBF	> 500,000 h acc. to IEC 1709 (SN29500)
Mounting position, installation notice	horizontally, on terminal rail TS 35	Operating temperature	-10 °C...+70 °C (Derating ab 55 °C)
Standards	DIN EN 50178 (PELV), DIN EN 60950 (SELV)	Status indication	Green LED
Weight	0.2 kg		

Insulation coordination

Humidity at operating temperature	5...95 % (indoors), Tu = 40°C, no condensation	electrical isolation, I/O rail	4 kV
electrical isolation, input-earth	1.5 kV	electrical isolation, input-output	3 kV
electrical isolation, output-earth	0.5 kV		

Creation date July 6, 2012 6:04:11 AM CEST

**INSTA
CP SNT 25W 5V 5A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data**PA52_7 signalling**

Status indication Green LED

Rated data UL

Certificate No. (UL) E252191VOL1SEC2

Classifications

ETIM 2.0	EC001039	ETIM 3.0	EC001039
UNSPSC	30-21-18-01	eClass 4.1	27-24-04-10
eClass 5.1	27-04-90-02	eClass 6.0	27-04-90-04
eClass 7.0	27-04-90-04		

Approvals

Approvals

**Downloads**

Declaration of Conformity [K286_06_09.pdf](#)

PDF [Warranty information](#)

[3-D model](#)

**INSTA
CP SNT 25W 5V 5A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com**Drawings****Electric symbol**