



Pos	A	B	C	Pos	A	B	C
4	9.70	3.81	5.60	16	24.94	19.05	20.84
6	12.24	6.35	8.14	18	27.48	21.59	23.38
8	14.78	8.89	10.68	20	30.02	24.13	25.92
10	17.32	11.43	13.22	22	32.56	26.67	28.46
12	19.86	13.97	15.76	24	35.10	29.21	31.00
14	22.40	16.51	18.30	26	37.64	31.75	33.54



Current Rating:1.5A AC/DC
Voltage Rating:230V AC/DC
Contact Resistance:20m ohm. Max.
Insulation Resistance:1000M ohm. Min.
Withstanding Voltage:500V AC/minute
Operating Temperature Range:-40°C ~ +105°C
Material and Finish
Insulator:High Temp. Plastic (UL94V-0)
Contact:Phosphor Bronze
Finish:Tin Plated

How to Order


TMM-X-X-XX-X

1-IDC Male
2-IDC Plug
3-DIP Male Straight
4-DIP Female Straight
5-DIP Female R/A
6-SMT Female Straight

1 - Tape & Reel with vacuum cap
2 - Tube
3 - Bag
4 - Tape & Reel without vacuum cap

— Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26

0-without lock
L-with lock



PCB Layout

TOLERANCE (mm)		APPROVALS		DATE		TITLE TMM Series Female Dip type w/ Lock		AMPHENOL Amphenol European Design Center			
X.	±0.3	DRAWN	Stephane	06/Apr/2009				Scale N.A.		Sheet 1 of 1	
XX	±0.2	CHECKED	Rob	06/Apr/2009							
X_XX	±0.15	APPROVED	Rob	06/Apr/2009							
UNLESS OTHERWISE SPECIFIED				UNIT: mm		SIZE: A4	DRAWING N° TMM-4-L-XX-X		REV. D		