








	10	9	8	7	6	5	4	3	2	1
F	15									
	14									
	13									
	12									
	11									
	10	560123								
	9		505151							
	8	560123		502351						
	7									
	6	560123								
	5									
E	4									
	3	560123								
	2									
CKTS	ISL Receptacle	TPA Receptacle	Standard Receptacle							
Mate With Series										




RECOMMENDED DIMENSIONS
FOR CONNECTOR INTERFACE

RELEASED EC NO: JTR2016-0011 DRWN: YAMAKI CHKD: KOMATSU APPR: MAYAMOTO 2015/03/25 2015/07/24 2015/07/24	DESCRIPTION	QUALITY SYMBOLS ▽_A = 0 ▽_B = 0 ▽_C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION							
					DRAWN BY YTAMAKI	DATE 2015/03/25	TITLE 2.0MM PITCH W/B CONN. INTERFACE DRAWING									
					CHECKED BY HKOMATSU	DATE 2015/07/24										
					APPROVED BY MAYAMAMOTO	DATE 2015/07/24										
					MATERIAL NO. ---		DOCUMENT NO. SD-502352-003-JP									
					SIZE A3							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
					ANGULAR ± - °		SHEET NO. 2 OF 2									
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											



SECTION Z-Z




MATED DRAWING

注記
NOTES

- 材質
ウエハー: 耐熱性ナイロン UL94V-0
ピン: 銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール: 銅合金、ニッケル下地、錫メッキ
MATERIAL
WAFER: POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FITTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色: ナチュラル
COLOR: NATURAL
- 嵌合相手:
ハウジング: 502351-xx00
錫メッキ端子: 50212-8*00, 50372-8*00, 560085-0101
金メッキ端子: 56161-8*81
MATES WITH
HOUSING: 502351-xx00
SN PLATING TERMINAL: 50212-8*00, 50372-8*00, 560085-0101
AU PLATING TERMINAL: 56161-8*81
- エンボス梱包品の詳細はSD-560020-002参照
DETAILED TAPING PACKAGE, SEE SD-560020-002
- ELV及びRoHS適合
ELV AND ROHS COMPLIANT
- 半田付け面のコプラナリティ: 0.1mm MAX.
CO-PLANARITY OF SOLDER TAILS TO BE 0.1mm MAX.

- 一般公差
GENERAL TOLERANCES
10 UNDER: 0.2
10 OVER 30 UNDER: 0.25
30 OVER: 0.3
ANGULAR $\pm 1^\circ$

REVISED EC NO: JTR2015-0089 DRAWN: YAMAKI CHKD: HKOMATSU APPR: MAYAMOTO	2014/12/25 2014/12/25 2015/04/28	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
						MM ONLY		5:1	METRIC		
						DRAWN BY DATE		TITLE 2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT molex		SHEET NO. 1 OF 4	
						SHSHIBATA 2009/02/18					
						CHECKED BY DATE					
						HKOMATSU 2009/02/18					
						APPROVED BY DATE					
						AKANESHIGE 2009/02/18		DOCUMENT NO.		SD-560020-001	
						MATERIAL NO.					
						SEE CHART					
		SIZE A3									




2CKTS

3CKTS


4CKTS

5CKTS


6CKTS



7CKTS




9CKTS



10CKTS

REVISED	EC NO: JTR2015-0089	TDRWN:Y.TAMAKI 2014/12/25 CHKD:HKOMATSU 2014/12/25 APPR: MAYAMAMOTO 2015/04/28	DESCRIPTION	QUALITY SYMBOLS F₁=0 F₂=0 F₃=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><th></th><th>mm</th><th>INCH</th></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>± ---</td><td>± ---</td></tr></table>			mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	0 PLACE	± ---	± ---	DIMENSION STYLE MM ONLY	SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
						mm	INCH																					
					4 PLACES	± ---	± ---																					
					3 PLACES	± ---	± ---																					
					2 PLACES	± ---	± ---																					
1 PLACE	± ---	± ---																										
0 PLACE	± ---	± ---																										
REV				2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT molex	DRAWN BY SHSHIBATA		DATE 2009/02/18	TITLE																				
					CHECKED BY HKOMATSU		DATE 2009/02/18																					
					APPROVED BY AKANESHI GE		DATE 2009/02/18																					
					MATERIAL NO.																							
					DOCUMENT NO. SD-560020-001		SHEET NO. 2 OF 4																					
					SEE CHART																							
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							



10

9

8

7

6


5

4


3

2


1



DETAIL Y




PULL OUT DIRECTION




NOTES


- 製品番号: 560020-***0 詳細寸法については、製品単体図面を参照ください。
PART NO. 5600020-***0 SEE SALES DRAWING FOR CONNECTOR
- 梱包数量: 650個/REEL
NUMBER OF CONNECTORS 650 PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- 材料
MATERIAL
キャリアテープ: ポリスチレン
CARRIER TAPE: POLYSTYRENE
トップテープ: PET, PE, PEF
TOP TAPE
リール: ポリスチレン
REEL: POLYSTYRENE



PULL OUT DIRECTION

DIRECTION OF CONNECTOR
IN EMBOSSED TAPEDETAIL X
(SCALE 10:1)

49.4	45.4	44	20.2	22.9	560020-0800	08
				20.9	560020-0700	07
37.4	33.4	32	14.2	18.9	560020-0600	06
				16.9	560020-0500	05
				14.9	560020-0400	04
29.4	25.4	24	11.5	12.9	560020-0300	03
				11.2	560020-0200	02
E	D	C	(B)	(A)	エンボス梱包品 製品番号 MATERIAL NO.	CIRCUITS

REVISED	EC NO: JTR2014-0066 DRWN: YAMAKI CHKD: HKOMATSU APPR: MAYAMOTO	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			10 UNDER	± 0.2	DRAWN BY YTAMAKI	DATE 2012/02/29	TITLE 2.0MM PITCH W/B ST. WAFER ASSY EMBOSSED TAPE PACKAGE				
			10 OVER 30 UNDER	± 0.25	CHECKED BY HKOMATSU	DATE 2012/02/29					
			30 OVER	± 0.3	APPROVED BY MAYAMOTO	DATE 2012/03/01	molex				
			ANGULAR ±1 °	MATERIAL NO.	DOCUMENT NO.	SHEET NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-560020-002		1 OF 1		
B	REV	SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9

8

7

6

5

4

3

2

1