



Features

- DC to 1 GHz
- Flanged model
- Low VSWR
- 12.5, 25, 50 and 100 ohm resistance values available

Applications

- High power RF transmission

CHF190104xBF Series 800 W Power RF Flanged Chip Termination/Resistor

General Specifications

SubstrateBeo
Resistive Film.....Thick Film
TabAg
Cover Substrate.....AL203
Mounting FlangeCu plated with Ni
Resistance 12.5, 25, 50 or 100 ohms
Tolerance±5 %
Packaging20 pcs./tray

Absolute Ratings

Power800 W
Frequency1.0 GHz
VSWR1.2 Maximum

How To Order


CHF 190104 C B F 500 L

Model _____
Size _____
Version (See Product Dimensions) _____
 C
 E (Version E only exists for Terminations)
Substrate _____
Mount _____
 F = Flange
Value _____
 12R5 = 12.5 Ohms (Resistor Only)
 250 = 25 Ohms (Resistor Only)
 500 = 50 Ohms (Resistor and Termination)
 101 = 100 Ohms (Resistor and Termination)
Function _____
 L = Termination
 R = Resistor (See Product Dimensions)




Asia-Pacific:
Tel: +886-2 2562-4117
Fax: +886-2 2562-4116
Europe:
Tel: +41-41 768 5555
Fax: +41-41 768 5510
The Americas:
Tel: +1-951 781-5500
Fax: +1-951 781-5700
www.bourns.com

Characteristic Curve



Product Dimensions



REV. 09/08

*RoHS Directive 2002/95/EC Jan 27 2003, including Annex
Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[CHF190104CBF500L](#) [CHF190104CBF250R](#) [CHF190104CBF500R](#) [CHF190104CBF101L](#) [CHF190104CBF101R](#)
[CHF190104CBF12R5R](#)