



Pb-free
HEAT



SW1142P

1608 (h=0.20mm) Type White LED

Features

Package	1608 (h=0.20 mm) Type, Pale yellow resin
Product features	▪ Outer Dimension 1.6 x 0.8 x 0.20mm(L x W x H) ▪ Temperature range - Storage Temperature : -40℃~100℃ - Operating Temperature : -40℃~ 85℃ ▪ Lead-free soldering compatible ▪ RoHS compliant
Chromaticity coordinates	TYP. x = 0.27, y = 0.26 (Condition : I _F =1mA)
Half Intensity Angle	120 deg.
Die materials	InGaN
Rank grouping parameter	Sorted by luminous intensity and chromaticity per rank taping
Assembly method	Auto pick & place machine (Auto Mounter)
Soldering methods	Reflow soldering
Taping and reel	4,000pcs per reel in a 8mm width tape. (Standard) Reel diameter: ϕ 180mm
ESD	UP to 1kV (HBM)

Recommended Applications

Cellular Phone only



SW1142P

1608 (h=0.20mm) Type White LED

Color and Luminous Intensity

(Ta=25°C)

Part No.	Material	Emitted Color	Lens Color	Luminous Intensity		
				Iv (mcd)		
				MIN.	TYP.	I _f (mA)
SW1142P	InGaN	White	Diffused Pale Yellow	10	25	1

Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Absolute Maximum Ratings	Unit
Power Dissipation	P_d	14	mW
Forward Current	I_F	4	mA
Pulse Forward Current ※1	I_{FRM}	8	mA
Derating (Ta=25°C or higher)	ΔI_F	0.046	mA/°C
	ΔI_{FRM}	0.092	mA/°C
Reverse Voltage	V_R	5	V
Operating Temperature	T_{opr}	-40~+85	°C
Storage Temperature	T_{stg}	-40~+100	°C

※1 I_{FRM} Measurement condition : Pulse Width $\leq 1ms.$, Duty $\leq 1/20$.

Electro-Optical Characteristics

(Ta=25°C)

Item	Conditions	Symbol	Characteristics		Unit
Forward Voltage ※1	$I_F=1mA$	V_F	TYP.	2.8	V
			MAX.	3.1	
Reverse Current	$V_R=5V$	I_R	MAX.	100	μA
Half Intensity Angle	$I_F=1mA$	$2\theta_{1/2}$	TYP.	120(θ_x)	deg.
				120(θ_y)	
Chromaticity Coordinates	$I_F=1mA$	x	TYP.	0.27	-
		y	TYP.	0.26	-

※1 Forward Voltage Tolerance Range : $\pm 0.1V$

Luminous Intensity Rank (Unit : mcd)

(Ta=25°C)



Rank	I _V (mcd)		Condition
	MIN.	MAX.	
A	10	16	I _F =1mA
B	16	25	
C	25	40	
D	40	64	
E	64	-	

Intensity Tolerance each Rank : +/-10%

※ Please contact our sales staff concerning rank designation.

Sorting Chart for Chromaticity Coordinates

(Ta=25°C)




Chromaticity Coordinates Tolerance Each Rank : +/-0.02

Rank	Left Down Point		Left Upper Point		Right Upper Point		Right Down Point	
	x	y	x	y	x	y	x	y
A	0.243	0.187	0.209	0.221	0.228	0.252	0.262	0.218
B	0.262	0.218	0.228	0.252	0.247	0.283	0.281	0.249
C	0.281	0.249	0.247	0.283	0.267	0.314	0.300	0.280
D	0.300	0.288	0.266	0.314	0.285	0.345	0.319	0.311

※ Please contact our sales staff concerning rank designation.


Technical Data

Spectral Distribution
Relative Intensity vs. Wavelength
Condition : $T_a = 25^\circ\text{C}$, $I_F = 1\text{mA}$




Spatial Distribution Example


Condition : $T_a = 25^\circ\text{C}$



Forward Voltage vs. Forward Current
Condition : $T_a = 25^\circ\text{C}$




Forward Voltage vs. Forward Current
Condition : $T_a = -20^\circ\text{C} \sim 85^\circ\text{C}$




Technical Data

Forward Current vs. Relative Intensity
Condition : $T_a = 25^\circ\text{C}$




Derating


Ambient Temperature vs. Maximum Forward Current
Repetition Frequency : $f \geq 50\text{Hz}$, Pulse Width: $t_w \leq 1\text{msec}$



Ambient Temperature vs. Relative Intensity
Condition : $I_f = 1\text{mA}$




Ambient Temperature vs. Forward Voltage
Condition : $I_f = 0.5 \sim 10\text{mA}$



Technical Data


Dynamic Drive Rating

Duty cycle vs. Maximum Forward Current
Condition : $T_a = 25^\circ\text{C}$




Pulse Width vs. Maximum Tolerable Current Ratio

Condition : $T_a = 25^\circ\text{C}$




Forward Current vs. Chromaticity

Condition : $T_a = 25^\circ\text{C}$



Ambient Temperature vs. Chromaticity


Condition : $I_F = 1\text{mA}$



Package Dimensions


(Unit: mm)

Weight: (0.90)mg



Recommended Soldering Pattern


(Unit: mm)




Taping Specification

(Unit: mm)

Quantity: 4,000pcs/ reel (standard)



Reflow Soldering Conditions



- 1) The above profile temperature gives the maximum temperature of the LED resin surface. Please set the temperature so as to avoid exceeding this range.
- 2) Total times of reflow soldering process shall be no more than 2 times.
When the second reflow soldering process is performed, intervals between the first and second reflow should be short as possible (while allowing some time for the component to return to normal temperature after the first reflow) in order to prevent the LED from absorbing moisture.
- 3) Temperature fluctuation to the LED during the pre-heating process shall be minimized.

Manual Soldering Conditions

Iron tip temp.	350 °C	(MAX.)
----------------	--------	--------

Soldering time and frequency	3 s	(MAX.)
	1 time	(MAX.)

Handling

These types are designed chiefly for Cellular phone application, and are setting the thickness of the Product to MAX.0.25mm or less thinly. To achieve the tin type of the product, making each material thin is aimed at. Because they are inferior to our general LEDs by an external stress, please use these product types after paying attention to the following.

- 1) Please set the mounting load to Max. 2N.
- 2) Please do not increase more quantity of the soldering paste than necessary quantity
(The thickness of stencil Mask : about 100-120 μ), because the terminal area of the product is small.
- 3) Please avoid the collision of the mounting board etc. after LEDs were mounted on the substrate.
- 4) When warp of substrate is large after these were mounted on FPC etc, please use these product types after affirming these is no problem.
- 5) Please use these product types after affirming there is no problem about the mounting position etc. of product from substrate edge, when mounting them on multi-layer and multi-piece PCBs.

Reliability Testing Result

Reliability Testing Result	Applicable Standard	Testing Conditions	Duration	Failure
Room Temp. Operating Life	EIAJ ED- 4701/100(101)	Ta = 25°C, If = Maximum Rated Current	1,000 h	0/25
Resistance to Soldering Heat	EIAJ ED- 4701/300(301)	Pre-heating : 150~180°C 120s Max. Operation Heating : 230°C 40s Max. Peak Temperature : 260°C	Twice	0/25
Temperature Cycling	EIAJ ED- 4701/100(105)	Minimum Rated Storage Temperature(30min) ~Normal Temperature(15min) ~Maximum Rated Storage Temperature(30min) ~Normal Temperature(15min)	5 cycles	0/25
Wet High Temp. Storage Life	EIAJ ED- 4701/100(103)	Ta = 60±2°C, RH = 90±5%	1,000 h	0/25
High Temp. Storage Life	EIAJ ED- 4701/200(201)	Ta = Maximum Rated Storage Temperature	1,000 h	0/25
Low Temp. Storage Life	EIAJ ED- 4701/200(202)	Ta = Minimum Rated Storage Temperature	1,000 h	0/25
Vibration, Variable Frequency	EIAJ ED- 4701/400(403)	98.1m/s ² (10G), 100 ~ 2KHz sweep for 20min., XYZ each direction	2 h	0/10

Failure Criteria

Items	Symbols	Conditions	Failure criteria
Luminous Intensity	Iv	If Value of each product Luminous Intensity	Testing Min. Value < Spec. Min. Value x 0.5
Forward Voltage	V _F	If Value of each product Forward Voltage	Testing Max. Value ≥ Spec. Max. Value x 1.2
Reverse Current	I _R	V _R = Maximum Rated Reverse Voltage V	Testing Max. Value ≥ Spec. Max. Value x 2.5
Cosmetic Appearance	-	-	Occurrence of notable decoloration, deformation and cracking

Special Notice to Customers Using the Products and Technical Information Shown in This Data Sheet

- 1) The technical information shown in the data sheets are limited to the typical characteristics and circuit examples of the referenced products. It does not constitute the warranting of industrial property nor the granting of any license.
- 2) For the purpose of product improvement, the specifications, characteristics and technical data described in the data sheets are subject to change without prior notice. Therefore it is recommended that the most updated specifications be used in your design.
- 3) When using the products described in the data sheets, please adhere to the maximum ratings for operating voltage, heat dissipation characteristics, and other precautions for use. We are not responsible for any damage which may occur if these specifications are exceeded.
- 4) The products that have been described to this catalog are manufactured so that they will be used for the electrical instrument of the benchmark (OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument).
The application of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. needs a high reliability and safety, and the breakdown and the wrong operation might influence the life or the human body. Please consult us beforehand if you plan to use our product for the usages of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. except OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument.
- 5) In order to export the products or technologies described in this data sheet which are under the "Foreign Exchange and Foreign Trade Control Law," it is necessary to first obtain an export permit from the Japanese government.
- 6) No part of this data sheet may be reprinted or reproduced without prior written permission from Stanley Electric Co., Ltd.
- 7) The most updated edition of this data sheet can be obtained from the address below:
<http://www.stanley-components.com>