


4

3

2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
A1	-					



Wire Range mm' AWG	Crimp Height mm	Insulation Range mm	Terminals
0,03-0,09 32-28	0,53 ±0,03	1,4 max.	167023-2
0,20-0,56 24-20	0,77 ±0,03	1,4 max.	141603-3
0,12-0,14 26	0,72 ±0,03	0,5 - 1,0	141603-3

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±1°

MATERIAL -

FINISH -

DWN Ch.Witt 24OCT2005

CHK -

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT 330 g

CUSTOMER DRAWING

tyco
Electronics

tyco Electronics AMP GmbH
D - 64625 Bensheim

NAME
HAND TOOL ASSEMBLY FOR MODU IV
Handzange für Modu IV

SIZE A3

CAGE CODE 00779

DRAWING NO © 169481-1

RESTRICTED TO -

SCALE -

SHEET 1 of 1

REV D

AMP 1470-19 REV 31MAR2000

Pro/ENGINEER DRAWING