

VC-EMV-KV-PG21(9-13/ 9,5)

Order No.: 1854200

The illustration shows versions Pg16 and Pg21



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1854200>

EMC half screw connection Pg21, for metal housings of sizes 2-4, consisting of rubber seal, iris spring, cone disks and pressure screw, for size 1 housings, cable shielding range [mm] 5.5-9.5, cable [mm] 9-13

Commercial data

GTIN (EAN)	4017918145866
sales group	D290
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0531 KG
Catalog page information	Page 374 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
12/20/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Cable gland material	Brass
Material, pressure screw	Nickel-plated brass

Seal material	TPE
Wrench size, union nut	30 mm
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

Certificates / Approvals



Certification

GOST

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;