

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74650-1001](#)
Status: **Active**
Overview: VHDM-HSD™ Backplane Connectors
Description: 2.00mm Pitch 8-Row VHDM-HSD™ Backplane Header, Guide Pin Signal Module, Pin End Version, 60 Circuits, Pin Length 4.75mm. Series:74659 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74031-999 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Backplane Connectors
Series [74650](#)
Application Backplane
Application Tooling Documents TM-622010999
Comments No Keying Orientation
Component Type PCB Header
Overview [VHDM-HSD™ Backplane Connectors](#)
Product Name VHDM-HSD™
Style N/A
UPC 800756483580

Physical

Circuits (Loaded) 60
Circuits (maximum) 60
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal Copper-Nickel-Silicon, High Performance Alloy (HPA), Stainless Steel

Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Net Weight 7.821/g
Number of Columns 10
Number of Pairs Open Pin Field
Number of Rows 8
Orientation Vertical
PC Tail Length 2.50mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.80mm
Packaging Type Tube
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 2.00mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74650Series](#)

Mates With
HSD Daughtercards [74680](#) , [74686](#)

Use With
Daughtercard Modules

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Signal Pin Inserter	0622015700
Repair Tool	
Insertion Module	0622020205
for Advanced Mate	
Signal Header, 8-Row by 10-Wide,	
20.00mm	

Polarized to PCB
Surface Mount Compatible (SMC)
Temperature Range - Operating
Termination Interface: Style

Yes
Yes
-40 to 105°C
Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact
Data Rate
Shield Type
Shielded
Voltage - Maximum

2A
5.0 Gbps
Ground Plane Shield
Yes
120V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-74031-999
SD-74650-002

VHDM-HSD is a trademark of Amphenol Corporation

This document was generated on 01/23/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION