


RECOMMENDED PANEL MOUNTING

PANEL THICKNESS	X
0.75-1.25	19.20-19.30
1.25-2.00	19.30-19.40
2.00-3.00	19.50-19.60





SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
1a-1	OPEN	1-1b



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 15A @125VAC;
8A @250VAC.
- ▲ 5. LAMP VOLTAGE: NO LAMP
- MATERIAL:
CONTACT SURFACE: SILVER ALLOY.
TERMINAL: COPPER ALLOY W/SILVER PLATE
- ELECTRICAL LIFE: 10,000 CYCLES
- CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: >1,500V AC 1 MIN
- 2002/95/EC (ROHS) COMPLIANT.
- ▲ DENOTES CRITICAL PARAMETER.

ACTUATOR COLOR
▲ BLACKHOUSING COLOR:
▲ BLACK

E-SWITCH®



TITLE R1966DBLKBLKBS

SCALE 1.5:1

DATE 4/6/2006

DR BK

DWG M309329

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	19359	UPDATE HOUSING	11/02/10	BMA
A	15925	RELEASED FOR PRODUCTION	4/6/06	BK
REV	PCR NO	DESCRIPTION	DATE	BY