


# DIN Twin-contact Connectors

## XC5


### A Wide Variety of DIN Connectors That Conform to UL/CSA Standards.

- Fully preserves the characteristics of normal DIN connectors while increasing the number of terminals available.
- Meets world market needs with products ranging from one-piece connectors (card edge) to two-piece connectors.
- Uses a twin-contact system for high reliability and low cost.
- Lower insertion force as a result of FEM analysis techniques.
- Conform to UL standards (file no. E 103202) and CSA standards (file no. LR 62678).




### Structure


#### Twin Contacts (2-point Contact System)



### Low Insertion Force Design



The shape of the Plug contact tip is based on the DIN standard dimensions, however, a small radius, R, has been introduced between the shaft and the tip. This results in less force being required for insertion.



### Connector Styles

#### Double-row Connectors

| Model      | XC5A<br>B type                      | XC5B<br>B type                     | XC5E<br>Q type                   | XC5F<br>Q type                        |
|------------|-------------------------------------|------------------------------------|----------------------------------|---------------------------------------|
| Appearance | Plug with right-angle terminals<br> | Socket with straight terminals<br> | Plug with straight terminals<br> | Socket with right-angle terminals<br> |

#### Triple-row Connectors

| Model      | XC5C<br>C type                      | XC5D<br>C type                     | XC5G<br>R type                   | XC5H<br>R type                        |
|------------|-------------------------------------|------------------------------------|----------------------------------|---------------------------------------|
| Appearance | Plug with right-angle terminals<br> | Socket with straight terminals<br> | Plug with straight terminals<br> | Socket with right-angle terminals<br> |

### Ratings and Characteristics

|                       |                                                  |
|-----------------------|--------------------------------------------------|
| Rated current         | 2 A                                              |
| Rated voltage         | 300 VAC                                          |
| Contact resistance    | 20 mΩ max. (at 20 mV, 100 mA max.)               |
| Insulation resistance | 10 <sup>6</sup> MΩ min. (at 100 VDC)             |
| Dielectric strength   | 1,000 VAC for 1 min (leakage current: 1 mA max.) |
| Connector insertion   | 0.59 N max. per contact                          |
| Contact removal       | 0.15 N min. (with test gauge, t = 0.56 mm)       |
| Insertion durability  | 200 times                                        |
| Ambient temperature   | Operating: -55 to 125°C (with no icing)          |

### Materials and Finish

| Item      |            | Plugs                                                | Sockets                                                        |
|-----------|------------|------------------------------------------------------|----------------------------------------------------------------|
| Housings  |            | Fiber-glass reinforced PBT resin (UL94V-0)/gray      |                                                                |
| Contact s | Mating end | Brass/nickel base, 0.4-μm gold plating (See note 1.) | Phosphor bronze/nickel base, 0.4-μm gold plating (See note 1.) |
|           | Terminals  | Brass/nickel base, tin plating                       | Phosphor bronze/nickel base, tin plating                       |


- Note:**
1. For non-standard plating specifications, contact OMRON
  2. Wrap terminal contacts are made from phosphor bronze.
  3. See "Precautions" for information about Wire Wrap terminals

# XC5A Double-row Plugs, DIN B-type (Standard)

## ■ Dimensions

XC5A-□□22

(With right-angle through-hole terminals)



| No. of contacts | Dimensions (mm) |       |        |        |       |       | Coding Key positions (contact No.) |
|-----------------|-----------------|-------|--------|--------|-------|-------|------------------------------------|
|                 | A               | B     | C      | D      | E     | F     |                                    |
| 20              | 37.9            | 32.1  | 22.86  | 33.02  | 28.1  | 29.3  | 3, 8                               |
| 32              | 53.2            | 47.4  | 38.10  | 48.26  | 43.3  | 44.6  | 5, 12                              |
| 44              | 68.4            | 62.6  | 53.34  | 63.50  | 58.5  | 59.8  | 4, 9, 14, 19                       |
| 50              | 76.0            | 70.2  | 60.96  | 71.12  | 66.2  | 67.4  | 5, 10, 16, 21                      |
| 64              | 93.8            | 88.0  | 78.74  | 88.90  | 83.9  | 85.2  | 6, 13, 20, 27                      |
| 100             | 139.5           | 133.7 | 124.46 | 134.62 | 129.7 | 130.9 | 10, 20, 31, 41                     |

## ■ Ordering Information

| No. of contacts | Terminal type                      | Model     |
|-----------------|------------------------------------|-----------|
| 20*             | Right-angle through-hole terminals | XC5A-2022 |
| 32              |                                    | XC5A-3222 |
| 44*             |                                    | XC5A-4422 |
| 50*             |                                    | XC5A-5022 |
| 64              |                                    | XC5A-6422 |
| 100*            |                                    | XC5A-0122 |


\*Marked items have an increased number of contacts while following DIN standards.

# XC5B Double-row Sockets, DIN B-type (Standard)

## ■ Dimensions


### XC5B-□□21

(With straight through-hole terminals)



### XC5B-□□23

(With straight wrap terminals)



| No. of contacts | Dimensions (mm) |       |        |        |       | Coding Key slot positions (contact No.) |
|-----------------|-----------------|-------|--------|--------|-------|-----------------------------------------|
|                 | A               | B     | C      | D      | E     |                                         |
| 20              | 38.9            | 29.1  | 22.86  | 34.12  | 27.1  | 3, 8                                    |
| 32              | 54.2            | 44.4  | 38.10  | 49.36  | 42.3  | 5, 12                                   |
| 44              | 69.4            | 59.6  | 53.34  | 64.60  | 57.5  | 4, 9, 14, 19                            |
| 50              | 77.0            | 67.2  | 60.96  | 72.22  | 65.2  | 5, 10, 16, 21                           |
| 64              | 94.8            | 85.0  | 78.74  | 90.00  | 82.9  | 6, 13, 20, 27                           |
| 100             | 140.5           | 130.7 | 124.46 | 135.72 | 128.7 | 10, 20, 31, 41                          |

## ■ Ordering Information

| No. of contacts | Terminal type                   |                         |
|-----------------|---------------------------------|-------------------------|
|                 | Straight Through-hole terminals | Straight wrap terminals |
| 20*             | XC5B-2021                       | XC5B-2023               |
| 32              | XC5B-3221                       | XC5B-3223               |
| 44*             | XC5B-4421                       | XC5B-4423               |
| 50*             | XC5B-5021                       | XC5B-5023               |
| 64              | XC5B-6421                       | XC5B-6423               |
| 100*            | XC5B-0121                       | XC5B-0123               |


\*Marked items have an increased number of contacts while following DIN standards.

# XC5E Double-row Plugs, DIN Q-type (Reverse)

## ■ Dimensions


### XC5E-□□21

(With straight through-hole terminals)



### XC5E-□□23

(With straight wrap terminals)



| No. of contacts | Dimensions (mm) |       |        |        |       |       | Coding Key positions (contact No.) |
|-----------------|-----------------|-------|--------|--------|-------|-------|------------------------------------|
|                 | A               | B     | C      | D      | E     | F     |                                    |
| 20              | 38.9            | 32.1  | 22.86  | 34.12  | 28.1  | 29.3  | 3, 8                               |
| 32              | 54.2            | 47.4  | 38.10  | 49.36  | 43.3  | 44.6  | 5, 12                              |
| 44              | 69.4            | 62.6  | 53.34  | 64.60  | 58.5  | 59.8  | 4, 9, 14, 19                       |
| 50              | 77.0            | 70.2  | 60.96  | 72.22  | 66.2  | 67.4  | 5, 10, 16, 21                      |
| 64              | 94.8            | 88.0  | 78.74  | 90.00  | 83.9  | 85.2  | 6, 13, 20, 27                      |
| 100             | 140.5           | 133.7 | 124.46 | 135.72 | 129.7 | 130.9 | 10, 20, 31, 41                     |

## ■ Ordering Information

| No. of contacts | Terminal type                   |                         |
|-----------------|---------------------------------|-------------------------|
|                 | Straight through-hole terminals | Straight wrap terminals |
| 20*             | XC5E-2021                       | XC5E-2023               |
| 32              | XC5E-3221                       | XC5E-3223               |
| 44*             | XC5E-4421                       | XC5E-4423               |
| 50*             | XC5E-5021                       | XC5E-5023               |
| 64              | XC5E-6421                       | XC5E-6423               |
| 100*            | XC5E-0121                       | XC5E-0123               |


\*Marked items have an increased number of contacts while following DIN standards.

# XC5F Double-row Sockets, DIN Q-type (Reverse)

## ■ Dimensions

XC5F-□□22

(With right-angle through-hole terminals)



| No. of contacts | Dimensions (mm) |       |        |        |       | Coding Key slot positions (contact No.) |
|-----------------|-----------------|-------|--------|--------|-------|-----------------------------------------|
|                 | A               | B     | C      | D      | E     |                                         |
| 20              | 37.9            | 29.1  | 22.86  | 33.02  | 27.1  | 3, 8                                    |
| 32              | 53.2            | 44.4  | 38.10  | 48.26  | 42.3  | 5, 12                                   |
| 44              | 68.4            | 59.6  | 53.34  | 63.50  | 57.5  | 4, 9, 14, 19                            |
| 50              | 76.0            | 67.2  | 60.96  | 71.12  | 65.2  | 5, 10, 16, 21                           |
| 64              | 93.8            | 85.0  | 78.74  | 88.90  | 82.9  | 6, 13, 20, 27                           |
| 100             | 139.5           | 130.7 | 124.46 | 134.62 | 128.7 | 10, 20, 31, 41                          |

## ■ Ordering Information

| No. of contacts | Terminal type                      | Model     |
|-----------------|------------------------------------|-----------|
| 20*             | Right-angle through-hole terminals | XC5F-2022 |
| 32              |                                    | XC5F-3222 |
| 44*             |                                    | XC5F-4422 |
| 50*             |                                    | XC5F-5022 |
| 64              |                                    | XC5F-6422 |
| 100*            |                                    | XC5F-0122 |


\*Marked items have an increased number of contacts while following DIN standards.

# XC5C Triple-row Plugs, DIN C-type (Standard)

## ■ Dimensions

XC5C-□□22

(With right-angle through-hole terminals)



| No. of contacts | Dimensions (mm) |      |       |       |      |      | Coding Key positions (contact No.) |
|-----------------|-----------------|------|-------|-------|------|------|------------------------------------|
|                 | A               | B    | C     | D     | E    | F    |                                    |
| 32*             | 53.2            | 47.4 | 38.10 | 48.26 | 43.3 | 44.6 | 5, 12                              |
| 48              | 53.2            | 47.4 | 38.10 | 48.26 | 43.3 | 44.6 | 5, 12                              |
| 64*             | 93.8            | 88.0 | 78.74 | 88.90 | 83.9 | 85.2 | 6, 13, 20, 27                      |
| 96              | 93.8            | 88.0 | 78.74 | 88.90 | 83.9 | 85.2 | 6, 13, 20, 27                      |

\*Has no center row (row b).

## ■ Ordering Information

| No. of contacts | Terminal type                      | Model     |
|-----------------|------------------------------------|-----------|
| 32*             | Right-angle through-hole terminals | XC5C-3222 |
| 48              |                                    | XC5C-4822 |
| 64*             |                                    | XC5C-6422 |
| 96              |                                    | XC5C-9622 |


\*Has no center row (row b).

# XC5D Triple-row Sockets, DIN C-type (Standard)

## ■ Dimensions


### XC5D-□□21

(With straight through-hole terminals)



### XC5D-□□23

(With straight wrap terminals)



| No. of contacts | Dimensions (mm) |      |       |       |      | Coding Key slot positions (contact No.) |
|-----------------|-----------------|------|-------|-------|------|-----------------------------------------|
|                 | A               | B    | C     | D     | E    |                                         |
| 32*             | 54.2            | 44.4 | 38.10 | 49.36 | 42.3 | 5, 12                                   |
| 48              | 54.2            | 44.4 | 38.10 | 49.36 | 42.3 | 5, 12                                   |
| 64*             | 94.8            | 85.0 | 78.74 | 90.00 | 82.9 | 6, 13, 20, 27                           |
| 96              | 94.8            | 85.0 | 78.74 | 90.00 | 82.9 | 6, 13, 20, 27                           |

\*Has no center row (row b).

## ■ Ordering Information

| No. of contacts | Terminal type                   |                         |
|-----------------|---------------------------------|-------------------------|
|                 | Straight through-hole terminals | Straight wrap terminals |
| 32*             | XC5D-3221                       | ---                     |
| 48              | XC5D-4821                       | XC5D-4823               |
| 64*             | XC5D-6421                       | XC5D-6423               |
| 96              | XC5D-9621                       | XC5D-9623               |


\*Has no center row (row b).

# XC5G Triple-row Plugs, DIN R-type (Reverse)

## ■ Dimensions



XC5G-□□21

(With straight through-hole terminals)



XC5D-□□23

(With straight wrap terminals)



| No. of contacts | Dimensions (mm) |      |       |       |      |      | Coding Key positions (contact No.) |
|-----------------|-----------------|------|-------|-------|------|------|------------------------------------|
|                 | A               | B    | C     | D     | E    | F    |                                    |
| 48              | 54.2            | 47.4 | 38.10 | 49.36 | 43.3 | 44.6 | 5, 12                              |
| 64*             | 94.8            | 88.0 | 78.74 | 90.00 | 83.9 | 85.2 | 6, 13, 20, 27                      |
| 96              | 94.8            | 88.0 | 78.74 | 90.00 | 83.9 | 85.2 | 6, 13, 20, 27                      |

\*Has no center row (row b).

## ■ Ordering Information

| No. of contacts | Terminal type                   |                         |
|-----------------|---------------------------------|-------------------------|
|                 | Straight through-hole terminals | Straight wrap terminals |
| 48              | XC5G-4821                       | XC5G-4823               |
| 64*             | XC5G-6421                       | XC5G-6423               |
| 96              | XC5G-9621                       | XC5G-9623               |


\*Has no center row (row b).

## XC5H Triple-row Sockets, DIN R-type (Reverse)

## ■ Dimensions

XC5H-□□22

(With right-angle through-hole terminals)



| No. of contacts | Dimensions (mm) |      |       |       |      | Coding Key slot positions (contact No. |
|-----------------|-----------------|------|-------|-------|------|----------------------------------------|
|                 | A               | B    | C     | D     | E    |                                        |
| 48              | 53.2            | 44.4 | 38.10 | 48.26 | 42.3 | 5, 12                                  |
| 64*             | 93.8            | 85.0 | 78.74 | 88.90 | 82.9 | 6, 13, 20, 27                          |
| 96              | 93.8            | 85.0 | 78.74 | 88.90 | 82.9 | 6, 13, 20, 27                          |

\*Has no center row (row b).



## ■ Ordering Information

| No. of contacts | Terminal type                            | Model     |
|-----------------|------------------------------------------|-----------|
| 48              | Right-angle<br>through-hole<br>terminals | XC5H-4822 |
| 64*             |                                          | XC5H-6422 |
| 96              |                                          | XC5H-9622 |

\*Has no center row (row b).

# Tools and Accessories (Sold Separately)

## Coding Cutter XY2D-0001




Cut the Coding Key on the Plug and insert the Coding Key in the Coding Key slots on the Socket to prevent improper insertion of the Plug into the Socket.


1. Cut the Coding Key(s) in the slot in the plug housing wall with the special cutting tool (XY2D-0001).

**Note:** Coding Cutters may not work with some DIN-style connector combinations. In that case, contact your OMRON representative.

## Coding Key XC5Z-0001



Material: PBT resin (UL94HB)/white




2. Insert the special Coding Key (XC5Z-0001) into the Coding Key slots in the housing wall of the corresponding Socket.

**Note:** 1. Each XC5Z-0001 has four Coding Keys.

2. Coding Keys may not work with some DIN-style connector combinations. In that case, contact your OMRON representative.

## Temporary Fastening Pins XC5Z-0002

(For use with 1.6-mm boards)



Fastening pins (XC5Z-0002) are used to keep the connector flush against the board during automated soldering.

**Note:** 1. For the XC5A, XC5F, XC5C, and XC5H.


2. Temporary fastening pins cannot be used with DIN-style connectors.

## Dust Cover XC5T-962

(For DIN41612 C- or R-type Triple-row Plugs with 64 or 96 contacts)

## XC5T-963

(For DIN41612 C- or R-type Triple-row Sockets with 64 or 96 contacts)



Material: Polyamide resin (UL94V-2)/white

This cover is for protection against dust only, and should not be used for flux protection during automated soldering.

# Mating Diagrams

|                       | Vertical (Standard) | Vertical (Reverse) | Stacking (See note.) | Horizontal (See note.) |
|-----------------------|---------------------|--------------------|----------------------|------------------------|
| Double-row Connectors |                     |                    |                      |                        |
| Triple-row Connectors |                     |                    |                      |                        |


**Note:** By combining a Standard and a Reverse Connector, stacking and horizontal connections can be made. In this case, the triangular marks (terminal number 1) on the Plug and the Socket will not match.

# Precautions

## ■ Correct Use

### Basic Mating Dimensions

Mating dimensions for all Connectors should be as shown in the following diagram.



α: 3.55 mm

The distance between the center line of the mounting holes on the mother board and the daughter board. (This center line is shifted 0.3 mm toward row a from row b.)

β: 2.54 mm

The distance between the mounting holes on the daughter board and row a.



γ: 5.3 mm

The distance between the edge of the daughter board and row a.

δ: 12.4 to 14.2 mm

To ensure reliability, be sure to keep the Connectors within these dimensions when mounting.

The allowable margins for mating the Connectors are shown below.



### Applicable Wrap Post Wire Sizes

AWG30, AWG28, AWG26, or AWG24  
(Solid wire: 0.25 to 0.51 mm dia.)


### Wrap Post Length

3 wires

### Soldering

#### Automated Soldering

Use masking tape to mask Right-angle Connectors before automated soldering.



(Recommended tape: 3M Sumitomo #214)

#### Automated Soldering Conditions (Jet Flow)

1. Soldering temperature: 250±5°C
2. Continuous soldering time: Within 5 s

A large grid of 100 small squares, each containing a unique combination of symbols (plus, minus, multiplication, division, equals, and less than or greater than signs) and numbers (1 through 9). The symbols and numbers are arranged in a way that suggests a mathematical or logical pattern, possibly related to the 'Mathematical Symbols' mentioned in the text.

All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at [http://www.components.omron.com/components/web/webfiles.nsf/sales\\_terms.html](http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html)

**ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.**

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

---

**OMRON**<sup>®</sup>

**OMRON ELECTRONIC  
COMPONENTS LLC**

55 E. Commerce Drive, Suite B  
Schaumburg, IL 60173

**847-882-2288**

**OMRON ON-LINE**

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>