



PRODUCT NUMBER

20020035-XXXXXXLF

20020035-□□□□B0□LF

PITCH

G: 5.00 mm

H: 5.08 mm

POLES

02: 2 POLES

03: 3 POLES

24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

PROPERTY TABLE

PROPERTY TABLE					
FCI SERIES NAME		35-500	35-508		
PITCH (mm)		5.00	5.08		
VOLTAGE RATING (VAC)		300	300		
CURRENT RATING (A)		10	10		
APPLICABLE WIRE RANGE (AWG)		1-WIRE	12~26	12~26	
		2-WIRE	NA	NA	
WIRE CROSS SECTION (mm ²)		SOLID	1-WIRE	2.5	2.5
			2-WIRE	NA	NA
		STRANDED	1-WIRE	2.5	2.5
			2-WIRE	NA	NA
OPENING CONTACT HOUSING(mm ²)			2.4x3.0	2.2x3.0	
WIRE STRIP LENGTH(mm)			8~9	8~9	
WITHSTANDING VOLTAGE (kV)			1.6	1.6	
OPERATING TEMP. (°C)			-40~+115	-40~+115	
POLES AVAILABLE			02~24	02~24	
SAFETY CERTIFICATE					

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 INSULATING LEVER: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-3 WIRE GUARD : STAINLESS STEEL.
- 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
- 1-5 SCREW: STEEL, ZINC PLATED.

2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.




3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.

4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.


5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code				surface	tolerance	projection	product family		
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
A	T11-0004	WL	011811	angles	X.±0.5		TERMINAL BLOCK		
B	T-005306	WL	082311	tolerances	X.X±0.3		PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT W/FLANGE		
				X*±1*	X.XX±0.1	scale	sheet 1 of 3		
				dr	WENDY CHEN	113010	dwg no		
				engr	JASON HSU	113010	20020035		
				chr	JASON HSU	113010	A4		
				appd	JASON HSU	113010	type		
							CUSTOMER Drawing		
sheet index	revision sheet	B	B	B	B	B			
		1	2	3					

PRODUCT NUMBER	SERIES NAME	PITCH
20020035-GXXXXXXLF	35-500	5.00 mm



SECTION A-A




N = Number of poles
 DIM. L = $(N \times 5.00 [.197]) + 0.6 [.024]$
 DIM. P = $(N - 1) \times 5.00 [.197]$
 DIM. T = $(N \times 5.00 [.197]) + 10.02 [.394]$
 DIM. K = $(N + 1) \times 5.00 [.197]$

POLES	DIM. L & P	DIM. T & K
2-6p	$\pm 0.15 [.006]$	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$	$\pm 0.25 [.010]$
13-18p	$\pm 0.25 [.010]$	$\pm 0.30 [.012]$
19-24p	$\pm 0.30 [.012]$	$\pm 0.40 [.016]$

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B				angles	$X \pm 0.5$ $X.X \pm 0.3$	scale	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT W/FLANGE
				$X \pm 1^\circ$	$X.XX \pm 0.1$		dwg no
				dr	WENDY CHEN	113010	sheet 2 of 3
				enr	JASON HSU	113010	size
				chr	JASON HSU	113010	A4
				appd	JASON HSU	113010	type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020035-HXXXXXXLF	35-508	5.08 mm



N = Number of poles
 DIM. L = $(N \times 5.08 [.200]) + 0.5 [.020]$
 DIM. P = $(N - 1) \times 5.08 [.200]$
 DIM. T = $(N \times 5.08 [.200]) + 0.16 [.400]$
 DIM. K = $(N + 1) \times 5.08 [.200]$

POLES	DIM. L & P	DIM. T & K
2-6p	$\pm 0.15 [.006]$	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$	$\pm 0.25 [.010]$
13-18p	$\pm 0.25 [.010]$	$\pm 0.30 [.012]$
19-24p	$\pm 0.30 [.012]$	$\pm 0.40 [.016]$

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B				angles X°±1°	X.±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, DOWNSIDE CONTACT W/FLANGE
		dr	WENDY CHEN	113010			dwg no
		enr	JASON HSU	113010			sheet 3 of 3
		chr	JASON HSU	113010			size
		appd	JASON HSU	113010			A4
sheet index	revision sheet						type
							CUSTOMER Drawing