






ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN		2006/03/09 2006/03/09 2006/03/10	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 □=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS METRIC	⊙ □ THIRD ANGLE PROJECTION	TITLE DVI_D(F)-DFP(M) ADAPTER	
						mm	INCH	DRAWN BY PDAI	DATE 2006/03/07					
					4 PLACES	± ---	± ---	CHECKED BY ZXDENG	DATE 2006/03/07					
					3 PLACES	± ---	± ---	APPROVED BY	DATE					
					2 PLACES	± ---	± ---	BORON	2006/03/07	moLEX MOLEX INCORPORATED				
					1 PLACE	± ---	± ---	ANGULAR ±---°		MATERIAL NO. 88741-9300		DOCUMENT NO. SD-88741-014		SHEET NO. 1 OF 2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							SIZE A4		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

7	6	5	4	3	2	1																																																										
E	NOTE:1. PLASTIC COVER: SNOW WHITE UL GRADE ABS. 2. DVI CONNCEOTOR SPECIFICATION 2.1 REFER TO PRODUCT SPEC. PS-74320-001 2.2 CONTACT PLATING: AU FLASH. 3. ELECTRICAL PERFORMANCE 3.1 INSULATION RESISANCE: 20 M Ohms Min 3.2 DIELECTRIC STRENGTH: 300V DC FOR 10 MILLISECONDS. 4. ADAPTOR SPECIFICATION 4.1 REFER TO PRODUCT SPEC. PS8874I-8800. 5. THIS PRODUCT MUST MEET MX RoHS COMPLIANCE.			7. MATERIAL LIST			E																																																									
D				<table><tr><td>F</td><td>SNOW WHITE LATCH 887899305</td></tr><tr><td>E</td><td>DFP20 CONNECTOR 887899294</td></tr><tr><td>D</td><td>DVI(F) TO DFP(M) ADAPTER BOTTOM COVER 887899307</td></tr><tr><td>C</td><td>DVI(F) TO DFP(M) ADAPTER TOP COVER 887899302</td></tr><tr><td>B</td><td>DVID FEMALE SCREW 887806066</td></tr><tr><td>A</td><td>DVID FEMALE CONNECTOR 743207000</td></tr><tr><td>ITEM</td><td>DESCRIPTION</td></tr></table>			F	SNOW WHITE LATCH 887899305	E	DFP20 CONNECTOR 887899294	D	DVI(F) TO DFP(M) ADAPTER BOTTOM COVER 887899307	C	DVI(F) TO DFP(M) ADAPTER TOP COVER 887899302	B	DVID FEMALE SCREW 887806066	A	DVID FEMALE CONNECTOR 743207000	ITEM	DESCRIPTION	D																																											
F	SNOW WHITE LATCH 887899305																																																															
E	DFP20 CONNECTOR 887899294																																																															
D	DVI(F) TO DFP(M) ADAPTER BOTTOM COVER 887899307																																																															
C	DVI(F) TO DFP(M) ADAPTER TOP COVER 887899302																																																															
B	DVID FEMALE SCREW 887806066																																																															
A	DVID FEMALE CONNECTOR 743207000																																																															
ITEM	DESCRIPTION																																																															
C	6. CONNECTION DIAGRAM						C																																																									
B	<table><tr><td>SHIELD</td><td>SHIEDL</td><td>GROUND</td></tr><tr><td>PIN 24</td><td>PIN 6</td><td>TMDS CLOCK-</td></tr><tr><td>PIN 23</td><td>PIN 5</td><td>TMDS CLOCK+</td></tr><tr><td>PIN 22</td><td>PIN 4</td><td>TMDS CLOCK SHIELD</td></tr><tr><td>PIN 19</td><td>PIN 14</td><td>TMDS DATA 0 SHIELD</td></tr><tr><td>PIN 18</td><td>PIN 15</td><td>TMDS DATA 0+</td></tr><tr><td>PIN 17</td><td>PIN 16</td><td>TMDS DATA 0-</td></tr><tr><td>PIN 16</td><td>PIN 18</td><td>HOT PLUG DETECT</td></tr><tr><td>PIN 15</td><td>PIN 7</td><td>GROUND(+5V & HV SYNC.)</td></tr><tr><td>PIN 14</td><td>PIN 8</td><td>POWER +5V</td></tr><tr><td>PIN 11</td><td>PIN 3</td><td>TMDS DATA 1 SHIELD</td></tr><tr><td>PIN 10</td><td>PIN 1</td><td>TMDS DATA 1+</td></tr><tr><td>PIN 9</td><td>PIN 2</td><td>TMDS DATA 1-</td></tr><tr><td>PIN 7</td><td>PIN 19</td><td>DDC DATA</td></tr><tr><td>PIN 6</td><td>PIN 20</td><td>DDC CLOCK</td></tr><tr><td>PIN 3</td><td>PIN 13</td><td>TMDS DATA 2 SHIELD</td></tr><tr><td>PIN 2</td><td>PIN 11</td><td>TMDS DATA 2+</td></tr><tr><td>PIN 1</td><td>PIN 12</td><td>TMDS DATA 2-</td></tr><tr><td>DVI_D(F)</td><td>DFP(M)</td><td>CABLE FUNCTION</td></tr></table>			SHIELD	SHIEDL	GROUND	PIN 24	PIN 6	TMDS CLOCK-	PIN 23	PIN 5	TMDS CLOCK+	PIN 22	PIN 4	TMDS CLOCK SHIELD	PIN 19	PIN 14	TMDS DATA 0 SHIELD	PIN 18	PIN 15	TMDS DATA 0+	PIN 17	PIN 16	TMDS DATA 0-	PIN 16	PIN 18	HOT PLUG DETECT	PIN 15	PIN 7	GROUND(+5V & HV SYNC.)	PIN 14	PIN 8	POWER +5V	PIN 11	PIN 3	TMDS DATA 1 SHIELD	PIN 10	PIN 1	TMDS DATA 1+	PIN 9	PIN 2	TMDS DATA 1-	PIN 7	PIN 19	DDC DATA	PIN 6	PIN 20	DDC CLOCK	PIN 3	PIN 13	TMDS DATA 2 SHIELD	PIN 2	PIN 11	TMDS DATA 2+	PIN 1	PIN 12	TMDS DATA 2-	DVI_D(F)	DFP(M)	CABLE FUNCTION				B
SHIELD	SHIEDL	GROUND																																																														
PIN 24	PIN 6	TMDS CLOCK-																																																														
PIN 23	PIN 5	TMDS CLOCK+																																																														
PIN 22	PIN 4	TMDS CLOCK SHIELD																																																														
PIN 19	PIN 14	TMDS DATA 0 SHIELD																																																														
PIN 18	PIN 15	TMDS DATA 0+																																																														
PIN 17	PIN 16	TMDS DATA 0-																																																														
PIN 16	PIN 18	HOT PLUG DETECT																																																														
PIN 15	PIN 7	GROUND(+5V & HV SYNC.)																																																														
PIN 14	PIN 8	POWER +5V																																																														
PIN 11	PIN 3	TMDS DATA 1 SHIELD																																																														
PIN 10	PIN 1	TMDS DATA 1+																																																														
PIN 9	PIN 2	TMDS DATA 1-																																																														
PIN 7	PIN 19	DDC DATA																																																														
PIN 6	PIN 20	DDC CLOCK																																																														
PIN 3	PIN 13	TMDS DATA 2 SHIELD																																																														
PIN 2	PIN 11	TMDS DATA 2+																																																														
PIN 1	PIN 12	TMDS DATA 2-																																																														
DVI_D(F)	DFP(M)	CABLE FUNCTION																																																														
A	<table><tr><td rowspan="5">ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN</td><td rowspan="5">2006/03/09 2006/03/09 2006/03/10</td><td rowspan="5">DESCRIPTION REV</td><td rowspan="5">QUALITY SYMBOLS ▽=0 ▽=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM/IN</td><td>SCALE ---</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES</td><td>mm</td><td>INCH</td><td>DRAWN BY PDAI</td><td>DATE 2006/03/07</td><td colspan="2" rowspan="4">TITLE DVI_D(F)-DFP(M) ADAPTER</td></tr><tr><td>3 PLACES</td><td>mm</td><td>INCH</td><td>CHECKED BY ZXDENG</td><td>DATE 2006/03/07</td></tr><tr><td>2 PLACES</td><td>mm</td><td>INCH</td><td>APPROVED BY BORON</td><td>DATE 2006/03/07</td></tr><tr><td>1 PLACE</td><td>mm</td><td>INCH</td><td>MATERIAL NO. 88741-9300</td><td>DOCUMENT NO. SD-88741-014</td><td>SHEET NO. 2 OF 2</td></tr><tr><td colspan="8">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A4</td><td colspan="4">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>			ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN	2006/03/09 2006/03/09 2006/03/10	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	4 PLACES	mm	INCH	DRAWN BY PDAI	DATE 2006/03/07	TITLE DVI_D(F)-DFP(M) ADAPTER		3 PLACES	mm	INCH	CHECKED BY ZXDENG	DATE 2006/03/07	2 PLACES	mm	INCH	APPROVED BY BORON	DATE 2006/03/07	1 PLACE	mm	INCH	MATERIAL NO. 88741-9300	DOCUMENT NO. SD-88741-014	SHEET NO. 2 OF 2	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							A										
ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN	2006/03/09 2006/03/09 2006/03/10	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0					GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS METRIC			THIRD ANGLE PROJECTION																																																
								4 PLACES	mm	INCH	DRAWN BY PDAI	DATE 2006/03/07	TITLE DVI_D(F)-DFP(M) ADAPTER																																																			
									3 PLACES	mm	INCH	CHECKED BY ZXDENG					DATE 2006/03/07																																															
									2 PLACES	mm	INCH	APPROVED BY BORON			DATE 2006/03/07																																																	
				1 PLACE	mm	INCH	MATERIAL NO. 88741-9300		DOCUMENT NO. SD-88741-014	SHEET NO. 2 OF 2																																																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																							
tb_frame_A4_P_ME_T Rev. D 2004/04/02			6	5	4	3	2	1																																																								