


THIS DRAWING IS A CONTROLLED DOCUMENT

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA


Restricted to: General Release

USED ON



Left Side

Connector(s): MT-RJ SECURE (No Pins)
Mode: MM
Housing Color: Blue
Geom. Spec: 115-1215



Fiber Path

Fiber A -  B
Fiber B -  A

- Notes:
- 1 IL tested at 1300nm.
 - 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 3 Label 2 will not be present on any cable assembly less than 5 meters long.
 - 4 Includes dust caps (not shown on print).

Right Side

Connector(s): ST
Mode: MM
Housing Color: N/A
Geom. Spec: N/A

LOC
CE
DIST
16

	B	Rev Per EC#	06-022379	9/27/2006	-	MK			
P	LTR	REVISION RECORD	DATE	DIN	APVD				

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
	0 P.L.C. ± -
	1 P.L.C. ± -
	2 P.L.C. ± -
	3 P.L.C. ± -
	4 P.L.C. ± -

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to ST		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6278884		SHEET
			1 of 3
			REV B

Customer Print

AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS AND IT IS NOT TO BE REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Blue		ST	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278884-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6278884-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6278884-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6278884-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6278884-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6278884-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6278884-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6278884-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6278884-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6278884-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6278884-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6278884-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6278884-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6278884-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6278884-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6278884-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6278884-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6278884-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6278884-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6278884-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6278884-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6278884-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6278884-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6278884-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6278884-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6278884-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6278884-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6278884-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6278884-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6278884-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6278884-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6278884-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6278884-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6278884-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6278884-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6278884-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6278884-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6278884-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6278884-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6278884-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6278884-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Blue	6
0.0139	sheet	Leg Label - "A"	7
0.0139	sheet	Leg Label - "B"	8
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	9
2	piece	Crimp Eyelet	10
2	piece	ST Short Boot - 1.6 to 2.0mm, Beige	11
2	piece	ST Connector, Ceramic, Metal Nut	12
2	piece	2.5mm ferrule cover	13
2	piece	PVC Build-up tubing	14
AR	meter	2 fiber, 50/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	15
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	16
2	piece	Trace Label	17

B	Rev Per EC#	06-022379	9/27/2006	-	MK		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± 1 P.L.C. ± 2 P.L.C. ± 3 P.L.C. ± 4 P.L.C. ±
Customer Print	

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Michael Kepko			
APVD	Michael Kepko			
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to ST				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 6278884	2 of 3	B

8 7 6 5 4 3 2 1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B	Rev Per EC#	06-022379	9/27/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters			
Ø	9 P.L.C.	±	-
□	1 P.L.C.	±	-
□	2 P.L.C.	±	-
□	3 P.L.C.	±	-
□	4 P.L.C.	±	-

Customer Print

DW		Cable Assy Configurator		MATERIAL		HEAT TREAT			
CHK		Michael Kepko		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608					
APVD		Michael Kepko							
NAME								FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to ST	
SCALE		SIZE		DRAWING NO		SHEET		REV	
NTS		A2		C- 6278884		3 of 3		B	