


MATERIAL#	APPLICATION	SLEEVING	AWG	LENGTH(FT.)	TOL (+/- IN.)	PINOUT
74569-1007	Ctrl to Ctrl	YES	30	1.6	0.6	PINOUT1
74569-1008	Ctrl to Ctrl	YES	28	3.3	0.6	PINOUT1
74569-1009	Ctrl to BP	YES	30	1.6	0.6	PINOUT2
74569-1010	Ctrl to BP	YES	28	3.3	0.6	PINOUT2
74569-1011	Symmetric	YES	30	1.6	0.6	PINOUT3
74569-1012	Symmetric	YES	28	3.3	0.6	PINOUT3



NOTES:

1. MATERIAL:

OVER MOLD - POLYBUTYLENE TEREPHTHALATE (PBT), 94-V0,
GLASS FILLED 30%.

LATCH - STAINLESS STEEL ALLOY.

CABLE -

SIGNALS PVC INSULATION

SOLID COPPER SIGNAL AND DRAIN.

INNER DIELECTRIC IS POLYOLEFIN

TWIN-AX SHIELD IS ALUMINIZED POLYESTER FOIL.

PCB - FR4

2. PRODUCT TO PERFORM PER

PRODUCT SPECIFICATION: PS-79536-001.

3. PRODUCT SERIES 79536 MATES TO 75783 (RIGHT ANGLE),

75794 (VERTICAL) AND 47077 (SFF 8484) SERIES MATES TO
87861 SERIES.

4. THIS PRODUCT CONFORMS TO THE MECHANICAL

DIMENSIONING AND ELECTRICAL

PERFORMANCE REQUIREMENTS OF

SFF-8086, SFF-8087

AND SFF-8484.

5. MINIMUM RECOMMENDED BEND RADIUS 28 MM.

6. ASSEMBLY IS RoHS COMPLIANT.


7. LABEL NOTE:

MOLEX


74569-10XX

MADE IN CHINA

YY/WW



ENTER DESCRIPTION EC NO: USY2006-0287 DRW:KPHILLIPS 2006/03/29 CHKD:T.HALL 2006/04/10 APPR:DOOYE 2006/04/12	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 			
				mm	INCH	DRAWN BY JERWIN	DATE 2005/09/01	TITLE IPASS (MINI-SAS) INTERNAL CABLE 36 CKT, 4X TO 8484 FOR VAR				
			4 PLACES	± ---	± ---	CHECKED BY T. HALL	DATE 2005/09/01					
			3 PLACES	± ---	± .01							
			2 PLACES	± 0.25	± ---	APPROVED BY D.DOYE	DATE 2005/09/01	MOLEX INCORPORATED				
			1 PLACE	± ---	± ---							
			ANGULAR ± 1 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-74569-002		1 OF 4		
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74569-1011