


**Part Number: 76871-0002**
**Quad Small Form-factor Pluggable Plus (QSFP) Assembly, Stacked 2 by 1 with Elastomer Gaskets and Light Pipes, Tin-Lead**

*Series image - Reference only*

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	Contact Molex
<b>Series:</b>	<a href="#">76871</a>
<b>Category:</b>	I/O Connectors
<b>Overview:</b>	<a href="#">Quad Small Form-factor Pluggable Plus (QSFP+) Interconnect Solution</a>

**Use With:**
[74757](#), [74758](#)
**Product Environmental Compliance**
[EU RoHS](#): RoHS Compliant by Exemption

[China RoHS](#)
[REACH SVHC](#): Contains SVHC: No

[Low-Halogen Status](#): Not Low-Halogen

**Part Detail**
**General**

<b>Status</b>	Obsolete
Category	I/O Connectors
Series	<a href="#">76871</a>
Application	Module-to-Board
Component Type	Receptacle
Overview	<a href="#">Quad Small Form-factor Pluggable Plus (QSFP+) Interconnect Solution</a>
Product Name	QSFP
Type	N/A

**Physical**

Boot Color	N/A
Circuits (Loaded)	76
Circuits (maximum)	76
Circuits Detail	76
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.25mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

**Electrical**
**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Shield Type	EMI Gasket
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

**Agency Certification**
**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-76870-0002, AS-76870-001
Product Specification	PS-76870-001
Sales Drawing	SD-76871-0002, SD-76871-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Global**

Description	Product #
Multi-Port Connector Insertion Tool	<a href="#"><u>0622030380</u></a>
Multi-Port Connector Extraction Tool	<a href="#"><u>0622030390</u></a>

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)