

August 2012

SEMICONDUCTOR GENERAL CATALOG

Sensors/Image Pickup Devices

Image Sensors
Magnetic Sensors

Image Sensors

CCD Linear Image Sensors

Part Number	Style	Photosensitive Pixels (Picture Element)			Sensitivity (Typ.) (V/lx-s)	Data Rate (Max) (MHz)	Other Features
		Type/Lamp	Effective Pixels	Size (μm)			
TCD1103GFG ☆	Lens reduction type	B/W	1500	5.5 x 64	79	2	Digital shutter Sample-and-hold
TCD1254GFG ☆			2500	5.25 x 64	103	2	
TCD1706DG			7400	4.7 x 4.7	15	25 x 4	
TCD1710DG			7500 x 2 Line		15	15 x 2	
TCD1711DG			7450		15	30 x 2	
TCD2563BFG		Color	5340 x 4 Line	5.25 x 8.4	R:22.6, G:28.0, B:17.0	Color:25, B/W:25 x 2	TDI
TCD2564DG			5400 x 3 Line	7 x 7	R:9.6, G:8.9, B:3.8	30 x 2	
TCD2565BFG			5400 x 4 Line	5.25 x 5.25	R:10.2, G:9.2, B:4.0, B/W:14.7	Color:35, B/W:35 x 2	2-line distance (color)
TCD2566BFG			5340 x 4 Line	Color:5.25 x 6.825 B/W:5.25 x 8.4	R:31.7, G:32.8, B:19.9, B/W:59.4	Color:35, B/W:35 x 2	TDI
TCD2711DG			7500 x 3 Line	9.325 x 9.325	R:18.9, G:20.4, B:13.4	35 x 2	
TCD2712DG			7500 x 3 Line	9.325 x 9.325	R:14.1, G:22.2, B:9.1	30 x 4	
TCD2713DG			7500 x 4 Line	9.325 x 9.325	R:13.1, G:18.4, B:7.6, B/W:23.8	Color:35 x 2, B/W:35 x 4	2-line distance (color)
TCD2715DG			7450 x 3 Line	4.7 x 4.7	R:5.7, G:5.2, B:2.2	30	
TCD2716DG			7450 x 3 Line	4.7 x 4.7	R:9.1, G:8.5, B:3.8	30 x 2	
TCD2717BFG			7500 x 4 Line	4.7 x 4.7	R:8.0, G:7.2, B:3.1	Color:35, B/W:35 x 2	2-line distance (color)
TCD2720BFG			7500 x 4 Line	4.7 x 4.7	R:8.0, G:7.2, B:5.4, B/W:11.5	Color:35 x 2, B/W:35 x 4	2-line distance (color)
TCD2722BFG			7450 x 3 Line	4.7 x 4.7	R:7.2, G:6.9, B:2.9	35 x 2	
TCD2915BFG			10680 x 3 Line	2.625 x 8.4	R:5.6, G:7.0, B:4.3	20	
TCD2916BFG			10680 x 4 Line		R:6.7, G:7.0, B:4.3, B/W-H:20.6, B/W-H:12.4	Color:25, B/W:25 x 2	
TCD2964BFG			21360 x 6 Line	2 x 4	R:1.3, G:1.5, B:0.7	10	Overflow drain

☆: Dry-packed

- The products shown in bold are also manufactured in offshore fabs.
- Contact the Toshiba sales representative for information about RoHS compliance before you purchase any components.

CMOS Area Image Sensors

Part Number	Package	Features			
		Optical Format (Inches)	Total Pixel Count (PIX)	Color/Mono	Digital Signal Processor
TCM9001MD	Camera module	1/10	648 (H) x 492 (V) (VGA)	Color (RGB)	Yes
TCM9200MD	Camera module	1/4	1648 (H) x 1216 (V) (2.0M)	Color (RGB)	Yes

- Contact the Toshiba sales representative for information about RoHS compliance before you purchase any components.

	Package	Resolution (DPI)	Applications	Remarks
	16PIN GLCC	—	Barcode readers	
	22PIN Cerdip	A3 600	Photocopiers, scanners	
	22PIN CLCC	A4 600	Photocopiers, color scanners	
	22PIN Cerdip			
	22PIN CLCC			
	22PIN CLCC			
	68PIN Cerdip	A3 600		
	22PIN Cerdip			
	32PIN CLCC			
	32PIN CLCC			A3 600
	32PIN CLCC	A3 600		
	22PIN CLCC	A4 1200		
	32PIN CLCC	A4 4800	Color scanners	

Magnetic Sensors

Magnetic Sensors (Digital Output)

Part Number	Pole	Output	Supply Voltage V _{CC} (V)			Supply Current @ V _{CC} = 2.3 to 2.7 V						Magnetic Flux Density						Operating Frequency (Hz)			Package
						Average Current I _{CC} (μA)			Operating Current I _{CCON} (mA)			Operating Point B _{ON} (mT)			Releasing Point B _{OFF} (mT)						
		min	typ.	max	min	typ.	max	min	typ.	max	min	typ.	max	min	typ.	max	min	typ.	max		
TCS10SPU	S	Push-pull	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	UFV
TCS10SLU		Open-drain	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS11SLU		Open-drain with inverting output	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS10NPU	N	Push-pull	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS10NLU		Open-drain	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS11NLU		Open-drain with inverting output	2.3	—	3.6	—	5.5	9.5	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS10DPU	S/N	Push-pull	2.3	—	3.6	—	8.5	13.2	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS10DLU		Open-drain	2.3	—	3.6	—	8.5	13.2	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS11DLU		Open-drain with inverting output	2.3	—	3.6	—	8.5	13.2	—	0.7	1.3	—	1.8	2.5	0.3	0.8	—	—	25	—	
TCS20DPR		Push-pull	2.3	—	3.6	—	▲8.5	—	—	▲0.8	—	—	3.4	4.4	0.9	2.0	—	—	25	—	SOT-23F
TCS20DLR		Open-drain	2.3	—	3.6	—	▲8.5	—	—	▲0.8	—	—	3.4	4.4	0.9	2.0	—	—	25	—	
TCS20DPC		Push-pull	2.3	—	3.6	—	▲8.5	—	—	▲0.8	—	—	2.6	3.8	0.3	1.2	—	—	25	—	CST6C
TCS20DLC		Open-drain	2.3	—	3.6	—	▲8.5	—	—	▲0.8	—	—	2.6	3.8	0.3	1.2	—	—	25	—	
TCS30DPC*	Push-pull	1.6	—	3.6	—	●0.4	●9.5	—	●0.4	●0.9	—	—	4.4	0.5	—	—	—	25	—		
TCS30DLC*	Open-drain	1.6	—	3.6	—	●4.6	●4.5	—	●0.4	●0.9	—	—	4.4	0.5	—	—	—	25	—		

Note: The UFV package measures 2.0 x 2.1 x 0.7 mm and is a variant of SC-88A.

*: New product

●: When V_{CC} = 1.6 V

▲: When V_{CC} = 2.5 V

• Contact the Toshiba sales representative for information about RoHS compliance before you purchase any components.

**Toshiba America
Electronic Components, Inc.**

- Irvine, Headquarters
Tel: (949)623-2900 Fax: (949)474-1330
- Buffalo Grove (Chicago)
Tel: (847)484-2400 Fax: (847)541-7287
- Duluth/Atlanta
Tel: (770)931-3363 Fax: (770)931-7602
- El Paso
Tel: (915)771-8156
- Marlborough
Tel: (508)481-0034 Fax: (508)481-8828
Tel: (508)303-5041 Fax: (508)481-8890

- Parsippany
Tel: (973)541-4715 Fax: (973)541-4716
- San Jose
Tel: (408)526-2400 Fax: (408)526-2410
- Wixom (Detroit)
Tel: (248)347-2607 Fax: (248)347-2602

Toshiba Electronics do Brasil Ltda.
Tel: (011)2539-6681 Fax: (011)2539-6675**Toshiba India Private Ltd.**

- New Deli Office
Tel: (0124)499-6600 Fax: (0124)499-6611
- Bangalore Office
Tel: (080)251-90800 Fax: (080)490-91945

Toshiba Electronics Europe GmbH

- Düsseldorf Head Office
Tel: (0211)5296-0 Fax: (0211)5296-400
- France Branch
Tel: (1)47282181
- Italy Branch
Tel: (039)68701 Fax: (039)6870205
- Munich Office
Tel: (089)20302030 Fax: (089)203020310
- Spain Branch
Tel: (91)660-6798 Fax: (91)660-6799
- Sweden Branch
Tel: (08)704-0900 Fax: (08)80-8459
- U.K. Branch
Tel: (0870)060-2370 Fax: (01252)53-0250

Toshiba Vietnam Consumer Products Co.,Ltd.
Tel: (043)776-5950 Fax: (043)776-5956**Toshiba Electronics Asia (Singapore) Pte. Ltd.**
Tel: (6278)5252 Fax: (6271)5155**Toshiba Electronics Service (Thailand) Co., Ltd.**
Tel: (02)501-1634 Fax: (02)501-1638**Toshiba Electronics Trading (Malaysia)Sdn. Bhd.**

- Kuala Lumpur Head Office
Tel: (03)5631-6311 Fax: (03)5631-6307
- Penang Office
Tel: (04)226-8523 Fax: (04)226-8515

Toshiba Electronics (Shanghai) Co., Ltd.

- Shanghai Head Office
Tel: (021)6139-3888 Fax: (021)6190-8288
- Beijing Branch
Tel: (010)6590-8796 Fax: (010)6590-8791
- Chengdu Branch
Tel: (028)8675-1773 Fax: (028)8675-1065
- Hangzhou Office
Tel: (0571)8717-5004 Fax: (0571)8717-5013
- Nanjing Office
Tel: (025)8689-0070 Fax: (025)8689-0125
- Qingdao Branch
Tel: (532)8579-3328 Fax: (532)8579-3329
- Shenzhen Branch
Tel: (0755)2399-6897 Fax: (0755)2399-5573

Toshiba Electronics Asia, Ltd.
Tel: 2375-6111 Fax: 2375-0969**Toshiba Electronics (Dalian) Co., Ltd.**
Tel: (0411)8368-6882 Fax: (0411)8369-0822**Tsurong Xiamen Xiangyu Trading Co., Ltd.**
Tel: (0592)226-1398 Fax: (0592)226-1399**Toshiba Electronics Korea Corporation**
Tel: (02)3484-4334 Fax: (02)3484-4302**Toshiba Electronics Taiwan Corporation**
Tel: (02)2508-9988 Fax: (02)2508-9999

- ▶ Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- ▶ This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- ▶ Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- ▶ **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative.
- ▶ Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- ▶ Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- ▶ The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ▶ **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- ▶ Product may include products using GaAs (Gallium Arsenide). GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- ▶ Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- ▶ Product may include products subject to foreign exchange and foreign trade control laws.
- ▶ Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**

In addition to the above, the following are applicable only to development tools.

- ▶ Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Use the Product in a way which minimizes risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. For using the Product, customers must also refer to and comply with the latest versions of all relevant TOSHIBA information, including without limitation, this document, the instruction manual, the specifications, the data sheets for Product.
- ▶ Product is provided solely for the purpose of performing the functional evaluation of a semiconductor product. Please do not use Product for any other purpose, including without limitation, evaluation in high or low temperature or humidity, and verification of reliability.
- ▶ Do not incorporate Product into your products or system. Products are for your own use and not for sale, lease or other transfer.

TOSHIBA

TOSHIBA CORPORATION
Semiconductor & Storage Products Company