

För icke direkt toleranssatta mått
gäller toleransklass
General tolerances if not other-
wise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt
ritning 4100-4644.
Additional general tolerances in
accordance with drawing 4100-4644.


LASERMÄRKNING/LASER MARKING:

TEXTFONT: GEN-ISO



Datumkod / Date code "YYYYYY"

Serienummer / Serial number "XXXXXXX"

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
1	1017308000	D 4101-0068 4101-1970 4101-1971 A 4101-2611 4101-2615 4101-2724M A 4100-6689 4101-3332 TEXT	031010	SE



A - A



4101-2611
4101-2615
4100-3776
4101-2724M POSITION A

Packas enligt förpackningsritning 4101-2728
Packed according to drawing 4101-2728

Förspänning / Preload: 150 ± 30 N

Tolkmått / Gauge dimensions (mm)		
Urtag Nest	Gåtolk GO	Stopptolk NO GO
Hex 2.67	Ø2.62	Ø2.72
Hex 3.25	Ø3.20	Ø3.30
Sqr 0.72	Ø0.70	Ø0.74

Material			Behandling/Treatment			Status	
Konstr./Design TGW			Ritad/Drawn TGW			Prel.utc.	
Datum/Date 01-12-04			Skala/Scale 1:1			Kontr./Checked Godk./Approved	
pressmaster®			Benämning/Denomination KRIMPTÅNG DCC-0308			Vikt/Weight, gram	
ISO 9001 REG NR FM13687			CRIMPING TOOL			Art grp 012	
						Ritn nr/Drawing no 43002862	
						REV 001	