

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19154-0028

Status:

Active

Overview:

Splices

Description:

InsulKrimp™ Butt Splice for 10-12 AWG Wire



Series

image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-19902-013 (PDF)
- Product Specification PS-19902-007 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-011 (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19154
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Splices
Product Name	Butt, InsulKrimp™
UPC	800753108936

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Insulation	PVC
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	2.540/g
Packaging Type	Bag
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	6.35mm max.
Wire Size AWG	10, 12
Wire Size mm²	3.30 - 5.00

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Old Part Number	C-246X
-----------------	--------

Reference - Drawing Numbers

Product Specification	PS-19902-007, PS-19902-011, PS-19902-013
Sales Drawing	SD-19154-006

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: Yes

China RoHS



Hydrazine
Dibutyl phthalate
Diarsenic pentaoxide
Diarsenic trioxide
Bis (2-ethyl(hexyl)phthalate) (DEHP)
Triethyl arsenate
Benzyl butyl phthalate
2-Pyrrolidinone, 1-methyl
2,4-Dinitrotoluene
Trixylyl phosphate
Sodium perborate;
perboric acid, sodium salt
Sodium
peroxometaborate

Low-Halogen Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19154Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below.
Crimp Height Specifications are then

*contained in the Application Tooling
Specification document.*

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050300</u>
PremiumGrade™ Hand Crimp Tool	<u>0640010100</u>
Hand Crimp Tool	<u>0640010300</u>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050100</u>

This document was generated on 10/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION