

15,000 V - 20,000 V Rectifiers

25 mA - 50 mA Forward Current

100 ns Recovery Time

X150UFG
X200UFG

AXIAL LEADED
HERMETICALLY SEALED




4

ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage (Vrwm)	Average Rectified Current (Io)		Reverse Current @ Vrwm (Ir)		Forward Voltage (Vf)		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impedance θ_{J-L}			Junction Cap. @50VDC @ 1kHz (Cj)
		55°C(1)	100°C(2)	25°C	100°C	25°C		25°C	25°C	25°C	L=000	L=.125	L=.250	25°C
	Volts	mA	mA	µA	µA	Volts	mA	Amps	Amps	ns	°C/W	°C/W	°C/W	pF
X150UFG	15000	50	25	1.0	20	22.0	100	3	0.5	100	5	12	21.5	2.0
X200UFG	20000	25	13	1.0	20	30.0	50	2	0.5	100	5	12	21.5	2.0

(1)TL=55°C L=0.375" (2)TL=100°C L=0.375" (3)If=125mA, Ir=250mA, Irr=63mA • Op.Temp.= -65°C to +175°C Stg.Temp.= -65°C to +200°C



Part	A
X150UFG	.360(9.14) MAX.
X200UFG	.380(9.65) MAX.



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

X150UFG X200UFG

