





PRODUCT NUMBER SEE SHEET 2



|               |            |        |                |            |                |               |                        |                  |       |     |
|---------------|------------|--------|----------------|------------|----------------|---------------|------------------------|------------------|-------|-----|
| spec ref      | *          | dr     | Eddy Zeng      | 2013/11/14 | projection     | MM            | size                   | A3               | scale | 3:2 |
| tolerance std | ASME Y14.5 | eng    | Eddy Zeng      | 2013/11/20 | chr            | Li-He         | 2013/11/20             | ecn no           | -     |     |
|               |            | appr   | Pei-Ming Zheng | 2013/11/20 | product family | PwrBlade+     | rel level              | Released         |       |     |
| surface       | ✓          | linear | 0.X            | ±0.5       | FCI            | 52S           | dwg no                 | 10106262-0013001 | rev   | A   |
|               |            |        | 0.XX           | ±0.25      |                | RA STB HEADER |                        |                  |       |     |
|               |            |        | 0.XXX          | ±0.10      |                |               |                        |                  |       |     |
| ASME Y14.5    | angular    |        | 0°             | ±2°        | www.fci.com    | cat. no.      | Product - Customer Drw | sheet 1 of 3     |       |     |



A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.  
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:  
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.  
-SIGNAL CONTACT - COPPER ALLOY.  
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn  
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.  
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.  
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



Copyright FCI.

|                        |                |            |                                   |                           |                        |          |                  |     |
|------------------------|----------------|------------|-----------------------------------|---------------------------|------------------------|----------|------------------|-----|
| dr                     | Eddy Zeng      | 2013/11/14 | <div>projection</div> <div></div> | <div>MM</div> <div></div> | size                   | A3       | scale            | 3:2 |
| eng                    | Eddy Zeng      | 2013/11/20 |                                   |                           | ecn no                 | -        |                  |     |
| chr                    | Li- He         | 2013/11/20 |                                   |                           | rel level              | Released |                  |     |
| appr                   | Pei-Ming Zheng | 2013/11/20 | product family                    |                           | PwrBlade+              |          |                  |     |
| <div>www.fci.com</div> |                |            | cat. no.                          |                           | Product - Customer Drw |          | sheet 3 of 3     |     |
| <div>FCi</div>         |                |            | title                             |                           | 52S                    |          | rev              |     |
|                        |                |            |                                   |                           | RA STB HEADER          |          | A                |     |
|                        |                |            |                                   |                           | dwg no                 |          | 10106262-0013001 |     |