

THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.


RoHS



LED1 POLARITY			LED2 POLARITY		
PIN 13	PIN 14	COLOR	PIN 15	PIN 16	COLOR
-	+	YELLOW	-	+	GREEN

ELECTRICAL CHARACTERISTICS @ 25°C

TURNS RATIO		
TP1	1CT : 1CT	±2%
TP2	1CT : 1CT	±2%
TP3	1CT : 1CT	±2%
TP4	1CT : 1CT	±2%
OCL @ 100kHz/100mVRMS		
8mA DC BIAS	350 μH MIN.	
INS. LOSS		
0.1MHz TO 1MHz	-1.1 dB MAX	
1MHz TO 65MHz	-0.5 dB MAX	
65MHz TO 100MHz	-0.8 dB MAX	
100MHz TO 125MHz	-1.2 dB MAX	
RET. LOSS (MIN)		
0.5MHz-40MHz	-18 dB	
40MHz-100MHz	-12+20LOG(f/80MHz) dB	
CM TO CM REJ		
100kHz - 100MHz	-30 dB MIN	
CM TO DM REJ		
100kHz - 100MHz	-35 dB MIN	
HIPOT (Isolation Voltage):		1500 Vrms or 2250VDC
100% OF PRODUCTION TESTED TO COMPLY WITH IEEE 802.3 ISOLATION REQUIREMENTS.		
LED 1		
VF (FORWARD VOLTAGE)	IF=20mA	YELLOW 2.1V TYP.
λD (DOMINANT WAVELENGTH)	IF=20mA	YELLOW 590nm TYP.
LED 2		
VF (FORWARD VOLTAGE)	IF=20mA	GREEN 2.2V TYP.
λD (DOMINANT WAVELENGTH)	IF=20mA	GREEN 570nm TYP.




ORIGINATED BY		DATE	TITLE	gigabit MagJack® (12 cores, Tab Up) 0826-1A1T-23-F PATENTED	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REFERENCE		
CHOW WANCHUNG		2014-10-14				TOL. IN INCH		UNIT : INCH [mm]	REV. : E	
DRAWN BY		DATE			FILE NAME	.X		SCALE : N/A	SIZE : A4	
HU XIANG		2014-10-14				.XX			PAGE : 2	
			.XXX							

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

MECHANICAL SPECIFICATION


RoHS



NOTES:

PLASTIC HOUSING: THERMOPLASTIC PA
FLAMMABILITY RATING UL 94V-0
CONTACTS: 50 MICRO-INCH HARD GOLD PLATING
OR EQUIVALENT.
OUTPUT PINS: TIN-COATED COPPER WIRE, DIA 0.018 INCH.
METAL SHIELD: NICKEL PLATED ON COPPER ALLOY.
(ALL GROUND LEADS ARE SOLDER DIPPED)

1. MARK PART WITH MFG LOGO, MFG NAME, PART NUMBER,
DATE CODE AND PATENTED.



- CULUS UL RECOGNIZED - FILE #E196366 AND E169987.
2. THE PRODUCT IS RoHS COMPLIANT.
3. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS.
4. THE PRODUCT IS PATENTED, THE PATENT NUMBER IS
U.S. PAT. 5,736,910.

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM. TOL. IN INCH	[] METRIC DIM. AS REFERENCE
LI QUANKUN	2014-10-14	gigabit MagJack® (12 cores, Tab Up)	08261A1T23-F	.X	UNIT : INCH [mm] REV. : E
DRAWN BY	DATE	0826-1A1T-23-F	FILE NAME	.XX	SCALE : N/A SIZE : A4
ZHANG XUEZHENG	2014-10-14	PATENTED	08261A1T23-F_E.DWG	.XXX ±0.010	PAGE : 3





THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



RECOMMENDED PCB FOOTPRINT

COMPONENT SIDE VIEW



NOTES

THE SHADED AREA ON THE CUSTOMER BOARD ARE
RECOMMENDED TO BE CLEAR OFF ANY VIA HOLE OR
COMPONENT PAD.

ORIGINATED BY
LI QUANKUN

DATE
2014-10-14

TITLE
gigabit MagJack ®
(12 cores, Tab Up)
0826-1A1T-23-F
PATENTED

PART NO. / DRAWING NO.
08261A1T23-F

FILE NAME
08261A1T23-F_E.DWG

STANDARD DIM.
TOL. IN INCH

.X
.XX
.XXX ±0.004

[] METRIC DIM. AS REFERENCE

UNIT : INCH [mm] REV. : E

SCALE : N/A SIZE : A4

PAGE : 4


bel
COMPONENTS FOR A
CONNECTED
PLANET

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



SUGGESTED PANEL OPENING



NOTE:

THE DISTANCE OF PANEL INSIDE SURFACE RELATIVE TO FRONT SURFACE OF PART IS ONLY A SUGGESTION. IN CASE THIS DISTANCE IS DIFFERENT, THE REQUIRED PANEL OPENING DIMENSIONS CHANGE ACCORDINGLY.

PACKING INFORMATION

PACKING TRAY : 0200-9999-F6 (TOP)

0200-9999-F7 (BOTTOM)

PACKING QUANTITY : 40 PCS FINISHED GOODS PER TRAY

10 TRAYS (400 PCS FINISHED GOODS) PER CARTON BOX

NOTE : CARDBOARDS ARE PLACED BETWEEN LAYERS OF PACKING TRAY INSIDE CARTON BOX
(INCLUDE THE UPPERMOST AND LOWERMOST TRAY)

ORIGINATED BY LI QUANKUN	DATE 2014-10-14	TITLE gigabit MagJack ® (12 cores, Tab Up) 0826-1A1T-23-F PATENTED	PART NO. / DRAWING NO. 08261A1T23-F	STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REFERENCE	
				.X		UNIT : INCH [mm]	REV. : E
DRAWN BY ZHANG XUEZHENG	DATE 2014-10-14		FILE NAME 08261A1T23-F_E.DWG	.XX		SCALE : N/A	SIZE : A4
				.XXX	±0.004		PAGE : 5

bel
COMPONENTS FOR A
CONNECTED
PLANET