




REMARK:

1. CHARACTERISTICS:

OPERATING TEMPERATURE RANGE: -55° C~105° C

2. MATERIAL:

INSULATORS: THERMOPLASTIC G.F(UL94V-0) BLACK

SHELL: CARBON STEEL, 100u" Min NICKEL TIN TOP OVER,
50u" Min COPPER UNDER PLATE.

STOPPER: CARBON STEEL.

3. PART NUMBER DESCRIPTION: 10090930-P XX X X LF

SERIES NO.

TYPE
P: PIN (MALE)


NUMBER OF CONTACTS

15: 15-PIN
26: 26-PIN
44: 44-PIN
62: 62-PIN

LF: ROHS COMPLIANT

PLANGE MOUNTING OPTION
A: STANDARD HOLE

CONTACT FINISH
0: NO CONTACT






POS.	PART NO.	A	B	C	D	E	H
15	10090930-P150ALF	30.81	24.99	16.92	19.10	2.29	5.90 ^{+0.25} ₀
26	10090930-P260ALF	39.24	33.32	25.25	27.75	2.29	5.90 ^{+0.25} ₀
44	10090930-P440ALF	53.04	47.04	38.96	41.30	2.29	5.70 ^{+0.25} ₀
62	10090930-P620ALF	69.32	63.50	55.42	57.40	2.41	5.70 ^{+0.25} ₀

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI			
ltr	ecn no	dr	date	linear	.X ± 0.38	projection	MM	www.fciconnect.com			
A	T09-1157	J.H	12/10/09		.XX ± 0.25			title			
					.XXX ± 0.10			HDEC MALE CRIMPING			
				angles	0° ±2°						
				dr	JASON HSU 12/10/09			product family D-SUB		code TWN	
				enr	JASON HSU 12/10/09			size dwg no		sheet 1 of 2	
				chr	GARY HSIEH 12/10/09			A4		10090930	
				appd	JOSEPH HSIA 12/10/09			scale 1:1			
sheet index	revision	A	A								
	sheet	1	2								



PART NO.: 10090930-P780ALF



REMARK:
 1. CHARACTERISTICS:
 OPERATING TEMPERATURE RANGE: -55° C~105° C
 2. MATERIAL:
 INSULATORS: THERMOPLASTIC G.F(UL94V-0) BLACK
 SHELL: CARBON STEEL, 100u" Min NICKEL TIN TOP OVER, 50u" Min COPPER UNDER PLATE.
 STOPPER: CARBON STEEL.
 3. PART NUMBER DESCRIPTION: 10090930-P XX X X LF

SERIES NO. _____
 TYPE _____
 P: PIN (MALE)
 NUMBER OF CONTACTS _____
 78: 78-PIN

LF: ROHS COMPLIANT
 FLANGE MOUNTING OPTION
 A: STANDARD HOLE
 CONTACT FINISH
 0: NO CONTACT

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ± 0.38	projection		title			
A					.XX ± 0.25			HDEC 78P MALE CRIMPING			
					.XXX ± 0.10			product family D-SUB			
				angles	0° ±2°	MM		size dwg no			
				dr	JASON HSU 12/10/09			code			
				enr	JASON HSU 12/10/09			TWN			
				chr	GARY HSIEH 12/10/09	scale	1:1	sheet			
				appd	JOSEPH HSIA 12/10/09			2 of 2			
sheet index	revision sheet										